

SPECIFICATIONS

PERFORMANCE

Processor

Up to 6th Generation Intel® Core™ i7 Processor

Operating System

Windows 10 Home

Graphics

Integrated Intel® or AMD Radeon™ R7 M360

Memory

Up to 16 GB DDR3L

Webcam

1MP HD with Single Microphone /
Intel® RealSense™ 3D Camera¹ (15" only)

Storage

Up to 1 TB HDD /
Up to 1 TB SSHD

Audio

JBL® Stereo Speakers¹ with
Dolby® Advanced Audio™ Certification

Battery²

Up to 4 Hours Local Video Playback

CONNECTIVITY

WiFi and Bluetooth®

WiFi 2 x 802.11 a/c, Bluetooth® 4.0

Connectors

2 x USB 3.0, 1 x USB 2.0, HDMI™-out, VGA,
4-in-1 Card Reader (SD, SDHC, SDXC, MMC),
Audio Combo Jack

DESIGN

Display

14" or 15.6" FHD (1920 x 1080)

Dimensions (W x D x H)

14"
(mm) : 347 x 249 x 24.4
(inches) : 13.66" x 9.80" x 0.96"
15.6"
(mm) : 384 x 265 x 24.6
(inches) : 15.12" x 10.43" x 0.97"

Weight

14" : Starting at 4.6 lbs (2.1 kg)
15.6" : Starting at 5.1 lbs (2.3 kg)

PRELOADED SOFTWARE

Security & Support

- Lenovo™ OneKey Recovery
- Lenovo™ Companion 3.0
- Lenovo™ Photo Master
- Lenovo™ SHAREit
- Lenovo™ REACHit
- McAfee® LiveSafe™



¹ Optional.

² Battery life (and recharge times) will vary based on many factors including system settings and usage. A description of the environment under which the test was performed is available upon request.

LENOVO™ SERVICES

Warranty Upgrades – On-site / In-Home Service

Maximizes PC uptime and productivity by providing convenient, fast repair services in your own home.

Accidental Damage Protection

Avoid the hassles of unexpected repair costs. Provides coverage for non-warranted damage incurred under normal operating conditions, such as minor spills, drops or damage to the integrated screen.

Warranty Extensions (1-to-3 Years Total Duration)

This fixed-term, fixed-cost service helps accurately budget for PC expenses, protect your valuable investment and potentially lower the cost of ownership over time.

OPTIONS & ACCESSORIES



Lenovo™ Bluetooth®
Sports Earphone W520

Ultra long standby up to 100 hrs,
plus 5 hrs talk rechargeable
battery embedded with
Micro USB port



Lenovo™ Wireless
Mouse N100

Contoured design for
smooth & comfortable
navigation



Lenovo™
Speaker M0620

2.0 channel multimedia
speaker system



WWW.LENOVO.COM

Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustrative purposes only. **Lenovo product specifications:** For full Lenovo product specifications, visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. Trademarks: The following are trademarks or registered trademarks of Intel Corporation in the U.S. or other countries. UltraBook, Celeron, Celeron Inside, Core Inside, Intel, Intel Logo, Intel Atom, Intel Atom Inside, Intel Core, Intel Inside, Intel Inside Logo, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, vPro Inside, Xeon, Xeon Phi and Xeon Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product and service names may be trademarks or service marks of others. All product and company names mentioned herein are the trademarks or registered trademarks of their respective owners. Any rights not expressly granted herein are reserved. All other trademarks are property of their respective owners. Battery life (and recharge times) will vary based on many factors including system settings and usage. A description of the environment under which the test was performed is available upon request. ©2015 Lenovo.

