

CTL® Education Chromebook



Intel® Education Solutions
The power to transform the classroom for the 21st century

FAST, SECURE AND SIMPLE

CTL®'s Education Chromebook is designed for the classroom, but versatile enough for the mobile professional. This lightweight, budget-friendly laptop offers security, long battery life and an easy-to-use interface.

Meet Chromebook: A new type of computer *Everything is built-in to make it fast and hassle-free*

There are no software programs or security updates to worry about. The CTL® Education Chromebook updates automatically so it doesn't slow down over time. Its design allows it to wake from sleep quickly and have a long battery life.

Rugged Design for Students and Commuters

Reinforced ports, non-slip texture and retractable handle

The CTL® Education Chromebook is designed to withstand bumps and accidental drops of up to 70cm on concrete. When the device is dropped on a side or corner, the plastic bumper hits the ground first, protecting the LCD screen. Reinforced ports, water-resistant keyboard, a non-slip texture and low-profile carry handle make this the ideal laptop for students and commuters. The fanless design keeps it sleek and cool.

User-Friendly and Ergonomic

Simple interface helps you focus on your tasks

Students, teachers and professionals can quickly get to work because the Education Chromebook starts in seconds. The anti-reflective screen minimizes glare under fluorescent lights and near windows. An ergonomic keyboard with anti-peel keys stands up to the demands of classroom and professional use.

Secure and Serviceable

Built-in protection and a serviceable battery

The Education Chromebook has built-in virus protection, multiple layers of security and verified boot to keep the device safe from viruses, malware and other computer nasties. It's also easy to maintain, with a serviceable battery.

To learn more and reserve yours now, visit <http://ctl.net/education-chromebook>



CTL® Education Chromebook

Item	Description
Screen	11.6" 1366 x 768 HD LED anti-glare screen
Processor	Intel® Celeron® N2930 (2M Cache, up to 2.16 GHz - Quad Core - No Fan)
Battery	Up to 9.5 hours of use* (serviceable battery)
Operating System	Chrome OS
I/O Ports	Full HDMI, 1 x USB 3.0, USB 2.0, 2-in-1 card reader, security lock slot
Storage	16GB SSD
Memory	4GB RAM
Connectivity	Wi-Fi 802.11 a/b/g/n 2 x 2, Bluetooth 4.0
Multimedia	Stereo, Mic that rotates with camera, HD webcam
Dimensions	11.8" x 8.4" x .88"
Weight	3.04 pounds
Ruggedness	70 cm drop, water-resistant keyboard, anti-peel keys, reinforced ports and hinges, non-slip texture
Adapter	40 Watts (19V 2.1A)
Camera	1.0MP 720P HD <u>rotatable</u> camera with optional snap-on lens (30X magnification)
Handle	Retractable handle for easy portability, can hang in a school locker

*Based on manufacturing specs and subject to change based on operating conditions.