

CyberPower

LX1500GU

BATTERY BACKUP

Offers significant energy savings, battery backup and surge protection.

A mini-tower UPS with line interactive topology, the CyberPower LX1500GU provides battery backup (using simulated sine wave output) and surge protection for desktop computers, workstations, networking devices, and home entertainment systems.

The LX1500GU uses Automatic Voltage Regulation (AVR) to correct minor power fluctuations without switching to battery power, which extends battery life. AVR is essential in areas where power fluctuations occur frequently. Two USB charge ports power portable devices such as mobile phones and tablets, even during a utility power failure.

The LX1500GU comes with a three-year warranty (including coverage of batteries) and a \$500,000 Connected Equipment Guarantee.

TYPICAL APPLICATIONS

- Desktop Computers
- Home Networking
- Voice Over Internet Protocol (VoIP) Phone Systems
- Personal Electronics
- Home Theater Equipment

FEATURES

- 1500VA / 900W
- Line-Interactive Topology
- AVR & GreenPower UPS™
- Multifunction LCD Panel
- USB 2.1A Charging Ports
- RJ45 and Coax Protection
- Mini-Tower Form Factor
- 10 Outlets / USB Port
- EMI/RFI Filters
- PowerPanel® Personal
- Three-Year Warranty



SPECIFICATIONS

GENERAL	
UPS Topology	Line Interactive
ENERGY STAR® Certified	Yes
Energy Saving	GreenPower UPS™ Bypass Technology

INPUT	
Input Frequency Range	57 Hz - 63 Hz
Plug Style	Right Angle - 45° Offset
Circuit Breaker	15 A

LX1500GU BATTERY BACKUP

SPECIFICATIONS

OUTPUT	
Overload Protection	Internal Circuitry Limiting, Circuit Breaker Protected
Outlets - Widely Spaced	2
Watts	900 W
On Battery Frequency	60 Hz +/- 1%
Outlets - Battery & Surge Protected	5
Outlets - Surge-Only Protected	5
Automatic Voltage Regulation	Single Boost
VA	1500 VA
On Battery Voltage	120 VAC +/- 5%
On Battery Waveform	Simulated Sine Wave
Outlets - Total	10
BATTERY	
Runtime at Half Load	14 min
Battery Type	Sealed Lead-Acid Battery
Battery Quantity	2
Replacement Battery Cartridge	RB1290X2
Typical Recharge Time	8 Hours
Runtime at Full Load	2 min
Battery Size	12 V / 9 Ah
User Replaceable Battery	Yes
MANAGEMENT & COMMUNICATIONS	
Software (Free Download)	PowerPanel® Personal
Audible Alarms	Battery Mode, Low Battery, Overload, Fault
HID Compliant USB Port	Yes
Management Cable	USB Cable
LED Indicators	Power On, Wiring Fault



SURGE PROTECTION & FILTERING	
Network Protection RJ45	1-in / 1-out (10/100/1000)
Surge Suppression	890
PHYSICAL DIMENSIONS	
Physical Dimensions - Width/Height/Depth (cm)	9.91 x 24.89 x 34.8 cm
Physical Dimensions - Width/Height/Depth (mm)	99 x 249 x 348 mm
Physical Dimensions - Width/Height/Depth (in.)	3.9 x 9.8 x 13.7 in.
Weight (lbs.)	25 lbs.
Weight (kg)	11.3 kg
ENVIRONMENTAL	
Operating Temperature	32 to 104 °F (0 to 40 °C)
Operating Relative Humidity	0 to 90 % (non-condensing)
CERTIFICATIONS	
Environmental	RoHS Compliant
Safety	UL1778 cUL FCC DOC Class B
WARRANTY	
CEG Amount	\$500,000
Product Warranty	Three-Year Limited
Connected Equipment Guarantee	Lifetime