



Fortinet AP122

802.11ac Wall Plate Access Point

802.11ac in-room performance for hospitality and higher education

The AP122 is the first wall plate access point specifically designed to meet the ever-increasing mobile data needs of hotel guests and resident college and university students. With gigabit-data rates, the AP122 is perfectly suited for in-room deployment needs of the hotel, cruise line and higher-education residence-hall markets.

Designed to be placed in any location flush to a wall utilizing a standard junction box, the AP122 can be installed by standard service personnel using existing CAT5/6 cabling connected from a standard wall junction box. For wired connectivity, it features two 10/100 BASE-T switch ports to support a range of in-room IP device and user connectivity options. Additionally, one of the wired ports can operate as an IEEE 802.3af-compliant PoE Out port offering up to 13 watts of power, capable of powering devices such as IP telephones. This reduces costs in additional cabling, switch ports, and power sourcing equipment. An additional pass-through port allows connectivity for digital phones and a USB port offers options for future uses. The AP122 is built to provide years of trouble-free operation and is backed by a limited lifetime warranty.

With guest surveys commonly ranking Wi-Fi as the most requested guest amenity for the hospitality industry, ensuring a high-quality mobile experience has never been more critical. Like other Fortinet access points, the AP122 integrates seamlessly with our Network Manager, Mobile Connect, and other application solutions to bring intelligent management and resilient wireless services to your network. The AP122 is ideal for supporting IP-based services such as VoIP, IPTV, high-speed Internet access and in-room device connectivity. With Fortinet organizations can easily offer tiered services to different users, differentiating guests, employees, students and facility.

Additionally, Fortinet's single-channel option within the Mobile**FLEX** platform uniquely allows the AP122 to support pervasively, full channel 802.11ac in real-world deployments, which more than double the data rate over legacy 802.11n solutions. This architecture also greatly simplifies RF coverage planning and significantly reduces wireless LAN (WLAN) deployment costs.

AP122

802.11ac Wall Plate Access Point



Features

- 802.11ac 2x2:2 in-room wall plate form factor
- Multiple 10/100 client, PoE Out, pass-through ports
- Supports pervasive 80 MHz channel usage

Benefits

- Support for in-room, IP-based services such as VoIP, streaming video, and high-speed Internet access
- Support for in-room IP devices and digital phones with native access to in-house PBX system
- Maximizes full-channel 802.11ac throughout the enterprise
- No infrastructure upgrades



FortiCare Worldwide 24x7 Support
support.fortinet.com



FortiGuard Security Services
www.fortiguard.com

SPECIFICATIONS

Operating Modes

Centralized deployment mode
Distributed deployment mode
Remote VPN tunnel mode

Security

WEP, WPA-PSK, WPA-TKIP, WPA2-AES, 802.11i, 802.1X (EAP-TLS, EAP-TTLS, PEAP, LEAP, EAP-FAST, EAP-SIM, EAP-AKA, and EAP-MD5)
802.1X and captive portal authentication against local database on the controller, RADIUS, and Active Directory
RADIUS-assisted per-user and per-ESSID access control via MAC filtering

Management

Automatically discovers controllers and downloads configuration settings for plug-and-play deployment
Upgrades and management using System Director/E(z)RF® Network Manager
Support for SNMP

Wireless Specifications

Model Introduction

AP122 is a dual-radio architecture with:
- 2.4 GHz Std 802.11b/g/n
- 5.6 GHz 802.11a/n/ac

Supported radio technologies

2x2:2SS (two spatial streams)
IEEE Std 802.11b with Direct Sequence Spread Spectrum (DSSS)
IEEE Std 802.11ac with 20/40/80 MHz (HT20/HT40/VHT80) channel width
IEEE Std 802.11n with 40 MHz (HT40) channel width
IEEE Std 802.11a/g with 20 MHz channel

Supported Modulation

IEEE Std 802.11ac: BPSK, QPSK, 16-QAM, 64-QAM, and 256-QAM
IEEE Std 802.11a/g/n: BPSK, QPSK, 16-QAM, and 64-QAM
IEEE Std 802.11b: BPSK, QPSK, CCK

Supported MCS Index

Supported MCS0 to MCS9 for IEEE Std 802.11ac (NSS=1 to 2)
Supported MCS0 to MCS15 for IEEE Std 802.11n

Supported Frequency Bands

2.400 to 2.4835 GHz (ISM)
5.150 to 5.250 GHz (UNII-1)
5.250 to 5.350 GHz (UNII-2, upon DFS approval)

AP122 Default Transmit Power

Default transmit power per antenna	2.4 GHz:10dBm	5.2 GHz:13 dBm
Maximum available transmit power per antenna	2.4 GHz:17 dBm	5.2 GHz:17 dBm
Transmit power adjustment	1 dBm increments	

Actual Tx power dependent on national regulatory limits

AP122 Receiver Sensitivity

Standard	Data rate (Mbps)	Receiver sensitivity (dBm)
2.4GHz, IEEE 802.11b	1	-97
	11	-89
2.4GHz, IEEE 802.11g	6	-94
	54	-76
2.4GHz, IEEE 802.11n HT20	MCS0/8	-93
	MCS7/15	-72
2.4GHz, IEEE 802.11n HT40	MCS0/8	-91
	MCS7/15	-70
5GHz, IEEE 802.11a	6	-92
	54	-72
5GHz, IEEE 802.11n HT20	MCS0/8	-90
	MCS7/15	-72
5GHz, IEEE 802.11n HT40	MCS0/8	-86
	MCS7/15	-68
5GHz, IEEE 802.11AC HT20	MCS0NSS1/2	-89
	MCS8NSS1/2	-68
5GHz, IEEE 802.11AC HT40	MCS0NSS1/2	-88
	MCS8NSS1/2	-62
5GHz, IEEE 802.11AC HT80	MCS0NSS1/2	-82
	MCS8NSS1/2	-60

Antennas

Four integrated Single band omni-directional antennas for 2x2 MIMO with maximum antenna gain of 3.6 dBi in 2.4 GHz and 5 dBi in 5 GHz. Antennas are optimized for vertical wall mounted orientation of the AP.

Physical Specifications

Power

IEEE PoE (Power over Ethernet) 802.3af/802.3at injector or switch
48V external power adapter (sold separately)

Other Interfaces

One 10/100/1000 Mbps BASE-T Ethernet RJ45 for Data uplink (G1)
One 10/100 Mbps BASE-T Ethernet RJ45 port with PoE Out support.
One 10/100 Mbps BASE-T Ethernet RJ45 port
One USB 2.0 port (Type-A)
One reset button
One RJ45 Passthrough port: RJ45 to RJ45
One USB 2.0 port (Type-A)
One reset button
One RJ45 Passthrough port: RJ45 to RJ45
One USB (future use)
One tri-color LED over facade for AP status

LED Indicators

One tri-color LED for AP status

Mounting

Wall mount: junction box wall mount bracket included

Dimensions

AP122: 5.51" x 5.35" x 1.18" (14.0 cm x 13.6 cm x 3.0 cm)

Environmental

Operating temperature: 32° F to 104° F (0° C to 40° C)

Operating humidity: 5 to 95% (non-condensing)

Storage temperature: -40° F to 185° F (-40° C to 70° C) ambient

Storage humidity: 5 to 95% (non-condensing)

SPECIFICATIONS

AP122 Regulatory Compliance

Unintentional Radiation Compliance Requirements

FCC Part 15.107 - 47CFR15.107 October 1, 2008 Class B

FCC Part 15.109 - 47CFR15.109 October 1, 2008 Class B

ICES-003 Class B – issue 4, February 2004

EN 301 489-1

EN 301 489-17

EN55022 Class B – 2006

EN55024 / AS/NZS CISPR 24 / Immunity

EN61000-4-2,3,4,5,6

Japan VCCI Class B

EN60601-1-2

Radio Compliance Requirements

FCC Part 15.247 - 47 CFR Ch. I (10-1-00 Edition)

FCC Part 15.407 - 47 CFR15.407 October 1, 2008

RSS-210 Issue 8, December 2010

RSS-210 W52, W53 and W56

EN 300 328 v1.7.1 (2006-05)

EN 301 893 V1.7.1 (2008-12)

Japan Radio Law 38-24-1 (Ninsho) - WW 2.4 GHz band

Japan Radio Law 38-24-1 (Ninsho) - XW 5.3 GHz band and YX 5.6 GHz band

Certification Pending

Wi-Fi Certification pending – IEEE Std 802.11a/b/g/n/ac

Warranty

Limited lifetime warranty

Part Number

AP122: 802.11ac 2x2:2 dual radio, dual concurrent wall plate access point

Safety Compliance Requirements

UL 60950-1, 2nd Edition, 2011-12-19

CSA C22.2 No. 60950-1-07, 2nd Edition, 2011-12

EN 60950-1:2006+A11:2009+A1:2010+A12:2011

IEC 60950-1(ed. 2), IEC 60950-1(ed. 2);am1

Environmental Compliance Requirements

RoHS, Directive 2011/65/EU (RoHS 2)

WEEE, Directive 2012/19/EU

REACH, Regulation (EC) No 1907/2006

Ethernet Standards

Ethernet IEEE 802.3

Power Over Ethernet IEEE 802.3at PD

Power Over Ethernet IEEE 802.3af PSE

Wireless IEEE 802.11a/b/g/n/ac



GLOBAL HEADQUARTERS
Fortinet Inc.
899 Kifer Road
Sunnyvale, CA 94086
United States
Tel: +1.408.235.7700
www.fortinet.com/sales

EMEA SALES OFFICE
120 rue Albert Caquot
06560, Sophia Antipolis,
France
Tel: +33.4.8987.0510

APAC SALES OFFICE
300 Beach Road 20-01
The Concourse
Singapore 199555
Tel: +65.6513.3730

LATIN AMERICA SALES OFFICE
Prol. Paseo de la Reforma 115 Int. 702
Col. Lomas de Santa Fe,
C.P. 01219
Del. Alvaro Obregón
México D.F.
Tel: 011-52-(55) 5524-8480