

Business Laser Printer

HL-L6400DWT



The award-winning HL-L6400DWT monochrome laser printer is ideal for mid to large-sized workgroups with high print volumes, looking for a low total cost of ownership, advanced security features and improved productivity.

- Help maximize your budget with included Brother Genuine super high-yield cartridge for built in value and even lower cost printing with the ultra high-yield replacement cartridge
- Advanced security features provide network user authentication and help limit device and document access
- Dual paper trays help minimize user intervention and scalable paper handling is ideal for workgroups that require customized workflows
- Help improve your document workflow with a fast print speed
- Color Touchscreen display allows for easy menu navigation with the ability to create shortcuts to help simplify complex and frequently used tasks.
- Flexible connectivity and direct printing from popular business cloud services^A are ideal for today's mobile workforce

HL-L6400DWT

Specifications:

Print Technology	Electrophotographic Laser
LCD Display (type/size)	1.8" Color Touchscreen Display
Paper Size (maximum)	Paper Trays: Up to 8.5" x 14" (legal) Multi-Purpose Tray: 3.0" - 8.5" (W) / 5.0"-14" (L)
Print Speed (maximum)	Up to 52ppm
Time to First Page [▲]	Less than 7.5 seconds
Print Resolution (maximum)	Up to 1200 x 1200 dpi
Processor	800 MHz
Emulations	PCL6, BR-Script3*, IBM Proprinter, Epson FX, PDF version 1.7, XPS Version 1.0
Duplex Printing Capability	Yes
Paper Input Capacity (maximum) [∞]	(2) 520-sheet capacity paper trays, 50-sheet capacity multi-purpose tray
Optional Input Capacity (max.*) [∞]	1,610 sheets via optional tray
Output Capacity (std. / max.*) [∞]	250 sheets (face down), 10 sheets (face up), 1,050 sheets via optional mailbox/sorter/stacker
Media Types	Plain Paper, Letterhead, Colored Paper, Recycled Paper, Bond, Labels, Envelopes (up to 10)
Media Weights	Standard Paper Trays: 16 to 32 lbs. Multi-Purpose Tray: 16 to 53 lbs.
Memory (std. / max.)	512MB / 512MB
Standard Interfaces	Wireless 802.11b/g/n, Gigabit Ethernet, Hi-Speed USB 2.0
USB Host	Yes, Back (for external IC Card Reader) [°]
Operating Systems Compatibility	Windows: XP Home / XP Professional / XP Professional x64 Edition / Windows Vista / Windows 7, 8, 8.1, 10 / Windows Server 2003 / 2003 R2 (32/64 bit) / 2008 / 2008 R2 / 2012 / 2012 R2 macOS v10.8.5, 10.9.x, 10.10.x Linux
Mobile Device Compatibility [□]	AirPrint®, Google Cloud Print™ 2.0, Brother iPrint&Scan, Cortado Workplace, Mopria®, Wi-Fi Direct®, NFC ⁺
Web Connect ^Δ	GOOGLE DRIVE™, ONEDRIVE, DROPBOX, BOX, ONENOTE, EVERNOTE®
Security Features	Integrated NFC Card Reader, Active Directory, Secure Function Lock, Enterprise Security (802.1x), Lock Slot, Secure Print, SSL/TLS, IPsec
Warranty	1-year limited warranty

▲ From ready mode and standard tray.

* PostScript®3™ compatible.

∞ Maximum capacity based on using 20 lb. paper.

* Additional purchase required.

° Requires connection to a wireless network.

□ Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4).

^ Approximately 50,000 pages based on 3 pages per job and 30,000 pages based on 1 page per job and [letter/A4 simplex pages]. The number of pages may be affected due to a variety of factors including but not limited to media type and media size.

Δ Requires an Internet connection and an account with desired service.

+ The mobile device must have NFC capability and run Android OS 4.0 or later.

○ See www.brother.com for details.

Supplies & Accessories*:

TN-820	Standard Yield Toner Cartridge (approx. 3,000 pages)▼
TN-850	High-Yield Toner Cartridge (approx. 8,000 pages)▼
TN-880	Super High-Yield Toner Cartridge (approx. 12,000 pages)▼
TN-890	Ultra High-Yield Toner Cartridge (approx. 20,000 pages)▼
DR-890	Drum Unit (approx. 50,000 pages) [^]
LT-5505	Optional 250-Sheet Capacity Paper Tray
LT-6505	Optional 520-Sheet Capacity Paper Tray
MX-4000	4-Bin Mailbox/Stacker/Sorter
CH-1000	Card Reader Holder
BP60MPLTR	Multi-Purpose Paper (Letter, 500 sheets)
CB-2000	15.7" Printer Cabinet/Stand



At your side support. Online, call or live chat – Brother provides FREE technical support for the life of your product. At Brother, we want to ensure that your experience with us is exceptional. Visit us at brother-usa.com where you can download the latest product drivers and software, view product manuals, learn how to get the most out of your product with how-to videos and find answers to frequently asked questions.



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth. www.brotherearth.com

COMPATIBLE WITH
WINDOWS

