

Strong enough for every day.

Lenovo N22 Chromebooks are rugged, durable, and adaptable to any setting. Plus, their thin and light design makes them the perfect solution for on-the-go work, school, and play.



Rugged and Durable

- **Drop resistant** – built to withstand bumps and accidental drops from up to 70cm (2.3 feet)
 - **Stronger, thicker** rear cover and a frame around the screen, sides and corners absorb the force of bumps and reduce damage when dropped.
- **Reinforcement** around ports and hinges adds durability that stands up to student wear and tear
- **Anti-peel keys** resist removal by students
- **Water resistant keyboard** channels spills (up to 330ml) away from the electronics to prevent damage.
- **Sealed touchpad** protects the electronics from moisture and spills
- **Non-slip texture** hides wear and scratches and helps the students to better grip the device
- **Fanless design** eliminates the need for bottom vents which helps keep debris away from the electronics

Designed for Education

- **Rotatable camera** gives students flexibility in how they capture images and video.
 - A student can rotate the camera away to record a science experiment or capture video of other students doing a skit or presenting a report.
 - A student can rotate the camera up to closely examine an object.
 - The integrated microphone also rotates with the camera to better capture sound.
- The **anti-glare screen** produces less reflection under florescent lights and near classroom windows, reducing student eyestrain.
- With **up to 10 hours of battery life**, teachers and students can work where they need to without a power cord. The battery is serviceable and can be replaced by school IT.

Performance

Processor

Intel® Celeron N3050 (Dual core, 1M Cache, up to 2.58GHz)

Operating System

Chrome OS

Memory

2GB or 4GB Options

Camera

Rotatable 1.0MP 720p HD camera can be angled to capture images, video and support scientific inquiry activities

Storage

16GB SSD and optional GoogleDrive cloud storage

Audio

Stereo sound
Integrated microphone rotates with camera

Battery

Up to 10 hours of battery life (3200 mAH/cell) polymer 38Wh
Serviceable battery – can be replaced by school IT

Design

Display

11.6" 1366x768 resolution HD LED anti-glare screen

Dimensions

300mm x 215mm x 22.1 mm
11.8 inches x 8.5 inches x 0.88 inches

Weight

1.29kg (2.8lbs)

Connectivity

Ports

2-in-1 card reader (SD/MMC)
Full HDMI
2x USB3.0
Kensington security lock slot

Communication

Intel Dual Band AC 7260 adapter (WIFI 802.11 ac/a/b/g/n 2x2 with Bluetooth 4.0)




Warranty

1 Year Limited Mail-In Warranty

Optional Service Upgrades

- Priority Technical Support
- Warranty Upgrades
- Accidental Damage Protection

Recommended Accessories & Services

 <p>Sleeve</p> <p>4X40E48909</p>	 <p>Essential Backpack</p> <p>4X40E77329</p>	 <p>Security Cable Lock</p> <p>57Y4303</p>	<p>Upgrade to 3-year depot warranty with Accidental Damage Protection</p> <p>P/N 5PS0H71476</p>
--	---	--	--