

For longer extension distances, use a [B126-1A0](#) or [B126-1A0-WP-1](#) active receiver to:

- Extend a 1080p(60Hz) signal up to 150 ft.(45.7 m)
- Extend a 1080i(60Hz) signal up to 200 ft.(61 m)
- Extend a 3D signal up to 125 ft.(38.1 m)

For shorter distances, use a [B126-1P0](#) passive receiver to:

- Extend a 1080p(60Hz) signal up to 50 ft.(15.2 m)
- Extend a 1080i(60Hz) signal up to 100 ft.(30.5 m)

Further extend the signal range or add more displays by using a Tripp Lite [B126-110](#) Remote Repeater unit to:

- Add up to three repeaters on each channel of the [B126-002](#) for a total of 4 displays per channel(a receiver should be the last unit in a channel)
- Extend a 1080p(60Hz) signal up to 125 ft.(38.1 m) for each repeater added into a channel
- Extend a 1080i(60Hz) signal up to 175 ft.(53.3 m) for each repeater added into a channel
- Extend a 3D signal up to 100 ft.(30.5 m) for each repeater added into a channel

## 2-Port HDMI over Cat5/Cat6 Extender/Splitter, Box-Style Transmitter for Video/Audio, 1080p @ 60 Hz w/Intl. Power Supply

MODEL NUMBER: **B126-002-INT**



### Description

The B126-002-INT 2-Port HDMI over Cat5/Cat6 Extender/Splitter works with Tripp Lite B126-Series remote receivers to split a single HDMI audio/video signal into two separate signals. It's ideal for digital signs, trade shows, presentations, retail settings and other applications where the video source is located farther than conventional cables allow or that require multiple displays connected to one source. It uses HDMI cable(see Tripp Lite's P568-Series) to connect to the source and Cat5e/6 cable to transmit to the remote monitors(for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series).

When used with Tripp Lite's [B126-1A0](#) or [B126-1A0-WP-1](#) active remote receivers, the Extender/Splitter can extend a 1080i(60 Hz) signal up to 200 feet(61 m), a 1080p signal(60 Hz) up to 150 feet(45.7 m) and a 3D signal up to 125 feet(38.1 m). With a [B126-1P0](#) or [B126-1P0-WP-1](#) passive remote receiver, it can extend a 1080i(60 Hz) signal up to 100 feet(30.5 m) and a 1080p(60 Hz) signal up to 50 feet(15.2 m). Add up to three [B126-110](#) remote repeaters to each

### Highlights

- Perfect for digital signs, trade shows and retail settings
- Supports high-definition video resolutions up to 1080p (60 Hz)
- Supports stereo and 7.1-channel surround sound audio
- Works with all operating systems and HDMI video sources
- Plug and play—no software or drivers to install

### Package Includes

- B126-002-INT 2-Port HDMI over Cat5/Cat6 Extender/Splitter
- External power supply w/CEE 7/16 Schuko, BS1363 UK and AS2112 Australia plugs (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V, 2A)
- Mounting hardware
- Owner's manual

channel to fully extend the signal range or add more displays.

In addition to high-definition video, the B126-002-INT delivers full, rich stereo and 7.1-channel surround sound(multi-channel or PCM) audio. Easy to set up with no software or drivers to install. Mounts to a wall, rack or pole using the included hardware.

## Features

### Extends High-Definition Signals

- Extends a 1080i(60 Hz) signal up to 175 ft.(53.3 m), a 1080p(60 Hz) signal up to 125 ft.(38.1 m) and a 3D signal up to 100 ft.(30.5 m) with each optional Tripp Lite [B126-110](#) remote repeater
- Extends a 1080i(60 Hz) signal up to 200 ft.(61 m), a 1080p(60 Hz) signal up to 150 ft.(45.7 m) and a 3D signal up to 125 ft.(38.1 m) with Tripp Lite [B126-1A0](#) or [B126-1A0-WP-1](#) active remote receiver
- Extends a 1080i(60 Hz) signal up to 100 ft.(30.5 m) and a 1080p(60 Hz) signal up to 50 ft.(15.2 m) with Tripp Lite [B126-1P0](#) or [B126-1P0-WP-1](#) passive remote receiver
- Add up to 3 remote repeaters on each channel for maximum signal range
- Connects to next link in the chain with one Cat5e/6 cable(for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series)

### Supports the Latest Video and Audio Resolutions

- Works with all operating systems and HDMI video sources
- Supports HD resolutions up to 1080p(60 Hz)
- Supports stereo and 7.1-channel surround sound(multi-channel or PCM) audio
- Supports 24-bit True Color(8 bits per channel) and HDCP

### Easy to Set Up and Use

- Plug-and-play engineering—no software or drivers to download and install
- Connects quickly to source with HDMI cable, such as Tripp Lite's P568-Series
- LEDs indicate at a glance when the unit is receiving power and an HDMI signal from the source
- Included mounting hardware lets you install the unit on a wall, rack or pole
- International power supply with CEE 7/16 Schuko, BS1363 UK and AS2112 Australia plugs

## Specifications

OVERVIEW	
Cable Type	HDMI; UTP (Cat5, Cat5e, Cat6, Cat6a)
PHYSICAL	
Unit Dimensions (hwd / in.)	1 x 2.5 x 3.6
Unit Dimensions (hwd / cm)	2.54 x 6.35 x 9.14
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
<b>CONNECTIONS</b>	
Connector A	(2) RJ45 (FEMALE)
Connector B	HDMI (FEMALE)
Ports	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>