

## QSFP28 to QSFP28 100GbE Passive DAC Cable (M/M), QSFP-100G-CU2M Compatible, 2M (6.56 ft.)

MODEL NUMBER: **N282-02M-28-BK**



Combines four SFP channels operating at up to 28 Gbps into one affordable 100GbE cable. Ideal for data centers, high-end servers and enterprise wiring closets.

### Features

#### Connect Network Equipment at Speeds Up to 100 Gbps

- Combines four 28 Gbps SFP channels into single high-density cable
- Ideal for data centers, high-end servers and enterprise wiring closets
- Multi-platform support for 128G Fibre Channel and EDR InfiniBand
- Lower port cost and power budget when compared to fiber optics

#### Top-of-the-Line Construction

- 100 GbE 38-position “board-as-connector” design
- Zinc die-cast male QSFP+ connectors for superior EMI resistance
- Ergonomic pull-tab ejectors for quick, easy connections
- 8-pair wire technology optimized for bandwidth-intense applications
- Flexible 26 AWG conductors maintain smooth high-frequency response

#### Fully Compliant and Compatible

- Meets or exceeds strict 100-Gigabit Ethernet (100GBASE-CR4) standards
- Complies with IEEE 802.3bj and RoHS
- Complies with latest QSFP28 MSA (Multi-Source Agreement) SFF-8665 architecture
- Compatible with all QSFP and QSFP+ ports
- Compatible to Cisco QSFP-100G-CU2M

### Highlights

- Supports serial data rates up to 100 Gbps
- Complies with MSA SFF-8665 specifications
- Compatible to Cisco QSFP-100G-CU2M
- Meets or exceeds 100GBASE-CR4 standards
- Multi-platform support for 128G Fibre Channel and EDR InfiniBand
- Pull-tab ejectors for quick, easy connections

### System Requirements

- Networking switch or other hardware with open QSFP+ ports

### Package Includes

- N282-02M-28-BK QSFP28 to QSFP28 100GbE Passive DAC Copper InfiniBand Cable (M/M), 2 m (6 ft.)

## Specifications

OVERVIEW	
UPC Code	037332193155
Technology	SFP+/QSPP+/QSFP28
PHYSICAL	
Color	Black
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	9.5mm
Wire Gauge (AWG)	26
Cable Length (ft.)	6.6
Cable Length (m)	2
Cable Length (in.)	79.2
Cable Length (cm)	201.168
Minimum Bend Radius	50mm
Shipping Dimensions (hwd / cm)	43.18 x 36.32 x 1.27
Shipping Dimensions (hwd / in.)	17.00 x 14.30 x 0.50
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
ENVIRONMENTAL	
Operating Temperature Range	0 to +70
Storage Temperature Range	-20 to +85
Operating Humidity Range	5% to 85% RH
Storage Humidity Range	5% to 85% RH
COMMUNICATIONS	
Network Speed	100Gbps
IEEE Standards Supported	802.3bj
CONNECTIONS	
Side A - Connector 1	QSFP+ (MALE)
Side B - Connector 1	QSFP+ (MALE)
FEATURES & SPECIFICATIONS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Style	Passive
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	MSA SFF-8665, IEEE 802.3bj, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>