



→ SKU: ZBOX-BI325-BE/U/J/AUS

BI325



Enjoy a rich multimedia experience with energy efficient ZOTAC ZBOX BI325 mini-PC. Powered by the new Intel Braswell processor that trumps its predecessor with performance and power consumption, this Mini PC is the perfect desktop replacement.

The ZBOX BI325 stands no taller than a coffee maker and no wider than a toaster. It is perfect for daily activities such as web browsing, e-mails, productivity, and smooth HD entertainment.



technical specifications

FEATURES

- Intel Virtualization technology (VT-x)
- Intel Quick Sync Video technology
- Intel Clear Video HD technology
- Microsoft DirectX 11.2 compatible
- 802.11ac WiFi & Bluetooth 4.0 technology

SPECIFICATIONS

- Intel HD Graphics
- Intel N3160 (quad-core, 1.6 GHz up to 2.24 GHz)

HARD DRIVE & MEMORY

- 1 x 2.5-inch SATA 6.0 Gbps HDD/SSD slot
- 2 x DDR3L-1600 SO-DIMM slot (up to 8GB)

DISPLAY OUTPUTS

- HDMI 1.4b (3840x2160 @ 30 Hz)
- DisplayPort 1.1a (2560x1200 @ 60 Hz)
- VGA (2560x1200 @ 60 Hz)
- HDCP compliant

AUDIO OUTPUTS

- Loss-less Bitstream (LPCM / bitstream via HDMI)
- Combo mini-optical S/PDIF / analog stereo

FRONT PORTS

- Microphone input
- Headphone / mini-SPDIF output
- 3-in-1 card reader (SD/SDHC/SDXC)
- USB 3.0 port
- USB 3.0 type-C port
- WiFi LED
- Hard drive LED
- Power button

TOP PORTS

- 1 x USB 2.0 port

REAR PORTS

- 2 x USB 3.0 port
- 1 x 10/100/1000 Ethernet (RJ45)
- Power connector
- Wi-Fi Antenna connector

SOFTWARE COMPATIBILITY

- Microsoft Windows 10 (32/64-bit)
- Microsoft Windows 8.1 / 7* (64-bit)

MINI-PC DIMENSIONS

- Length: 188mm (7.4in)
- Width: 188mm (7.4in)
- Height: 44mm (1.73in)

BOX DIMENSIONS

- Length: 260mm (10.24in)
- Width: 210mm (8.27in)
- Height: 100mm (3.94in)

INSIDE THE BOX

- ZOTAC ZBOX BI325
- Power brick & cable
- Stand
- Mini Optical S/PDIF adapter
- 1 x Wi-Fi Antenna
- Driver disc

*Please refer to "installing Windows 7" in the User manual for Windows 7 installation instructions



HDMI®
HIGH-DEFINITION MULTIMEDIA INTERFACE

