



Hewlett Packard
Enterprise

HPE OFFICECONNECT 1405 SWITCH SERIES

Fixed Port Unmanaged Ethernet Switches



WHAT'S NEW

- New entry level 5G- and 8G- port switches for small offices.
- Plug and play, no configuration required.
- Quality of Service (QoS) and flow control for improved network efficiency.
- Energy Efficient Ethernet for low power consumption.
- 3 year warranty with 24X7 phone support

OVERVIEW

The HPE OfficeConnect 1405 Switch Series is a plug-and-play unmanaged fixed-port Layer 2 switch designed for small offices. These switches are preconfigured with connections using low-cost Ethernet copper cabling. They are Class B certified, energy efficient and quiet. They support administration-friendly features such as auto-negotiation. Designed for high reliability, long life, and low power consumption, they are ideal for businesses concerned with total cost of ownership.

for 90 days.

FEATURES

Ease of Use

The HPE OfficeConnect 1405 Switch Series offers unmanaged plug-and-play simplicity.

A comprehensive LED display with per-port indicators provides an at-a-glance view of status, activity, speed, and full duplex operation.

Flow control helps to provide reliable communications during full-duplex operation.

Connectivity and Performance

The HPE OfficeConnect 1405 Switch Series with Auto-MDIX automatically adjusts to straight-through or crossover cables on all 10/100 and 10/100/1000 ports.

Jumbo packet support for Gigabit Ethernet ports only offers up to 9216-byte frame size to improve performance of larger data transfers.

Half/Full duplex auto-negotiating capability on every port doubles the throughput of every port.

Quality of Service (QoS)

The HPE OfficeConnect 1405 Switch Series has IEEE 802.1p prioritization delivering data to devices based on priority and type of traffic.

The switches support energy efficient Ethernet.

Technical specifications

HPE OfficeConnect 1405 Switch Series

Differentiator	Unmanaged desktop switches designed for small offices.
Ports	Up to (16) 10/100 or (16) 10/100/100 ports, depending on model
Throughput	Up to 23.7 Mpps, depending on model
Routing/switching capacity	Up to 32 Gbps, depending upon model
Input voltage	100-240 VAC



For additional technical information, available models and options, please reference the [QuickSpecs](#)

HPE POINTNEXT SERVICES

[HPE Pointnext Services](#) brings together technology and expertise to help you drive your business forward and prepare for whatever is next.

Operational Services from HPE Pointnext Services

[HPE Pointnext Tech Care](#) provides fast access to product-specific experts, an AI-driven digital experience, and general technical guidance to help enable constant innovation. We have reimagined IT support from the ground up to deliver faster answers and greater value. By continuously searching for better ways to do things—as opposed to just fixing things that break—HPE Pointnext Tech Care helps you focus on achieving your business goals.

[HPE Pointnext Complete Care](#) is a modular, edge-to-cloud IT environment service that provides a holistic approach to optimizing your entire IT environment, and achieving agreed upon IT outcomes and business goals through a personalized and customer-centric experience. All delivered by an assigned team of HPE Pointnext Services experts.

HPE Integration and Performance Services help you customize your experience at any stage of your product lifecycle with a menu of services based on individual needs, workloads, and technologies.

- Advise, design, and transform
- Deploy
- Integrate and migrate
- Operate and improve
- Financial Services
- Greenlake Management Services
- Retire and sanitize
- IT Training and personal development

Other related services

[HPE Education Services](#) delivers a comprehensive range of services to support your people as they expand their skills required for a digital transformation. Consult your HPE Sales Representative or Authorized Channel Partner of choice for any additional questions and support options.

Defective Media Retention is optional and allows you to retain Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

HPE GREENLAKE

[HPE Greenlake](#) is HPE's market-leading IT as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model. HPE GreenLake delivers public cloud services and infrastructure for workloads on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please [explore them here](#).

Make the right purchase decision.
Contact our presales specialists.

[Find a partner](#)



Chat now (sales)



Call now



Buy now



Share now



Get updates



**Hewlett Packard
Enterprise**

© Copyright 2021 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Image may differ from the actual product
[PSN5096603USEN](#), September, 2021.