

iQ300

WM12N190GB

Automatic washing machine



A+++

iSensoric Washing Machine with iQDrive for highly effective and efficient laundry care.

- ✓ Intelligent and powerful iQdrive motor with 10-year warranty for highly effective and efficient laundry care.
- ✓ With the option speedPerfect, get perfect washing results in up to 65% less time.
- ✓ A+++ -10%: washes 10% more efficient than the requirement for energy efficiency class A+++.
- ✓ High-grade stainless steel drum for 1-7 kg loads.
- ✓ Outdoor / Impregnation programme for a gentle waterproofing of outdoor textiles.

Features

Technical Data



Built-in / Free-standing : Free-standing
 Door hinge : Left
 Color / Material body : White
 Length electrical supply cord (cm) : 210
 Height for building under : 850.00
 Height of the product (mm) : 848
 Dimensions of the product (mm) : 848 x 598 x 550
 Wheels : No
 Net weight (kg) : 68.0
 Drum volume (l) : 55
 Main colour of product : White
 Door Frame : silver-white
 Noise level washing (dB(A) re 1 pW) : 54
 Connection Rating (W) : 2300
 Current (A) : 10
 Voltage (V) : 220-240
 Frequency (Hz) : 50
 Cord Included : Yes
 Plug type : GB plug
 Length of drain hose (in) : 59.05
 Length of supply hose (in) : 59.05
 Appliance Dimensions (h x w x d) (inches) : x x
 Dimensions of the packed product (in) : 34.25 x 24.99 x 25.39
 Net weight (lbs) : 149
 Gross weight (lbs) : 151
 Length of drain hose : 150.00
 Length of supply hose : 150.00
 Gross weight (kg) : 68.0
 Connection Rating (W) : 2300
 Current (A) : 10
 Voltage (V) : 220-240
 Frequency (Hz) : 50
 Approval certificates : CE, VDE
 Water protection system : Multiple water protection
 Number of Options : 6
 Spin speed options : Variable
 Internal water heater included : No
 Digital countdown indicator : Yes
 Drying progress indicator : LED, LED-display



4 242003 765166

Optional accessories

WZ20490 Platform with pull-out
 WZ10130 Extension for cold water inlet /Aquastop
 WX975600 Floor securing component

iQ300

WM12N190GB

Automatic washing machine

Features	
<ul style="list-style-type: none">• iQdrive• iSensoric, Extraklasse <p>engine power and consumption</p> <ul style="list-style-type: none">• rated capacity: 7 kg• Energy Efficiency Class: A+++ -10%• 10% more economical (157kWh/year) than the standard value (174 kWh/year) of energy efficiency class A+++ in category 7 kg according to the EU-order 1061/2010• Energy consumption 157 kWh per year, based on 220 standard washing cycles for cotton programmes at 60°C and 40°C at full and partial load, and the consumption of the low power modes. Actual energy consumption will depend on how the appliance is used.• energy consumption of the standard 60 °C cotton programme 0.85 kWh at full load and 0.69 kWh at partial load and of the standard 40 °C cotton programme 0.51 kWh at partial load• weighted power consumption off-mode / left-on mode: 0.12 W / 0.5 W• Water consumption 9020 litres per year, based on 220 standard washing cycles for cotton programmes at 60°C and 40°C at full and partial load. Actual water consumption will depend on how the appliance is used.• spin-drying efficiency class: B• max. spin speed: 1200 rpm max. remaining moisture: 53 %• Indication that cotton 60° Eco and cotton Eco 40° are the standard washing programmes to which the information in the label and the fiche relates, that these programmes are suitable to clean normally soiled cotton laundry and that they are the most efficient programmes in terms of combined energy and water consumption. The actual temperature may vary with this combination from the specified program temperature. Washing times will be extended for the benefit of lower energy consumption. Washing effect A is always guaranteed in the process.• programme time of the standard 60 °C cotton programme 200 min at full load and 200 min at partial load and of the standard 40 °C cotton programme 200 min at partial load• Duration of the left-on mode: 15 min• Noise level washing in standard 60° cotton programme at full load in dB (A) re 1 pW: 54• Noise level spinning at standard 60°C cotton programme at full loading in dB (A) re 1 pW: 74 <p>programmes</p> <ul style="list-style-type: none">• Special programmes: intensive+quick, dark wash, shirts/blouses, outdoor/waterproofing, quick/mixture, hygiene, Quick 15'/30', Duvet, Drum Clean (with reminder), rinse/spin/drain, wool, delicates/silk	<p>options</p> <ul style="list-style-type: none">• varioPerfect: time- or energy optimized programs with perfect performance• touchControl buttons: Start delay, Temperature, start/pause with reload function, ecoPerfect/speedPerfect, Water & Rinse Plus, Spin speed reduction/Rinse hold <p>comfort and safety</p> <ul style="list-style-type: none">• Drum volume: 55 l• Multiple water protection• Large display for programme progress indication, temperature, spin speed, remaining time, 24 h end time delay and load recommendation• Fully electronic control dial for all wash- and special programs• Aquatronic wash system• waterPerfect: automatic load adjustment system• iQdrive: most energy-saving and quietest motortechnologie• 10 years guaranty on iQdrive• anti-vibration Design: more stability and quietness• Foam detection system• Unbalanced load detection• Overdosage indication• buzzer at end of program• Childproof• Divider for Liquid Detergent• 30 cm-porthole, silver-white with 180° openingdoor• Metal door closing hook• comfort lock <p>technical information</p> <ul style="list-style-type: none">• slide-under at height of 85 cm• Dimensions (H x W x D): 84.8 cm x 59.8 cm x 55.0 cm