

IPM-722

1MP HD Wi-Fi Network Small IR Bullet Camera

Features

- 1/4" 1Megapixel progressive scan CMOS
- H.264 & MJPEG dual-stream encoding
- Max 25/30fps@720P(1280×720)
- DWDR, Day/Night(ICR), 3DNR, AWB, AGC, BLC
- Multiple network monitoring: Web viewer, CMS(DSS/PSS) & DMSS
- 3.6mm fixed lens (6mm optional)
- Max. IR LEDs Length 30m
- Wi-Fi support
- IP66, DC12V

Technical Specifications

Model		DH-IPC-HFW1000S-W
Camera		
Image Sensor		1/4" 1Megapixel progressive scan CMOS
Effective Pixels		1280(H)x720(V)
Scanning System		Progressive
Electronic Shutter Speed		Auto/Manual 1/3(4)~1/100000s
Min. Illumination		Color: 0. 1Lux/F1.8 ; 0Lux (IR on)
S/N Ratio		More than 50dB
Video Output		N/A
Camera Features		
Max. IR LEDs Length		30m
Day/Night		Auto(ICR) / Color / B/W
Backlight Compensation		BLC /HLC /DWDR
White Balance		Auto/Manual
Gain Control		Auto/Manual
Noise Reduction		3D
Privacy Masking		Up to 4 areas
Lens		
Focal Length		3.6mm (6mm optional)
Max Aperture		F1.8(F1.8)
Focus Control		Manual
Angle of View		H: 59°(37°)
Lens Type		Fixed lens
Mount Type		Board-in Type
Video		
Compression		H.264B/H.264/MJPEG
Resolution		720P(1280×720)/VGA(640×480)
Frame Rate	Main Stream	720P(1 ~ 25/30fps)
	Sub Stream	D1/CIF(1 ~ 25/30fps)
Bit Rate		H.264: 448K ~ 8192Kbps

IPM-722

Audio	
Compression	N/A
Interface	N/A
Network	
Ethernet	RJ-45 (10/100Base-T)
Wi-Fi	Wi-Fi(IEEE802.11b/g/n)
Wi-Fi Range	50m(open field)
Protocol	IPv4/IPv6, HTTP, HTTPS, TCP/IP, UDP, UPnP, ICMP, IGMP, RTSP, RTP, SMTP, NTP, DHCP, DNS, PPPOE, DDNS, FTP, IP Filter, QoS
Compatibility	ONVIF, CGI
Max. User Access	20 users
Smart Phone	iPhone, iPad, Android, Windows Phone
Auxiliary Interface	
Memory Slot	N/A
RS485	N/A
Alarm	N/A
PIR Sensor Range	N/A
General	
Power Supply	DC12V
Power Consumption	< 6.5W
Working Environment	-30°C~+50°C, Less than 95%RH
Ingress Protection	IP66
Vandal Resistance	N/A
Dimensions	Φ70mm×66mm×155mm
Weight	0.42Kg

Dimensions (mm)

