


4MP Dome IP Camera with Junction Box

O4D1

2.8mm fixed lens, white housing

Features

- Supports up to 4MP @ 30fps in 16:9 widescreen format
- Built-in standard PoE (IEEE 802.3af)
- Adaptive IR LEDs reduce IR saturation
- IR Range: 98' (depending on scene reflection)
- True Day/Night operation (IR cut filter)
- True WDR (wide dynamic range) operation
- 2-way audio communication
- Micro SD card slot for edge recording (card not included)
- Sensor input and relay output
- IP67 compliant, weather resistant
- IK10 compliant, vandal resistant
- Junction box included
- Conformant with ONVIF Profile S
- 5 year warranty



Included Junction Box (O2VLJBD)

Camera Specifications

Image Sensor	Progressive scan 1/3" CMOS, 4MP
Maximum Resolution	2688 x 1520
Minimum Illumination	F2.0, 0.08 lux color; 0 lux (IR LED on)
IR Range	98' (depending on scene reflection)
White Balance	Auto / Presets / Manual
Compensation	WDR (120dB)/BLC/HLC
Day/Night	IR cut filter
Exposure Control	Digital slow shutter
Electronic Shutter Speed	1/3 ~ 1/100000 sec
DNR	3D

Video Specifications

Supported Resolutions	2688x1520 / 2560 x 1440 / 1920x1080 / 1280x720 @ 30fps
-----------------------	--

Compression	H.264, MJPEG
Bitrate Control	VBR, CBR
Multiple Streaming	3 streams

Audio Specifications

Mono Input	G.711
Mono Output	G.711

External Terminal Specifications

Ethernet	10/100 Mbps
Alarm	1 sensor input, 1 relay output
Video	N/A
Audio	1 mic in, 1 line out (RCA)
Storage	Micro SD slot (128GB max)
Power	DC jack

Network Specifications

Protocols	IPv4, IPv6, TCP, UDP, RTCP, RTP, RTSP, HTTP, HTTPS, SMTP, SNMP, UPnP, FTP, DHCP, Bonjour, QoS, 802.1x
DDNS support	Speco DDNS (free of charge)

Network Specifications (continued)

Security	User ID & Password protection, IP address filtering
User Access	20 simultaneous users (performance may vary depending on resolution and number of connections)

System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Motion detection, audio detection, face detection
Alarm Triggers	Analytics, network loss, sensor input
Alarm Events	FTP video/image file upload, email image upload, micro SD card recording, relay out
Video Buffer	Configurable pre-record & post-record
Image Settings	Privacy mask

Client Specifications

Web Browser Support	Windows (Internet Explorer 11)
PC Application	SecureGuard®
Mobile	SecureGuard® Mobile (iPhone® and Android™)

Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
Power Consumption	5W max.
Operating Temperature	-22°F - 140°F
Operating Humidity	0% - 95% RH
Unit Dimensions	4.3" (Dia.) x 3.2" (H)
Unit Weight	1 lb.
Certifications	FCC, RoHS, UL

Optional Accessories



O2VLWM
Dome Wall
Mount



POEINJ
12.95W
PoE Injector



PSW5
12VDC
Power Supply

**Visit www.specotech.com for latest ONVIF® support. ONVIF is a trademark of Onvif, Inc. iPhone and iPad are trademarks of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 2/14/17