


EB-2155W

DATASHEET



Offering excellent brightness to deliver perfect presentations with Gesture Presenter and intuitive easy to use features.

Our super-bright new business projector offers an outstanding brightness of 5,000 lumens. The EB-2155W is designed to project a scalable image size of up to 300 inches, and offers connectivity options such as dual HDMI and stream and share wireless features using Epson's Multi-PC projection or the Epson iProjection App.

Up to 300-inch display and outstanding quality

Full HD resolution combined with Epson's 3LCD technology ensures high-quality content has more vivid colours and brighter images. HDMI connectivity guarantees sharper and clearer presentation delivered on a scalable image size of up to 300 inches.

Simple setup and connectivity

The EB-2155W offers stream and share wireless LAN connectivity using Epson's Multi-PC projection or the Epson iProjection App, as well as two HDMI connections. Setup is easy too, thanks to features including auto-power-on, focus help, keystone correction and screen fit - allowing the user to deliver presentations quickly and effectively.

Keep costs down

Project for longer with improved reliability and a longer lamp life of up to 10,000 hours in eco mode.

Home screen

The home screen offers quick and easy access to a variety of useful functions, such as connection sources. Wireless connections can also be made easily using the information on screen.

Gesture Presenter

Change slides by simply moving your hand, making even smarter presentations a reality by liberating the user from their remote control or mouse.

Value add flexibility

The Multi-PC projection software bundled with the EB-2155W makes it possible to connect with up to 50 computers and partition the screen for split-screen projection capability - offering far better cost-effectiveness and flexibility than a flat-panel display.

KEY FEATURES

- **Up to 300-inch display and great quality**
HD-ready WXGA resolution with Epson's 3LCD technology
- **Outstanding 5,000-lumen brightness**
Project bold, colourful images even in bright rooms
- **Stream and share connectivity**
Including wireless connectivity and dual HDMI
- **Home screen and split-screen**
Quick and easy access to a variety of useful functions
- **Gesture Presenter**
Intuitively use gestures to control the projector



EPSON
WORLD LEADER
IN PROJECTORS

Source: Futuresource Consulting Ltd.

EPSON®
EXCEED YOUR VISION

PRODUCT SPECIFICATIONS

TECHNOLOGY

| | |
|-------------------|---|
| Projection System | 3LCD Technology, RGB liquid crystal shutter |
| LCD Panel | 0,59 inch with D8 |

IMAGE

| | |
|---------------------|---|
| Colour Light Output | 5.000 lumen- 3.600 lumen (economy) |
| White Light Output | 5.000 lumen - 3.600 lumen (economy) |
| Resolution | WXGA, 1280 x 800, 16:10 |
| Contrast Ratio | 15.000 : 1 |
| Lamp | 300 W, 5.000 h durability, 10.000 h durability (economy mode) |
| Keystone Correction | Auto vertical: ± 30 °, Auto horizontal ± 20 ° |
| Colour Reproduction | Upto 1.07 billion colours |

OPTICAL

| | |
|--------------------------|--------------------------|
| Projection Ratio | 1,38 - 2,24:1 |
| Zoom | Digital, Factor: 1 - 1,6 |
| Image Size | 29 inches - 280 inches |
| Projection Distance Wide | 0,9 m (29 inch screen) |
| Projection Distance Tele | 8,5 m (280 inch screen) |
| Projection Lens F Number | 1,51 - 1,99 |
| Focal Distance | 18,2 mm - 29,2 mm |
| Focus | Manual |
| Offset | 10 : 1 |

CONNECTIVITY

| | |
|-----------------------|---|
| USB Display Function | 3 in 1: Image / Mouse / Sound |
| Interfaces | USB 2.0 Type A, USB 2.0 Type B, RS-232C, Ethernet interface (100 Base-TX / 10 Base-T), Gigabit ethernet interface, WLAN, Wireless LAN IEEE 802.11b/g/n, VGA in (2x), VGA out, HDMI in (2x), Composite in, RGB in (2x), RGB out, MHL, Stereo mini jack audio out, Stereo mini jack audio in (2x) |
| Epson iProjection App | Ad-Hoc / Infrastructure |

ADVANCED FEATURES

| | |
|--------------------|--|
| Security | Kensington lock, Control panel lock, Password lock, Padlock, Security cable hole, Wireless LAN unit lock, Wireless LAN security, Password protection |
| Features | AV Mute Slide, Automatic input selection, Automatic keystone correction, Built-in speaker, CEC compatible, Direct Power on/off, Document Camera Compatible, Screen Fit, Freeze image, Gesture Presenter, Home Screen, Instant on/off, JPEG Viewer, Long lamp life, MHL audio/video interface, Network administration, OSD copy function, PC Free, iProjection App for Chromebook, Quick Corner, Slide show, Split-Screen-Function, Wireless LAN capable, iProjection App |
| Video Colour Modes | Blackboard, Dynamic, Photo, Presentation, DICOM SIM |

GENERAL

| | |
|--------------------|---|
| Energy Use | 405 W, 323 W (economy), 0,5 W (standby) |
| Product dimensions | 377 x 291 x 101 mm (Width x Depth x Height) |
| Product weight | 4,3 kg |
| Noise Level | Normal: 39 dB (A) - Economy: 29 dB (A) |
| Included Software | EasyMP Monitor, EasyMP Multi PC Projection |

OTHER

| | |
|----------|--|
| Warranty | 36 months Carry in or 8.000 h, Lamp: 12 months or 1.000 h (whichever comes first) Optional warranty extension available |
|----------|--|

EB-2155W

WHAT'S IN THE BOX

- VGA cable
- Power cable
- Remote control incl. batteries
- Software (CD)
- User Manual (CD-ROM)
- Wireless LAN unit
- Main unit

EPSON®

OPTIONAL ACCESSORIES

EB-2155W

- Air Filter - ELPAF41
V13H134A41
- Wireless LAN Adapter - ELPAP10
V12H731P01
- Quick Wireless Connect USB key - ELPAP09
V12H005M09
- Soft Carry Case - ELPKS68
V12H001K68
- Ceiling Mount (White) - ELPMB23
V12H003B23
- Ceiling Pipe (450mm) - ELPFP13
V12H003P13
- Ceiling Pipe (700mm) - ELPFP14
V12H003P14
- Lamp - ELPLP95 - EB-2xxx/5xxx
V13H010L95

LOGISTICS INFORMATION

| | |
|-------------------|---------------|
| SKU | V11H818040 |
| EAN code | 8715946628547 |
| Country of Origin | China |

Epson Deutschland GmbH
Otto-Hahn-Str. 4
D-40670 Meerbusch
Info-Line: 02159 92 79 500
Telefax: +49 (0) 2159/538-3000
www.epson.de

Epson in Österreich
Info-Line: 01 253 49 78 333
www.epson.at
Epson in der Schweiz
Info-Line: 022 592 7923
www.epson.ch

Alle Marken und eingetragenen Warenzeichen sind das Eigentum der Seiko Epson Corporation oder der jeweiligen Rechteinhaber.
Diese Produktinformationen können ohne vorherige Ankündigung geändert werden.

1. - iProjection App available on Android and iOS devices

EPSON®