


Serie | 4 Dishwashers

SMS50C22GB white
ActiveWater Dishwasher 60cm
Freestanding,



A++



Technical Data	
Cleaning performance :	A
Water consumption (l) :	9.5
Construction type :	Free-standing
Removable work top :	Yes
Door panel options :	Not possible
Height of removable worktop (mm) :	815
Height of the product (mm) :	845
Adjustable feet :	Yes - front only
Maximum adjustability feet (mm) :	20
Adjustable plinth :	No
Net weight (kg) :	46.0
Gross weight (kg) :	48.0
Connection rating (W) :	2400
Current (A) :	13
Voltage (V) :	220-240
Frequency (Hz) :	60; 50
Length of electrical supply cord (cm) :	175
Plug type :	GB plug
Length inlet hose (cm) :	165
Length outlet hose (cm) :	190.0
Hidden heating element :	Yes
:	Childlock appliance
Water softener (kWh) :	Yes
Top basket type :	low
Adjustable upper basket :	Single
Upper rack cup shelf :	2
Bottom basket type :	low
3rd Rack :	None
Silverware Basket :	Standard
Optional accessories :	
SGZ1010, SMZ2014, SMZ5000, SMZ5001, SMZ5002, SMZ5300	
Included accessories 2 :	baking-sheet spray head grey
Number of place settings :	12
Color / Material panel :	White
Color / Material body :	White
Color / Material top :	White
Brand :	Bosch
Product name / Commercial code :	SMS50C22GB
Number of place settings :	12
Energy efficiency class - NEW (2010/30/EC) :	A++
Energy consumption annual (kWh/annum) - NEW (2010/30/EC) :	258
Energy consumption (kWh) :	0.90
Power consumption in left-on mode (W) - NEW (2010/30/EC) :	0.10
Power consumption in off-mode (W) - NEW (2010/30/EC) :	0.10
Water consumption annual (l/annum) - NEW (2010/30/EC) :	2660
Drying performance :	A
Reference programme :	Eco
Total cycle time of reference programme (min) :	210
Duration of the left-on mode - NEW (2012/30/EC) (min) :	0
Noise level (dB(A) re 1 pW) :	48
Installation type :	Built-under
Panel ready :	No
Connection rating (W) :	2400
Current (A) :	13
Voltage (V) :	220-240
Frequency (Hz) :	60; 50
Energy Star Qualified :	No
NSF certified :	No
Plug type :	GB plug
Required cutout/niche size for installation (in) :	x x
Dimensions of the packed product (in) :	35.43 x 26.37 x 26.77
Net weight (lbs) :	102
Gross weight (lbs) :	105
Tub material :	Stainless steel

Serie | 4 Dishwashers

SMS50C22GB white **ActiveWater Dishwasher 60cm** **Freestanding,**

Performance

- Energy Efficiency Class: A++
- Capacity: 12 place settings
- Energy consumption in Eco 50 programme: 258 kwh per year, based on 280 standard cleaning cycles
- Water consumption in Eco 50 programme: 2660 litres per year, based on 280 standard cleaning cycles
- Programme time in Eco 50 programme: 210 minutes
- A rated performance for washing and A for drying
- Noise level dB (A) re 1pW: 48 dB
- Energy consumption in Eco 50 programme:
- Power consumption off-mode / left-on mode: 0.1 W / 0.1 W
- Duration of the left-on mode: 0 minutes
- Water consumption in Eco 50 programme: 9.5 litres

Programmes/functions

- 5 programmes:
Intensive 70 °C, Normal 65 °C, Eco 50 °C,
Quick Wash 45 °C, Pre Rinse
- 4 temperatures

Flexible design elements

- Vario basket system
- Height adjustable top basket when empty
- Silver baskets
- 2 foldable plate racks in bottom basket
- 2 foldable cup shelves in top basket

Innovations and technology

- ActiveWater hydraulic water system
- EcoSilence BLDC drive
- DosageAssist detergent dispenser
- Automatic detergent detection
- Load Sensor
- AquaMix - Glass protection system
- Leak protection system
- Heat exchanger - Hygienic and efficient drying
- Curved spray arms - Optimum water distribution

Design features

- water inlet indicator
- Control buttons on front of fascia
- Stainless steel interior
- Electronic time delay: 1-24 hours with remaining programme time indicator (min), water inlet indicator
- Colour of indicators: Red LED indicators
- LED salt refill indicator, LED rinse aid refill indicator
- Alternating spray arms
- Child safety - Childproof door lock
- Large item spray head
- Self-cleaning filter system with 3 piece corrugated filter
- Dimensions (HxWxD): 84.5 x 60 x 60cm
- Efficiency information relates to the Eco 50 programme. This programme is suitable for cleaning normally soiled tableware and is the most efficient programme in terms of combined energy and water consumption.