

FROST FREE AMERICAN
FRIDGE FREEZER
FREE STANDING
91cm WIDE
178.6cm HIGH



FSN535A20D

Hisense

Capacity :

Total gross capacity	610 litre
Total net capacity	535 litre
Fridge net capacity	367 litre
Freezer net capacity	168 litre

Dimensions :

Width (mm)	910
Height (mm)	1786.5
Depth (mm)	743
Packed product (W/H/D)	979x1877x777
Net weight (Kg)	110.0
Gross weight (Kg)	121.0
Container load (HC)	48

Energy label info / Performance :

Energy efficiency class	A+
Energy consumption / day	1.2 kWh
Energy consumption / year	438 kWh
Climate class	SN,N,ST,T
Noise level	42 db(A)
Freezer star rating	4
Freezing capacity in 24 hours	13 kg
Power off storage time	8 hours

Features :

Refrigerator :

Defrost	Frost Free
Fridge door balconies	5
Fridge adjustable shelves	4
Crispers	2
Glass shelf over crispers	Yes
Chrome Wine rack	Yes
Internal light	LED

Freezer :

Defrost	Frost Free
Freezer door balconies	3
Freezer drawers	2
Freezer adjustable Shelves	4
Water & ice dispenser tank	Yes
Internal light	LED

General :

Electronic temp control	Yes
Control display	LED
Multi Airflow	Yes
Plumbed water & ice dispenser	Yes
Inverter compressor	Yes
NANO freshness technology	Yes
Open door alarm	Yes
Holiday setting	Yes
Energy saving	Yes
Super cool	Yes
Super freeze	Yes
Adjustable feet	Yes

Basic Information :

Model Number	FSN535A20D
EAN	6921727007223
Product type	Frost Free
Built-in / Free standing	Free standing
Colour / Material - body	Grey/Steel
Colour / Material - door	SSL/Steel
Voltage	220 – 240 V
Frequency	50 Hz
Compressors	1