



by Schneider Electric


# In-Line Current Meter AP7152B

## Overview

The APC by Schneider Electric In-Line Current Meter monitors current to devices in the data center. The Current Meter has a sensor that measures the current that it and its attached devices use. The Current Meter can be monitored through Web, Telnet, SNMP, SSH, or StruxureWare Data Center Expert<sup>®</sup> interfaces.

**Digital display:** A digital display shows aggregate current being used by the Current Meter and its attached devices.

**Power cords:** Each 0.91 m (3 ft) power cord terminates with an IEC 309, 16-A, 2P+PE connector.



# Specifications

<b>Electrical</b>	
Input connector	IEC 309, 16 A, 2P+PE
Nominal input voltage	230 VAC
Input frequency	50/60 Hz
Acceptable input voltage	± 10% of nominal
Maximum input current (phase)	16 A
Output connector	IEC 309, 16 A, 2P+PE
Maximum output current (phase)	16 A
Nominal output voltage	230 VAC
Cord length	0.91 m (3.00 ft)
<b>Physical</b>	
Dimensions (H x W x D)	4.39 x 17.78 x 13.97 cm (1.73 x 7.00 x 5.50 in)
Shipping dimensions (H x W x D)	24.63 x 33.02 x 18.54 cm (9.70 x 13.00 x 7.30 in)
Weight	1.51 kg (4.05 lb)
Shipping weight	2.03 kg (5.45 lb)
<b>Environmental</b>	
Elevation (above MSL)	
Operating	3000 m (10,000 ft)
Storage	15 000 m (50,000 ft)
Temperature	
Operating	–5 to 45°C (23 to 113°F)
Storage	–25 to 65°C (–13 to 149°F)
Humidity	
Operating/Storage	5 to 95%, non-condensing
<b>Compliance</b>	
Safety	VDE, EAC, CE
EMC	EN 55022, EN 55024, VCCI, ICES-003, FCC Part 15, AS/NZS CISPR22

Customer support and warranty information are available at [www.apc.com](http://www.apc.com).

© 2016 APC by Schneider Electric. All rights reserved.

990-9949-001  
10/2016