



Key Features & Benefits

- 7kg Load
- Glass Door
- 4 Sensor Dry Programmes
- Delicate 'Wool Finish' Cycle
- 9hrs Delay Start
- Timed Drying Options - 150
- 'Anti Crease' Cycle
- Relax Programme
- Rapid 40 Programme
- Highly Efficient Reverse Action
- 'Empty Water' Indicator
- 'Filter Care' Indicator
- C Energy
- 85x60x60cm

FEATURES

Load Size	7
Sensor Dry System	Yes (up to 4)
LED Display	No
Countdown Display	No
Reverse Action Drying	Yes
Easy-empty top condenser drawer	No
Delay Start	Yes (3, 6, 9 hrs)
Floor level condenser reservoir	No
Glass Door	No
Large door for easy opening	Yes
Digital Display	No
Unique AquaVision Technology	No

BUTTONS / INDICATORS

On / Off	Yes
Start / Reset	Yes
Delay Start	Yes
Acrylic / Synthetic (Low heat)	Yes
'Empty Water' Indicator	No
'Filter Care' Indicator	Yes
'Memo' Option	No

PROGRAMMES

Delay Start	Yes
Delicate Wool Finish	Yes
Fast Iron	Yes
Refresh Cycle	yes
Timed Drying minutes (maximum setting)	150
Heat Settings	2
4 Levels of Sensor Drying:	Yes
Relax Programme	Yes
Rapid 40 Programme	Yes
Shirts Programme	No
Mix & Dry Programme	No
All towels, Store Dry, Hang Dry, Iron Dry	Bone Dry, Extra Dry, Cupboard Dry, Iron Dry

OTHER INFORMATION

Colour	White
Automatic safety door (stop drum on opening)	Yes

TECHNICAL SPECIFICATION

Energy Efficiency	C Energy
Annual Energy Consumption	580
Electrical supply (volts)	230
Rated loads (watts)	2300
Weight (kg) (packed)	31
Weight (kg) (unpacked)	29
Dimensions (HxWxD) cm (packed)	90x65x62
Dimensions (HxWxD) cm (unpacked)	85x60x60
Noise(dba)	67