

Cisco 4000 Series Integrated Services Routers

Cisco® 4000 Series Integrated Services Routers (ISRs) form an intelligent WAN platform that delivers the performance, security, and convergence capabilities that today's branch offices need.

Product Overview

The Cisco 4000 Series Integrated Services Routers (ISR) revolutionize WAN communications in the enterprise branch. With new levels of built-in intelligent network capabilities and convergence, the routers specifically address the growing need for application-aware networking in distributed enterprise sites. These locations tend to have lean IT resources. But they often also have a growing need for direct communication with both private data centers and public clouds across diverse links, including Multiprotocol Label Switching (MPLS) VPNs and the Internet.

The Cisco 4000 Series contains sixplatforms: the 4451, 4431, 4351, 4331, 4321 and 4221 ISRs (Figure 1).

Figure 1. Cisco 4000 Series Integrated Services Routers



Features and Benefits

Cisco 4000 Series ISRs provide you with Cisco Intelligent WAN (IWAN) software features and a converged branch infrastructure. Along with superior throughput, these capabilities form the building blocks of next-generation branch-office WAN solutions.

Cisco Intelligent WAN (IWAN)

Cisco IWAN is a set of intelligent software services that allow you to reliably and securely connect users, devices, and branch office locations across a diverse set of WAN transport links. IWAN-enabled routers like the 4000 Series dynamically route traffic across the "best" link based on up-to-the-minute application and network conditions for great application experiences. You get tight control over application performance, bandwidth usage, data privacy, and availability of your WAN links—control that you need as your branches conduct greater volumes of mission-critical business.

Cisco Converged Branch Infrastructure

The Cisco 4000 Series ISRs consolidate many must-have IT functions, including network, compute, and storage resources. The high-performance, integrated routers run multiple concurrent IWAN services, including encryption, traffic management, and WAN optimization, without slowing your data throughput. And you can activate new services on demand through a simple licensing change.

Table 1 breaks out many of the features and benefits of the Cisco 4000 Series that create an intelligent WAN and a converged branch infrastructure.

Table 1. Cisco 4000 Series ISR General Feature Highlights

Business Requirement(s)	Feature/Solution
Performance • Throughput • Service reliability	 Concurrent software services at speeds up to 2 Gbps. Backplane architecture supports high-bandwidth module-to-module communication at speeds up to 10 Gbps. A distributed multicore architecture with the industry's first internal services plane. Remote installation of application-aware services, which run identically to their counterparts in dedicated appliances.
Lower WAN expenditures	Embedded IWAN solution for creating lower-cost, business-class Internet connections.
Pay-as-you-grow Performance upgrade model Investment protection CapEx budget management	Router capacity can be increased with a remote performance-on-demand license upgrade (no hardware upgrade) for exceptional savings.
Superior and secure user application experiences	 ISR-AX "Application Experience" software bundle with advanced routing and network monitoring services. Dy namic Multipoint VPN (DMVPN), zone-based firewalls, intrusion prevention (Snort and Umbrella Branch) and content management using Cisco Cloud Web Security and OpenDNS protecting data, providing authentication credentials, and enabling transmissions that are not backhauled through the data center. Secure boot feature performs hardware-based authentication of the bootloader software to prevent malicious or unintended software from booting on the system. Code signing verifies digital signatures of executables prior to loading to prevent execution of altered or corrupted code. Hardware authentication protects against hardware counterfeiting by using an on-board tamper-proof silicon, including field replaceable modules. If authentication fails, the module is not allowed to boot.
IT consolidation, space savings, and improved total cost of ownership (TCO)	Single converged branch platform integrates routing, switching, virtual server, storage, security, unified communications, WAN optimization, and performance management tools.
Business continuity and increased resiliency	 4400 Series models (4451 and 4431 ISRs) support dual integrated power supplies for backup. The entire 4000 Series supports optional power supply capable of delivering additional PoE power to endpoints. Defined models provide for a DC power supply. Modular network interfaces with diverse connection options for load-balancing and network resiliency. Modular interfaces with online removal and insertion (OIR) for module upgrades without network disruption. Cisco Unified Survivable Remote Site Telephony (SRST), which serves as a resiliency complement to Cisco Hosted Collaboration Solution (HCS), a Cisco cloud-based UC service. Support for multiple, diverse access links: T1/E1, T3/E3, Serial, xDSL, Gigabit and Ten-Gigabit Ethernet.
Lower telephony costs with VoIP and rich media experiences	High-performance analog/digital gateway, allowing VoIP over less expensive Session Initiation Protocol (SIP) trunks. Integrated IP PBX (Cisco Unified Communications Express) and Session Border Controller (Cisco Unified Border Element, or CUBE).
Easier manageability and support	 Single, universal software image for all features and performance-on-demand licensing flexibility. No additional services and support needed for compute and storage. Supported by Cisco and third-party management tools, with programmability and automation.

Platform Architecture

Table 2 lists the primary hardware architectural features and benefits of the Cisco 4000 Series. The routers run modular Cisco IOS® XE Software, widely deployed in the world's most demanding networks. The software's comprehensive portfolio of services spans multiple technology areas, including security, WAN optimization, app and network quality of service (QoS), and embedded management.

Table 2. Architectural Highlights

Architectural Features	Benefits/Description
Multicore processors	 High-performance multicore processors support high-speed WAN connections. The data plane uses an emulated Flow Processor (FP) that delivers application-specific integrated circuit (ASIC)-like performance that does not degrade as services are added.
Embedded IP Security (IPsec) VPN hardware acceleration	 Increases scalability. When combined with an optional Cisco IOS XE Software Security license, enables WAN link security and VPN services.
Integrated Gigabit Ethernet	• The Cisco 4000 Series provides up to four built-in 10/100/1000 Ethernet ports for WAN or LAN.
ports	 Based on the platform, some of the 10/100/1000 Ethernet ports can support Small Form-Factor Pluggable (SFP)-based connectivity in addition to RJ-45 connections, enabling fiber or copper connectivity.
	 Optionally, depending on the platform, up to 30W PoE+ can be enabled on two of the built-in front panel Gigabit Ethernet interfaces to provide power to external devices such as fourth-generation (4G) LTE routers.
	 An additional dedicated Gigabit Ethernet port is provided for device management.
USB-based console access	 A mini ty pe B USB console port1 supports management connectivity when traditional serial ports are not available.
	Traditional console and auxiliary ports are also available.
Optional integrated power supply for distribution of PoE	 An optional upgrade to the internal power supply provides inline power (802.3af-compliant PoE or 802.3at-compliant PoE+) to optional integrated switch modules.
	Redundant PoE conversion modules provide an additional layer of fault tolerance.
Optional integrated redundant power supply (RPS)	 For the 4400 Series, power redundancy is available by installing an optional integrated RPS for decreasing network downtime and protecting the network from power failures.
	Optional PoE boost mode increases total PoE capacity to up to 1000W.
Cisco Enhanced Services Module (SM-X)	 Each service-module slot offers high data-throughput capability of up to 10 Gbps toward the system and up to 1 Gbps to other module slots.
	Support for both single- and double-wide service modules provides flexibility in deployment options.
	An SM-X slot can be converted into a Network Interface Module (NIM) slot using an optional carrier card.
	 Service modules support online insertion and removal (OIR), avoiding network disruption when installing new or replacement modules.1
Cisco Network Interface	• Up to three integrated NIM slots on the Cisco 4000 Series allow for flexible configurations.
Modules (NIMs) ³	 Each NIM slot offers options of up to two 2-Gbps connections, one toward the route processor and one for direct module-to-module communication. The 4221 ISR has only one 1-Gbps connection to the route processor.
	NIMs support OIR.
	Special NIMs add support for solid-state drives (SSDs) and hard disk drives (HDDs).1
Cisco Integrated Services Card (ISC) slot on motherboard	 Integrated Services Card natively supports the new Cisco High-Density Packet Voice Digital Signal Processor Modules (PVDM4s), providing greater-density rich-media voice.
	Each Integrated Services Card slot connects to the system architecture through an up to 2-Gbps link.
	 Future modules can be hosted on the Integrated Services Card slot, improving system functions.
Flash memory support	 A single flash memory slot is available to support high-speed storage densities, upgradable to up to 32 GB. The 4221 ISR ships with a fixed 8 GB flash.
	Two USB type A 2.0 ports provide capabilities for convenient storage.1
DRAM	 For the 4400 Series ISRs, the default control-plane memory is 4 GB, upgradable to 16 GB to provide additional scalability for control-plane features. The default data-plane memory is 2 GB.
	 For the 4300 Series ISRs, the default memory is 4 GB, upgradable to 16 GB (only 8 GB for the 4321) to provide additional scalability.
	The 4200 Series comes with 4 GB fixed DRAM.

¹ Not supported on the 4221 model.

The 4221 model supports shared console and auxiliary ports.
 Unified Communications (UC) License and Unified Communications NIM's are not supported on the ISR4221.

Managing Your Cisco 4000 Series ISRs

The Cisco network management applications listed at the top of Table 3 are standalone products that can be purchased or downloaded to manage your Cisco network devices. The applications are built specifically for the different operational phases; select those that best fit your needs. Those management capabilities listed under the "Cisco IOS Software XE Embedded Management" heading are directly integrated into the routers' software operating system.

Table 3. Network Management Solutions

Operational Phase	Application	Description			
Device staging and configuration	WebUI	 A GUI-based device-management tool for Cisco IOS and Cisco IOS XE Software-based access routers. This tool simplifies routing, firewall, VPN, unified communications, and WAN and LAN configuration through easy-to-use wizards. 			
Network-wide deployment, configuration, monitoring, and troubleshooting	Cisco Prime [®] Inf rastructure	 Offers comprehensive lifecycle management of wired and wireless access, campus, and branch-office networks, rich visibility into end-user connectivity, and application performance assurance. Provides wired lifecycle functions such as inventory, configuration, and image management; automated deployment; compliance reporting; integrated best practices; and reporting. 			
Staging, deployment, and changes to configuration and image files	Cisco Configuration Engine	 A secure network management product that provides zero-touch image and configuration distribution through centralized, template-based management. 			
Context-aware security configuration and monitoring	Cisco Prime Security Manager	 Management tool for configuring and managing context-aware security. The application supports both single- and multi-device manager form factors. Provides the ability to write and enforce the granular context-aware security policies. 			
Cisco Wide Area Application Service (WAAS) management	Cisco WAAS Central Manager The management tool for the WAAS1 ^{,4} (WAN optimization and application acceleration) integrated service. It provides a centralized mechanism for configuring WAAS features, reporting, and monitoring.				
Cisco IOS XE Software Embedded Mar	nagement Capabili	ties			
Feature	Description				
Cisco IOS Embedded Event Manager	A distributed an	d customized approach to event detection and recovery.			
(EEM)	Offers the ability to monitor events and take informational, corrective, or any desired EEM action when the monitored events occur or when a threshold is reached.				
Cisco IOS XE IP Service-Level Agreements (IP SLAs)	Helps assure the performance of new business-critical IP applications as well as IP services that use data and voice in an IP network.				
SNMP, Remote Monitoring (RMON), syslog, NetFlow, IP Flow Information Export (IPFix)	Network monitor	oring and accounting tools.			

Product Specifications

Table 4 lists the general product specifications for the Cisco 4000 Series routers.

 Table 4.
 Specifications of Cisco 4000 Series Integrated Services Routers

Technical Specifications	Cisco 4451	Cisco 4431	Cisco 4351	Cisco 4331	Cisco 4321	Cisco 4221
Aggregate Throughput	1 Gbps to 2 Gbps	500 Mbps to 1 Gbps	200 Mbps to 400 Mbps	100 Mbps to 300 Mbps	50 Mbps to 100 Mbps	35 Mbps to 75 Mbps
Total onboard WAN or LAN 10/100/1000 ports	4	4	3	3	2	2

⁴ It is suggested to use AppNav with an external WAAS device for the 4221 model.

Technical Specifications	Cisco 4451	Cisco 4431	Cisco 4351	Cisco 4331	Cisco 4321	Cisco 4221
RJ-45-based ports	4	4	3	2	2	2
SFP-based ports	4	4	3	2	1	1
Enhanced service- module slots	2	0	2	1	0	0
Doublewide service-module slots	1 (assumes no singlewide SM-X modules installed)	0	1 (assumes no singlewide SM-X modules installed)	0	0	0
NIM slots	3	3	3	2	2	2
OIR (all I/O modules)	Yes	Yes	Yes	Yes	Yes	No
Onboard ISC slot	1	1	1	1	1	No
Default memory double-data-rate 3 (DDR3) error- correction-code (ECC) DRAM (Combined control/services/da ta planes)	NA	NA	4 GB	4 GB	4 GB	4 GB
Maximum memory DDR3 ECC DRAM (Combined control/services/da ta planes)	NA	NA	16 GB	16 GB	8 GB	4 GB
Default memory DDR3 ECC DRAM (data plane)	2 GB	2 GB	NA	NA	NA	NA
Maximum memory DDR3 ECC DRAM (data plane)	2 GB	2 GB	NA	NA	NA	NA
Default memory DDR3 ECC DRAM (control/services plane)	4 GB	4 GB	NA	NA	NA	NA
Maximum memory DDR3 ECC DRAM (control/services plane)	16 GB	16 GB	NA	NA	NA	NA
Default flash memory	8 GB	8 GB	4 GB	4 GB	4 GB	8 GB
Maximum flash memory	32 GB	32 GB	16 GB	16 GB	8 GB	8 GB
External USB 2.0 slots (type A)	2	2	2	1	1	1
USB console port - type B mini (up to 115.2 kbps)	1	1	1	1	1	0
Serial console port - RJ45 (up to 115.2 kbps)	1	1	1	1	1	1 (combo CON/AUX port)
Serial auxiliary port - RJ45 (up to 115.2 kbps)	1	1	1	1	1	1 (combo CON/AUX port)
Power-supply options	Internal: AC, DC (roadmap) and PoE	Internal: AC, DC, and PoE	Internal: AC, DC (roadmap) and PoE	Internal: AC and PoE	External: AC and PoE	External AC only
Redundant power supply	Internal: AC, DC (roadmap) and PoE	Internal: AC, DC, and PoE	N/A	N/A	N/A	NA

Technical	Cisco 4451	Cisco 4431	Cisco 4351	Cisco 4331	Cisco 4321	Cisco 4221
Specifications						
Power Specifications	s					
AC input voltage	100 to 240 VAC autoranging	100 to 240 VAC autoranging	100 to 240 VAC autoranging	100 to 240 VAC autoranging	100 to 240 VAC autoranging	100 to 240 VAC autoranging
AC input frequency	47 to 63 Hz	47 to 63 Hz	47 to 63 Hz	47 to 63 Hz	47 to 63 Hz	47 to 63 Hz
AC input current range, AC power supply (maximum)	7.1 to 3.0A	3 to 1.3A	7.1 to 3.0A	3 to 1.3A	1.5 to 0.6A	1.5 to 0.6A
AC input surge current	<50 A	60 A peak and less than 5 Arms per half cycle	60 A peak and less than 12 Arms per half cycle	60 A peak and less than 5 Arms per half cycle	90 A peak and less than 3 Arms per half cycle	90 A peak and less than 3 Arms per half cycle
Typical power (no modules) (watts)	158	65	48	42	36	24
Maximum power with AC power supply (watts)	450 (no PoE)	250 (no PoE)	430	250	125	90
Maximum power with PoE power supply (platform only) (watts)	1000 with PoE redundant 1450 with PoE boost no redundancy	500 with PoE redundant 1000 with PoE boost no redundancy	990	530	260	NA (no PoE support)
Maximum endpoint PoE power available from PoE power supply (watts)	500 W with optional redundancy	250 W with optional redundancy	500	250	120	NA (no PoE support)
Maximum endpoint PoE power capacity with PoE boost (watts)	950 W no redundancy	500 W no redundancy	N/A	N/A	N/A	NA (no PoE support)
Sizes and Weights						
Dimensions (H x W x D)	3.5 x 17.25 x 18.5 in (88.9 x 438.15 x 469.9 mm)	1.73 x 17.25 x 19.97 in (43.9 x 438.15 x 507.2 mm)	3.5 x 17.25 x 18.5 in (88.9 x 438.15 x 469.9 mm)	1.75 x 17.25 x 17.25 in (44.45 x 438.15 x 438.15 mm)	1.75 x 14.55 x 11.60 in (44.55 x 369.57 x 294.64 mm)	1.72 x 12.7 x 10 in (43.7 x 322.6 x 254 mm)
External Power Supply Dimensions (H x W x D)	N/A	N/A	N/A	N/A	2.95 x 1.18 x 6.10 in (75 x 30 x 155 mm)	37 x 73 x 152 mm (Phihong mfg PN: AA90U-120A-R) 36.5 x 67 x 155 mm (Delta mfg PN: ADP90GR BA)
Shipping Box Dimensions (H x W x D)	9.75 x 22.25 x 26 in (24.76 x 56.51 x 66.04 mm)	7.88 x 22.25 x 28.75 in (200.2 x 565.1 x 730.25 mm)	9.75 x 22.25 x 26 in (24.76 x 56.51 x 66.04 mm)	7.125 x 22.75 x 22.5 in (180.98 x 577.85 x 571.5 mm)	7.0 x 21.5 x 16.125 in (177.8 x 546.1 x 409.6 mm)	4.13 x 18.25 x 12.94 in (104.9 x 463.6 x 328.7 mm)
Rack height	2 rack units (2RU)	1 rack units (1RU)	2 rack units (2RU)	1 rack unit (1RU)	1 rack unit (1RU)	1 rack unit (1RU)
Rack-mount 19in. (48.3 cm) EIA	Included	Included	Included	Included	Included	Optional
Rack-mount 23in. (58.4 cm) EIA	Optional	Optional	Optional	Optional	N/A	NA
Wall-mount	No	Yes	No	Yes	Mounting holes under chassis	Yes
Weight with 1, 450- WAC power supply (no modules)	28.8 lb (13.1 kg)	N/A	28.8 lb (13.1 kg)	N/A	N/A	NA
Weight with 1 1,000-WAC power supply+1 PoE power module (no other modules)	30.6 lb (13.9 kg)	N/A	29.0 lb (13.2 kg)	N/A	N/A	NA

Technical	Cisco 4451	Cisco 4431	Cisco 4351	Cisco 4331	Cisco 4321	Cisco 4221
Specifications						
Weight with AC PS (no modules)	N/A	18.5 lb (8.4 kg)	N/A	13.5 lb (6.2 kg)	7.7 lb (3.5 kg) + 1.2 lb (0.66 kg) external PS	7.1 lb (3.22 kg)
Weight with AC PS with POE (no modules)	N/A	18.6 lb (8.4 kg)	N/A	14.1 lb (6.4 kg)	N/A	NA
Typical weight (fully loaded with modules)	42.7 lb (19.4 kg)	22.4 lb (10.2 kg)	37.7 lb (17.1 kg)	16.1 lb (7.3 kg)	9.14 lb (4.2 kg) + 1.2 lb (0.66 kg) external PS	8.11 lb (3.68 kg)
Packaging Weight	6.4 lb (2.9 kg)	5.9 lb (2.7 kg)	6.4 lb (2.9 kg)	4.6 lb (2.1 kg)	2.2 lb (1 kg)	1.28 lb (0.58 kg)
Airflow	I/O side to bezel side	Right I/O side to Left I/O side	I/O side to bezel side			
MTBF (Hours)	480770	512970	566310	587250	593270	593270
Environmental Spec	ifications					
Operating Condition	ıs					
Temperature	32º to 104ºF (0º to 40ºC)	32º to 104ºF (0º to 40ºC)	32º to 104ºF (0º to 40ºC)	32° to 104°F (0° to 40°C)	32° to 104°F (0° to 40°C)	32º to 104ºF (0º to 40ºC)
Altitude	0 - 6,560 ft.	0 – 6,560 ft.	0 - 6,560 ft.			
(China)	(0 – 2,000 m)					
Atitude (Rest of the world)	0 - 10,000 ft. (0 - 3,050 m)					
Relative humidity	5% to 85%					
Short-term humidity	5% to 90%, not to exceed 0.024 kg water/kg of dry air	5% to 90%, not to exceed 0.024 kg water/kg of dry air	5% to 90%, not to exceed 0.024 kg water/kg of dry air	5% to 90%, not to exceed 0.024 kg water/kg of dry air	5% to 90%, not to exceed 0.024 kg water/kg of dry air	5% to 90%, not to exceed 0.024 kg water/kg of dry air
Acoustics: Sound pressure (Typical/maximum)	50.6/73.1 dBA	54.3/79.1 dBA	50.6/73.1 dBA	52.8/74.8 dBA	24.2/51.9 dBA	28.5/53 dBA
Acoustics: Sound power (Typical/maximum)	58.2/78.8 dBA	57.2/80.8 dBA	58.2/78.8 dBA	61.2/81.6 dBA	31.9/59.9 dBA	41/68 dBA
Nonoperating Cond	itions					
Temperature	-40° to 158°F (-40° to 70°C)					
Relative humidity	5% to 95%					
Atitude	15,584 ft (4750m)					
Regulatory and Com	pliance					
Safety	UL 60950-1 CAN/CSA C22.2 No. 60950-1 EN 60950-1 AS/NZS 60950-1 IEC 60950-1					
		GB-4943	GB-4943	GB-4943	GB-4943	GB-4943

Technical	Cisco 4451	Cisco 4431	Cisco 4351	Cisco 4331	Cisco 4321	Cisco 4221
Specifications						
EMC	47 CFR, Part 15	47 CFR, Part 15	47 CFR, Part 15	47 CFR, Part 15	ICES-003 Class A	ICES-003 Class A
	ICES-003 Class A	ICES-003 Class A	ICES-003 Class A	ICES-003 Class A	EN55022 Class A	EN55022 Class A
	EN55022 Class A	EN55022 Class A CISPR22 Class A	EN55022 Class A	EN55022 Class A	CISPR22 Class A	CISPR22 Class A
	CISPR22 Class A AS/NZS 3548	AS/NZS 3548	CISPR22 Class A AS/NZS 3548	CISPR22 Class A AS/NZS 3548	AS/NZS 3548 Class A	AS/NZS 3548 Class A
	Class A	Class A	Class A	Class A	VCCI V-3	VCCI V-3
	VCCI V-3	VCCI V-3	VCCI V-3	VCCI V-3	CNS 13438	CNS 13438
	CNS 13438	CNS 13438	CNS 13438	CNS 13438	EN 300-386	EN 300-386
	EN 300-386 EN	EN 300-386	EN 300-386	EN 300-386	EN 61000	EN 61000
	61000 (Immunity) EN 55024, CISPR	EN 61000	EN 61000	EN 61000	(Immunity)	(Immunity)
	24 EN50082-1	(Immunity)	(Immunity)	(Immunity)	EN 55024, CISPR 24	EN 55024, CISPR 24
	SD/EMI KN22,	EN 55024, CISPR 24	EN 55024, CISPR 24	EN 55024, CISPR 24	EN50082-1	EN50082-1
	KN24	EN50082-1	EN50082-1	EN50082-1	KN22, KN24	KN22, KN24
		KN22, KN24	KN22, KN24	KN22, KN24	14422, 14421	14422, 14421
Telecom	T1	TIA-968-B	TIA-968-B	TIA-968-B	TIA-968-B	TIA-968-B
	IC CS-03:2004	CS-03	CS-03	CS-03	CS-03	CS-03
	TIA-968-B:2009	ANSI T1.101	ANSI T1.101	ANSI T1.101	ANSI T1.101	ANSI T1.101
	HKTA 2028:2010	ITU-T G.823,	ITU-T G.823,	ITU-T G.823,	ITU-T G.823,	ITU-T G.823,
	HKTA 2017:2010	G.824	G.824	G.824	G.824	G.824
	HKTA 2015: 2006	RTTE Directive	IEEE 802.3	IEEE 802.3	RTTE Directive	RTTE Directive
	G.703:2001		RTTE Directive	RTTE Directive		
	ID0002:2007	Homologation requirements vary	Homologation requirements vary	Homologation requirements vary	Homologation requirements vary	Homologation requirements vary
	IS6100:2004	by country and	by country and	by country and	by country and	by country and
	DSPR Gray Book:2000	interface type. For specific country	interface type. For specific country	interface type. For specific country	interface ty pe. For specific country	interface type. For specific country
	DSPR Technical	information, refer	information, refer	information, refer	information, refer	information, refer
	Condition: 2004	to the online approvals data	to the online approvals data			
	E1	base at:	base at:	base at:	base at:	base at:
	AS/ACIF S016: 2001	http://www.ciscofax.com.	http://www.ciscofa x.com	http://www.ciscofa x.com.	http://www.ciscofa x.com	http://www.ciscofa x.com
	AS/ACIF S038: 2001					
	G.703:2001					
	TBR 4:1995					
	TBR 12:1993					
	TBR 13:1996					
	RRA 2009-38					
	(RRL 2005-96)					
	IDA TS DLCN:2011					
	IDATS ISDN					
	PRA:2005					
	IS6100: 2004					
	PTC 220:2008					
	Ethernet					
	IEEE 802.3					
	ANSA X3.263					

Technical Specifications	Cisco 4451	Cisco 4431	Cisco 4351	Cisco 4331	Cisco 4321	Cisco 4221	
Cisco IOS XE Soft	ware						
Protocols	IPv 4, IPv 6, static routes, Routing Information Protocol Versions 1 and 2 (RIP and RIPv 2), Open Shortest Path First (OSPF), Enhanced Interior Gateway Routing Protocol (EIGRP), Border Gateway Protocol (BGP), BGP Router Reflector, Intermediate System-to-Intermediate System (IS-IS), Multicast Internet Group Management Protocol Version 3 (IGMPv 3), Protocol Independent Multicast sparse mode (PIM SM), PIM Source-Specific Multicast (SSM), Resource Reservation Protocol (RSVP), Cisco Discovery Protocol, Encapsulated Remote Switched Port Analyzer (ERSPAN), Cisco IOS IP Service-Level Agreements (IPSLA), Call Home, Cisco IOS Embedded Event Manager (EEM), Internet Key Exchange (IKE), access control lists (ACL), Ethernet Virtual Connections (EVC), Dynamic Host Configuration Protocol (DHCP), Frame Relay (FR), DNS, Locator ID Separation Protocol (LISP), Overlay Transport Virtualization (OTV), ⁵ Hot Standby Router Protocol (HSRP), RADIUS, authentication, authorization, and accounting (AAA), Application Visibility and Control (AVC), Distance Vector Multicast Routing Protocol (DVMRP), IPv4-to-IPv6 Multicast, MPLS, Layer 2 and Layer 3 VPN, IPsec, Layer 2 Tunneling Protocol Version 3 (L2TPv3), Bidirectional Forwarding Detection (BFD), IEEE 802.1ag, and IEEE 802.3ah						
Encapsulations	Generic routing encapsulation (GRE), Ethernet, 802.1q VLAN, Point-to-Point Protocol (PPP), Multilink Point-to-Point Protocol (MLPPP), Frame Relay, Multilink Frame Relay (MLFR) (FR.15 and FR.16), High-Level Data Link Control (HDLC Serial (RS-232, RS-449, X.21, V.35, and EIA-530), and PPP over Ethernet (PPPoE)						
Traffic management		QoS, Class-Based Weighted Fair Queuing (CBWFQ), Weighted Random Early Detection (WRED), Hierarchical QoS, Policy-Based Routing (PBR), Performance Routing (PfR), and Network-Based Application Recognition (NBAR)					
Cryptographic algorithms		Encryption: DES, 3DES, AES-128 or AES-256 (in CBC and GCM modes); Authentication: RSA (748/1024/2048 bit), ECDSA (256/384 bit); Integrity: MD5, SHA, SHA-256, SHA-384, SHA-512					

Services Plane: Enabling the Branch-in-a-Box

All Cisco 4000 Series ISRs contain processing cores built in as standard to allow full-featured services to run on board. This includes the full-featured Cisco WAAS engine that provides application acceleration and highly responsive virtual desktop experience. The technology is known as Cisco Service Containers, and it uses a standard hypervisor to allow x64-based applications to run.

The 4000 Series routers can be fitted with solid-state drives (SSD) and server cards for local storage and computing capability. The Cisco UCS® E-Series server cards are available with 8-core Intel® Xeon® processors with up to 48 GB of high-speed DDR3 memory and three drives built in, offering RAID 0, 1, and 5. This immense amount of compute power can eliminate the need for any dedicated servers at branch sites. Cisco UCS E-Series cards can be configured and managed using VMware vCenter and pooled with data center compute resources.

Product Performance and Scalability

The Cisco 4000 Series is built on a multicore CPU architecture. It runs modular Cisco IOS XE Software, which allows the platform to use to full advantage a distributed multicore architecture. The architecture of the Cisco 4000 Series separates control- and data-plane operations and integrates an industry-first services plane. This design delivers full-featured integrated services up to Layer 7 at high performance, with the ability to deliver application-aware network services while maintaining a stable platform and a high level of performance during periods of heavy network traffic.

The 4000 Series consists of three subseries of routers – the 4400 Series, the 4300 Series, and the 4200 Series – whose performance levels are represented in Figure 2.

⁵ Supported only on the 4451 for bandwidths less than 100 Mbps.



Figure 2. Cisco 4000 Series ISRs Performance Comparison

Throughout the 4000 Series, all platforms come with fixed maximum performance levels. One fixed base performance level is delivered as the factory default, with an optional performance-on-demand license to increase the base forwarding throughput. This scenario enables deployment in high-speed WAN environments through performance-on-demand licensing to double or, for one of the platforms, triple the router capacity without any hardware upgrades.

All 4000 Series platforms have their fixed performance levels set well within actual capacity, with the result that performance does not necessarily degrade when a service is added to the configuration. This setup provides a deterministic performance, eliminating a network administrator's guesswork when planning for new services.

For a more detailed document on 4000 Series performance and platform scalability, refer to the white paper at http://www.cisco.com/c/en/us/products/collateral/routers/4000-series-integrated-services-routers-isr/white-paper-c11-734550.html.

Interfaces and Modules Support

The Cisco 4000 Series Integrated Services Routers (ISRs) are modular routers with LAN and WAN connectivity. The routers provide for network interface module (NIM) slots and enhanced service module (SM-X) slots, offering a rich set of modules, such as LAN, WAN and wireless interfaces, plus a range of compute engines for embedded services.

For the complete list of modules supported on the 4000 Series, refer to the Interfaces and Modules data sheet at http://www.cisco.com/c/en/us/products/routers/4000-series-integrated-services-routers-isr/relevant-interfaces-and-modules.html.

Support for Intelligent WAN

The 4000 Series is optimized for Cisco Intelligent WAN. For enterprises, this means that business-critical applications run faster, with more reliability and reduced operational expenditures (OpEx). The Intelligent WAN achieves this by giving all branches and data centers the ability to monitor, control, move, and report on streams of application data, such as specific web (HTTP) traffic. The 4000 Series has deep packet inspection capability and can accurately identify and control thousands of different applications, including custom in house enterprise applications.

The 4000 Series with Intelligent WAN can pay for itself in WAN cost savings within months, and the ongoing deep application visibility and reporting will continue to provide valuable application, site, and user statistics to better manage the rollout of new sites or applications.

The benefits are immense:

- 1. Business-critical applications no longer have to contend with each other or with traffic that should be served on a best effort basis.
- 2. The enterprise network becomes more reliable because multiple paths can be used.
- 3. Costs are greatly reduced because dual MPLS links can be replaced with a mix of MPLS and Internet.
- 4. The time required to bring up new remote sites is dramatically reduced because the Intelligent WAN supports rapidly deployed DSL and 3G/4G LTE connections as easily as MPLS.
- 5. Security is assured across these connections using a zero-touch secure VPN technology used by governments and finance organizations worldwide.

From a platform perspective, the 4000 Series has the following:

- 1. Separate control and data planes for prevention of denial-of-service (DoS) attacks, with intrusion prevention system (IPS) and firewall capability built in.
- 2. Software-as-a-service (SaaS) applications can have content locally cached. The caching is automatic and peers directly with Akamai technology to obtain intelligence.
- 3. Application performance speed is greatly increased using built-in application acceleration technology that can locally cache at a byte level.

Support for Data Modeling

Enterprises and service providers wish to drive down the operational cost (OpEx) of their networks and increase the agility and speed with which they deliver new services, furthered by investments in software-defined networking (SDN) and network functions virtualization (NFV). Cisco routers provide support for Netconf and YANG data modeling, with increasing model coverage in successive releases.

Cisco IOS Software Licensing and Packaging

Universal Cisco IOS XE Image

A single Cisco IOS XE Universal image encompassing all functions is delivered with the platform. Advanced features can be enabled simply by activating a software license on the Universal image. Technology packages and feature licenses, enabled through right-to-use licenses, simplify software delivery and decrease the operational costs of deploying new features.

Four major technologylicenses are available on the Cisco 4000 Series; these licenses can be activated through the Cisco software activation process identified at http://www.cisco.com/go/sa. The following licenses are available:

- IP Base: This technology package is available as the default.
- Application Experience (APPX): This license includes data and application performance features.
- Unified Communications (UC): ⁶ This license includes voice features.
- Security (SEC) or Security with No Payload Encryption (SEC-NPE): This license includes features for securing network infrastructure.

⁶ Unified Communications is not supported by ISR4221

The Cisco 4000 Series has a performance-on-demand license to increase the base forwarding throughput with no hardware changes. Also present is the High Security (HSEC) license, which removes the curtailment enforced by the U.S. government export restrictions on the encrypted tunnel count and encrypted throughput. The HSECK9 license is a separately required license for a feature to have full crypto functionality. Without the HSECK9 license, only 225 secure tunnels and 85 Mbps of crypto bandwidth would be available.

For additional information and details about Cisco IOS Software licensing and packaging on the Cisco 4000 Series, please visit

http://www.cisco.com/c/en/us/td/docs/routers/access/4400/software/configuration/quide/isr4400swcfq.pdf.

Cisco 4000 Series Bundles

Cisco 4000 Series routers are available is several attractive bundles. The AX bundles integrate Cisco Wide Area Application Services (WAAS), Security (SEC), and Data (DATA) licenses into a single bundle that is simple to order, configure, and deploy. For customers who are also interested in voice along with all of these features, AXV presents an attractive option. See Table 5 for details.

Table 5. Cisco 4000 Series Feature Bundles

Bundles	Features
Application Experience with Voice (AXV)	AX + Voice
Voice with Security (VSEC)	Voice + Security
Application Experience (AX)	IP Base + Security + advanced networking protocols: L2TPv3, BFD, MPLS, VRF, VXLAN (bandwidth less than 100 Mbps)
	Application Experience: PfRv3, WAAS with AppNav, NBAR2, AVC, IPSLA
	Hy brid Cloud Connectivity: LISP, OTV5 (for bandwidth less than 100 Mbps), Virtual Private LAN Services (VPLS), Ethernet over MPLS
	Intelligent web caching: Akamai Connect
Voice (V)	IP Base + Unif ied Communications: Cisco Unif ied Communications Manager Express, Survivable Remote Site Telephony (SRST), CUBE
Security (SEC)	IP Base + Adv anced Security: Zone-based firewall, IPsec VPN, EzVPN, Dynamic Multipoint VPN (DMVPN), FlexVPN

Note: The 4221/K9 does not support UC (voice). Hence, there are no V, VSEC, or AXV bundles for the 4221/K9 model.

More information on ISR AX bundles is available at http://www.cisco.com/go/ax.

A pay-as-you-grow licensing model lets you increase the performance level for the platforms from the base level to a higher level. So you can purchase at an attractive entry-level price point and increase the performance level as your business demand grows. Table 6 describes the performance licenses.

Table 6. Cisco 4000 Series Performance Licenses

Platform	Performance-on-Demand License	Features
ISR4451	FL-44-PERF-K9	Increases the performance from base performance 1 Gbps to 2 Gbps
ISR4431	FL-44-PERF-K9	Increases the performance from base performance 500 Mbps to 1 Gbps
ISR4351	FL-4350-PERF-K9	Increases the performance from base performance 200 Mbps to 400 Mbps
ISR4331	FL-4330-PERF-K9	Increases the performance from base performance 100 Mbps to 300 Mbps
ISR4321	FL-4320-PERF-K9	Increases the performance from base performance 50 Mbps to 100 Mbps
ISR4221	FL-4220-PERF-K9	Increases the performance from base performance 35 Mbps to 75 Mbps

⁷ Supported only on the 4451 model

Ordering Information

The Cisco 4000 Series ISRs are orderable and shipping. To place an order, refer to Table 7 and visit the Cisco Ordering Home Page.

Table 7. Cisco 4000 Series Ordering Information

Product Name	Product Description
ISR4451-X/K9	4451 ISR with 4 onboard GE, 3 NIM slots, 1 ISC slot, 2 SM slots, 8 GB flash memory default, 2 GB DRAM default (data plane), 4 GB DRAM default (control plane)
ISR4431/K9	4431 ISR with 4 onboard GE, 3 NIM slots, 1 ISC slot, 8 GB flash memory default, 2 GB DRAM default (data plane), 4 GB DRAM default (control plane)
ISR4351/K9	4351 ISR with 3 onboard GE, 3 NIM slots, 1 ISC slot, 2 SM slots, 4 GB flash memory default, 4 GB DRAM default
ISR4331/K9	4331 ISR with 3 onboard GE, 2 NIM slots, 1 ISC slot, 1 SM slot, 4 GB flash memory default, 4 GB DRAM default
ISR4321/K9	4321 ISR with 2 onboard GE, 2 NIM slots, 1 ISC slot, 4 GB flash memory default, 4 GB DRAM default
ISR4221/K9	4221 ISR with 2 onboard GE, 2 NIM slots, 1 ISC slot, 8 GB flash memory default, 4 GB DRAM default

For additional product numbers, including the Cisco 4000 Series bundle offerings, please contact your local Cisco account representative. To place an order, visit the <u>Cisco Ordering Home Page</u>. To download software, visit the <u>Cisco Software Center</u>.

Integrated Services Router Migration Options

The Cisco 4000 Series is included in the standard Cisco Technology Migration Program (TMP). Refer to http://www.cisco.com/go/tmp and contact your local Cisco account representative for program details.

Warranty Information

The Cisco 4000 Series Integrated Services Routers have a 90-day limited liability warranty.

Cisco and Partner Services for the Branch Office

Services from Cisco and our certified partners help you transform the branch-office experience and accelerate business innovation and growth. We have the expertise to create a clear, replicable, optimized branch-office footprint across technologies. Planning and design services align technology with your business goals and can increase deployment efficiency. Technical services help you improve operational efficiency, save money, and mitigate risk. Optimization services help you continuously improve performance and succeed with new technologies. For more information, please visit http://www.cisco.com/go/services.

Cisco Smart Net Total Care [™] technical support for the Cisco 4000 Series is available on a one-time or annual contract basis. Support options range from help-desk assistance to proactive, onsite consultation. All support contracts include:

- Major Cisco IOS Software updates for protocol, security, bandwidth, and feature improvements
- Full access rights to Cisco.com technical libraries for technical assistance, electronic commerce, and product information
- · Access 24 hours a day to the industry's largest dedicated technical support staff

Cisco Capital

Financing to Help You Achieve Your Objectives

Cisco Capital[®] can help you acquire the technology you need to achieve your objectives and stay competitive. We can help you reduce CapEx. Accelerate your growth. Optimize your investment dollars and ROI. Cisco Capital financing gives you flexibility in acquiring hardware, software, services, and complementary third-party equipment. And there's just one predictable payment. Cisco Capital is available in more than 100 countries. Learn more.

For More Information

For more information about the Cisco 4000 Series, visit http://www.cisco.com/go/isr4k or contact your local Cisco account representative.



Americas Headquarters Cisco Systems, Inc. San Jose, CA Asia Pacific Headquarters Cisco Systems (USA) Pte. Ltd. Singapore Europe Headquarters Cisco Systems International BV Amsterdam, The Netherlands

 $Cisco\ has\ more\ than\ 200\ offices\ worldwide.\ Addresses,\ phone\ numbers,\ and\ fax\ numbers\ are\ listed\ on\ the\ Cisco\ Website\ at\ www.cisco.com/go/offices.$

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: www.cisco.com/go/trademarks. Third party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)

Printed in USA C78-732542-15 01/17