

HP Pavilion x360 Convertible 15-bk010nr



Your 360° entertainment revolution

Seamlessly shift between four modes for an entertainment experience that gets you closer to your screen than ever before.

Product overview

- The laptop will never be the same again:** The 360 degree hinge gets you in the perfect position to work, watch, play and go.
- Take it anywhere:** Thin, light and great battery life, so your laptop can go wherever you go.
- A truly powerful audio experience:** HP Audio Boost and audio tuning by B&O PLAY deliver rich, authentic sound.

Key specifications

- Operating system:** Windows 10 Home⁽¹⁾
- Processor:** 6th generation Intel® Core™ i5-6200U Processor^(2b)
- Display:** 15.6-inch diagonal Full HD^(3g) IPS UWVA WLED-backlit multitouch-enabled edge-to-edge glass (1920 x 1080)
- Memory:** 8 GB DDR3L SDRAM (2 DIMM)
- Hard drive:** 1TB 5400RPM Serial ATA hard drive^(4b)
- Graphics:** Intel® HD Graphics 520^(4a) with up to 4168 MB total graphics memory
- Battery life:** Up to 8 hours and 30 minutes^(7g)
- Audio:** B&O PLAY with dual speakers
- Product weight:** 5.07 lb^(6g)
- Keyboard:** Full-size island-style keyboard with numeric keypad

Product features

- Windows 10 Home is here. Do great things.⁽¹⁾**
- 360° hinge for ultimate flexibility:** Work in notebook mode, watch in stand mode, play in tent mode, go in tablet mode.
- Fluid motion:** The synchronized geared hinge was engineered to rotate 360° fluidly, yet hold firmly in each mode.
- Streak design:** Easily take this thin and light PC from room to room or on the road. Take it anywhere and look sharp.
- 6th generation Intel processor:** Enhance your computing experience with the latest processors from Intel.
- Step up to the best:** IPS technology brings you clear views from almost any angle. Every seat is the best seat in the house.
- Beautifully immersive:** Reach out and touch, tap, or swipe with the responsive touchscreen. Experience expansive entertainment on its vibrant edge-to-edge Full HD display.^(3g)
- A truly powerful audio experience:** HP with Audio by B&O PLAY delivers rich, authentic audio custom-tuned in collaboration with sound experts at Bang & Olufsen. Let the immersive experience move you.
- Crisp sound. Big volume.** HP Audio Boost with smart amplification technology gives you loud, clear, and dynamic sound.
- Keep going with a battery that lasts:** Go about your day longer without recharging.
- One year of free cloud storage:** Get 25GB of free online storage for one year with Dropbox.⁽²²⁾
- McAfee® LiveSafe™:** Protect your operating systems with a free 30-day McAfee LiveSafe trial.⁽⁸⁾

Energy efficiency your way

HP is committed to global citizenship and environmental responsibility. Do the environment—and your wallet—a favor when you use the HP Pavilion x360 Convertible that meets strict energy-efficiency and helps reduce your carbon footprint.

- ENERGY STAR® certified^(6a)
- EPEAT® Silver registered⁽²⁷⁾
- Low Halogen⁽⁶¹⁾
- Mercury-free display backlights
- Arsenic-free display glass
- All HP computing products are delivered by SmartWay carriers.⁽⁶³⁾
- Recycled Packaging: Count on easy recycling every time. HP designs products and packaging that can be conveniently recycled or reused.⁽³¹⁾

Warranty and support

Our Customer Support Team consistently provides quick, responsive assistance in the U.S., Canada and Latin America.

Included with your product:

- HP's Hardware Limited Warranty:** Full warranty details are included with your product.
- HP Support Assistant - HPSA:** Optimized to enhance your support experience. Help for your PC and HP printers whenever you need it.⁽⁵⁶⁾⁽⁵⁷⁾
- Online Support:** For technical support with this product, visit HP Customer Support <http://support.hp.com>⁽⁹⁾
- Social Media Support:** To find solutions, ask questions, and share tips, join us on the HP Support Forum at hp.com/supportforum, on Twitter at twitter.com/HPSupport, and Facebook at facebook.com/HPSupport⁽⁹⁾
- Phone Support:** This product includes 90 days of complimentary phone support.⁽⁵³⁾ After 90 days, a fee may apply.

Extend your coverage:

- SmartFriend, part of HP Care:** Experts are available 24/7 to handle any tech issue, on any device, from any brand. Visit www.hp.com/go/smartfriend to learn more or call toll-free 1-844-814-1800 to get started.⁽⁹⁵⁾
- Care Packs:** Extend protection beyond the standard limited warranty. For more info, visit www.hp.com/go/carepack-services or call toll-free at 1-877-232-8009⁽⁸³⁾



Specifications

Operating System	• Windows 10 Home ⁽¹⁾
Processor	• 6th generation Intel® Core™ i5-6200U Processor ^(2b) • Dual-Core
Processor Speed	• 2.3GHz with turbo boost up to 2.8GHz ^{(2g)(7)}
Processor Cache	• 3MB L3 Cache
Memory	• 8 GB DDR3L SDRAM (2 DIMM)
Accessible memory slots	• Memory slot not user accessible
Video Graphics	• Intel® HD Graphics 520 ⁽¹⁴⁾ with up to 4168 MB total graphics memory
Hard Drive	• 1TB 5400RPM Serial ATA hard drive ^(4b)
Finish and Features	• Natural silver and ash silver with horizontal brushing in digital thread lines • Front-facing HP TrueVision HD Webcam with integrated dual array digital microphones ⁽⁹⁾
Display	• 15.6-inch diagonal Full HD ⁽³⁹⁾ IPS UWVA WLED-backlit multitouch-enabled edge-to-edge glass (1920 x 1080)
Network Card	• Integrated 10/100/1000 GbE LAN ⁽²⁹⁾
Wireless Option	• 1x1 802.11ac ⁽¹⁹⁾ WLAN and Bluetooth ⁽²⁶⁾
Digital Media	• Multi-Format Digital Media Card Reader
Audio	• B&O PLAY with dual speakers
Keyboard	• Full-size island-style keyboard with numeric keypad
Pointing Device	• HP Imagepad with multi-touch gesture support
External Notebook Ports	• 2 SuperSpeed USB 3.0 • 1 Universal Serial Bus (USB) 2.0 • 1 HDMI • 1 RJ-45 (LAN) • 1 Headphone-out/microphone-in combo jack
Dimensions	• Unpackaged: 0.94 in (H) x 15.04 in (W) x 9.84 in (D) • Packaged: 20.47 in (L) x 2.72 in (W) x 12.01 in (D)
Weight	• Unpackaged: 5.07 lb ⁽⁷⁶⁾ • Packaged: 6.50 lb
Security	• Kensington MicroSaver® lock slot • Power-on password • Accepts 3rd party security lock devices
Power	• 3-cell 48 WHr lithium-ion prismatic battery • 45W AC adapter
Battery Life	• Up to 8 hours and 30 minutes ⁽⁷⁰⁾
Warranty and Support	• 1-Year Limited Hardware warranty. Additional information available at www.support.hp.com ⁽⁹⁾ • 90 days Limited Technical support for Software and Initial Setup (from date of purchase) ⁽⁵³⁾

Software

Games	• Wild Tangent Games for HP pre-installed: Your HP computer comes with 10 free sessions of Delicious Emily's Wonder Wedding Premium Edition (\$19.99 value) and 10 free sessions of Runefall (\$9.99 value). ⁽⁷⁹⁾
HP Help and Support	• HP ePrint: Wirelessly print from anywhere, anytime, on any HP ePrint-enabled printer. ^(85a) • HP Support Assistant: Makes it easier than ever to get help for your PC and HP printers whenever you need it. HP Support Assistant is included with HP computers, absolutely free. ⁽⁵⁶⁾⁽⁵⁷⁾
Shopping and Services	• TripAdvisor online community: Easily find the lowest airfare, the best hotels, great restaurants, and fun things to do wherever you go. ⁽⁹⁾
Books, Music, Photos and Videos	• CyberLink PowerDirector: Create picture-perfect portraits and pro-quality videos with powerful editing tools. ⁽²³⁾ • Netflix: Watch movies and TV online or via DVDs with subscription. ⁽⁹⁾ • Snapfish: Enjoy your photos with access from any device, all in one place. Celebrate your memories with photo gifts and prints for delivery by mail, in-store pick-up, or print to any printer anywhere. ⁽³⁶⁾
Productivity and Tools	• One year of free cloud storage: Get 25GB of free online storage for one year with Dropbox. ⁽²²⁾
Security and protection	• HP 3D DriveGuard: Your PC's data stays safe from accidental bumps and bruises. • McAfee® LiveSafe™: Protect your operating systems with a free 30-day McAfee LiveSafe trial. ⁽⁸⁾

Additional Information

Product Number	• W2M08UA#ABA
Ad Embargo Date	• 07/10/2016
UPC Code	• 889899844892
Country of Origin	• China
Tariff Number	• 8471300000
Pallet Information	• Dimensions: 39.37 in (L) x 47.24 in (W) x 41.51 in (H) • Total weight: 599.50 lb • Layers: 3 • Products per layer: 29

Learn more at hp.com

⁽¹⁾ Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 10 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.microsoft.com> ^(2a) Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of higher performance. Intel, Pentium, Intel Core, Celeron, Intel logo and the Intel Inside logo are trademarks of Intel Corporation in the U.S. and other countries. ^(2b) Intel® Turbo Boost technology requires a PC with a processor with Intel Turbo Boost capability. Intel Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information. ^(4b) For storage drives, TB = 1 trillion bytes. Actual formatted capacity is less. Up to 35GB of drive is reserved for system recovery software. ⁽⁷⁾ GHz refers to internal clock speed of the processor. Other factors besides clock speed may impact system and application performance. ⁽⁸⁾ Internet access required and not included. Subscription required after 30 days trial period. McAfee, LiveSafe and the McAfee logo are trademarks or registered trademarks of McAfee, Inc. in the United States and other countries. ⁽⁹⁾ Internet access required and not included. Availability of public wireless access points limited. ⁽¹⁴⁾ Shared video memory (UMA) uses part of the total system memory for video performance. System memory dedicated to video performance is not available for other use by other programs. ⁽¹⁹⁾ Wireless access point and Internet service required and not included. Availability of public wireless access points limited. ⁽²²⁾ 25 GB of Dropbox space free for 12 months from date of registration. For complete details and terms of use, including cancellation policies, visit the Dropbox website at www.dropbox.com. Internet service required and not included. ⁽²³⁾ Intended for your original content and other lawful purposes. Do not copy protected material. ⁽²⁶⁾ Bluetooth® is a trademark owned by its proprietor and used by HP Inc. under license. ⁽²⁷⁾ EPEAT® Silver registered where applicable. EPEAT registration varies by country. See www.epeat.net for registration status by country. ⁽²⁹⁾ Actual speeds may vary. ⁽³¹⁾ Free recycling in select countries. Program may not be available in your area. Check www.hp.com/go/recycling to see if HP offers free recycling in your area. ⁽³⁶⁾ App availability varies by country. Supported on Windows 8.1 and above, Android and iOS operating systems. Free Snapfish membership required. Internet service required and not included. Print ordering for pick-up at select retailers available in U.S. only. ⁽³⁹⁾ Full High Definition (FHD) content is required to view FHD images. ⁽⁴³⁾ Call 1.800.474.6836 or www.support.hp.com for more information on Care Packs available after 90 days. After 90 days, an incident fee may apply. ⁽⁵⁶⁾ For more information visit hp.com/go/hpsupportassistant [Link will vary outside of the U.S.] HP Support Assistant is available for Android and Windows based PCs. ⁽⁵⁷⁾ Internet connection required for updating and connecting to HP Support. ⁽⁶¹⁾ External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen. ⁽⁶²⁾ ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. ⁽⁶³⁾ Designation based on actions to reduce transportation-related emissions. ⁽⁷⁰⁾ Windows 10 MM14 battery life will vary depending on various factors including product model, configuration, loaded applications, features, use, wireless functionality, and power management settings. The maximum capacity of the battery will naturally decrease with time and usage. See www.bapco.com for additional details. ⁽⁷⁶⁾ Weight and system dimensions may fluctuate due to configuration and manufacturing variances. ⁽⁷⁹⁾ Games may be limited during trial period. Full version games may be purchased at any time. Internet access required and not included. ⁽⁸²⁾ Service levels and response times for HP Care Pack Services may vary depending on geographic location. Service starts from date of hardware purchase. Restrictions and limitations apply. HP Care Packs are sold separately. See www.hp.com/go/carepack-services for details. ^(85a) Requires an Internet connection, not included, to an HP web-enabled printer and HP ePrint account registration. For complete details, see www.hp.com/go/mobileprinting ⁽⁸⁵⁾ HP SmartFriend will support any major brand of computer and tablet running Windows, OSX, iOS, Android, and Chrome OS. 24 x 7 phone support is available in the US only. Service availability varies by country/region. Internet connection required for remote support. HP SmartFriend sold separately or as an add-on feature. Actual product may vary from image shown. © Copyright 2016 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing shall be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. All other trademarks are the property of their respective owners. 06/8_r5 kc

