



HP ProDesk 600 G3 Small Form Factor PC

Powered for business, the HP ProDesk 600 SFF is a highly expandable PC featuring flexible connectivity options, strong security, and comprehensive manageability features in a stylishly redesigned chassis for the modern workplace.

HP recommends Windows 10 Pro.



Expansion that extends your investment

The full value of your investment comes with expansion that extends the life of your PC. The HP ProDesk 600 SFF has two bays, two slots, two M.2 connectors, and configurable video ports in addition to legacy ports.

HP exclusive security and manageability

Help prevent data breaches and downtime with HP BIOSphere Gen3⁵ and simplify management with HP WorkWise⁶, HP's most advanced smartphone app for PC management.

Powerful options

Power through your day with high-performance 7th Gen Intel[®] Core™ i3/i5/i7 processors² unleashed by optional Intel[®] Optane™⁴ technology, up to 64 GB of DDR4 memory⁴, and optional graphics cards⁴.

Connection hub

With 8 total USB ports, up to three video outputs, and optional Bluetooth™⁴ connectivity, the HP ProDesk 600 SFF becomes a hub for all your devices in the office.

- Power through your day with Windows 10 Pro¹ and the powerful HP ProDesk 600 SFF with built-in security, collaboration, and connectivity.
- Keep productivity high and downtime low with HP BIOSphere Gen3⁵ firmware-level automation. Your PCs have extra protection thanks to automatic updates and security checks.
- HP WorkWise⁶ is office intelligence rolled into one smartphone app to provide PC security, real-time PC performance information, and simplified printer driver installation for HP PC users.
- The HP Manageability Integration Kit³ helps speed up image creation and management of hardware, BIOS, and security through Microsoft System Center Configuration Manager.
- HP Client Security Suite Gen3³ features HP Multi-Factor Authenticate, HP Device Access Manager¹⁰, HP SpareKey, and HP Password Manager. These tools work to keep data out of reach and defend against theft, attacks, and unauthorized users.
- Improve the quality and security of custom Windows images with HP Image Assistant which assists ITDMs with image creation, identifies problems, and provides recommendations and remediation.
- Greatly improve the transfer rates of user's data, voice, and video communication when connecting over challenged LAN or Wi-Fi networks with HP Velocity.
- Rest easy with a PC that goes the distance and is designed to pass HP Total Test Process.
- Audio connections are easy with the Universal Audio Jacki that supports mic in, headphones, and CTIA headsets with the same connector.
- Simplify technical support with Helpdesk by HP Care. Rely on cost-effective expertise that's available 24x7, covering multiple brands, devices and operating systems¹¹.
- Help maximize your cash flow with the use of best-in-class hardware and services for a monthly subscription that allow you to replace your PC with a brand new one every three years¹².
- HP helps you preserve your time and optimize your resources with expert configuration and deployment services that bring you fast, accurate, and globally standardized IT solutions.

HP ProDesk 600 G3 Small Form Factor PC Specifications Table



Form Factor	Small form factor
Available Operating System	Windows 10 Pro 64 – HP recommends Windows 10 Pro. ¹ Windows 10 Home 64 ¹ Windows 10 Pro 64 (National Academic License) ² Windows 10 Home Single Language 64 ¹ Windows 7 Professional 64 (available through downgrade rights from Windows 10 Pro) ³ FreeDOS 2.0 NeoKylin Linux® 64
Available Processors	Intel® Core™ i7-7700 with Intel HD Graphics 630 (3.6 GHz, up to 4.2 GHz with Intel Turbo Boost, 8 MB cache, 4 cores); Intel® Core™ i5-7500 with Intel HD Graphics 630 (3.4 GHz, up to 3.8 GHz with Intel Turbo Boost, 6 MB cache, 4 cores); Intel® Core™ i5-7600 with Intel HD Graphics 630 (3.5 GHz, up to 4.1 GHz with Intel Turbo Boost, 6 MB cache, 4 cores); Intel® Core™ i3-7100 with Intel HD Graphics 630 (3.9 GHz, 3 MB cache, 2 cores); Intel® Core™ i3-7300 with Intel HD Graphics 630 (4 GHz, 4 MB cache, 2 cores); Intel® Core™ i3-7320 with Intel HD Graphics 630 (4.1 GHz, 4 MB cache, 2 cores); Intel® Core™ i7-6700 with Intel HD Graphics 530 (3.4 GHz, up to 4.0 GHz with Intel Turbo Boost, 8 MB cache, 4 cores); Intel® Core™ i5-6600 with Intel HD Graphics 530 (3.3 GHz, up to 3.9 GHz with Intel Turbo Boost, 6 MB cache, 4 cores); Intel® Core™ i5-6500 with Intel HD Graphics 530 (3.2 GHz, up to 3.6 GHz with Intel Turbo Boost, 6 MB cache, 4 cores); Intel® Core™ i3-6100 with Intel HD Graphics 530 (3.7 GHz, 3 MB cache, 2 cores); Intel® Pentium® G4560 with Intel HD Graphics 610 (3.5 GHz, 3 MB cache, 2 cores); Intel® Pentium® G4600 with Intel HD Graphics 630 (3.6 GHz, 3 MB cache, 2 cores); Intel® Pentium® G4620 with Intel HD Graphics 630 (3.7 GHz, 3 MB cache, 2 cores); Intel® Celeron™ G3950 with Intel HD Graphics 610 (3 GHz, 2 MB cache, 2 cores); Intel® Celeron™ G3930 with Intel HD Graphics 610 (2.9 GHz, 2 MB cache, 2 cores) ^{4,5}
Chipset	Intel® Q270
Maximum Memory	64 GB DDR4-2400 SDRAM ⁶ (Transfer rates up to 2400 MT/s)
Memory Slots	4 DIMM
Internal Storage	128 GB up to 256 GB 2.5" SATA SSD ⁷ 500 GB up to 1 TB 2.5" SATA SSHD (5400 rpm) ⁷ 500 GB up to 2 TB 3.5" SATA HDD (7200 rpm) ⁷ 256 GB up to 512 GB 2.5" SATA SED SSD ^{7,8} 256 GB up to 1 TB HP Turbo Drive G2 TLC SSD (PCIe) ⁷ 1 TB 3.5" SSHD (7200 rpm) ⁷ 500 GB up to 1 TB 2.5" SATA HDD (7200 rpm) ⁷ 500 GB 2.5" SATA SED HDD ⁷
Available Graphics	Integrated: Intel® HD Graphics 530; Intel® HD Graphics 630; Intel® HD Graphics 610 ^{10,11,12} Discrete: NVIDIA® GeForce® GT 730 HDMI (1 GB); NVIDIA® GeForce® GT 730 (2 GB)
Audio	Conexant CX20632 codec with universal audio jack and 2W internal speaker, headset and headphone front ports (3.5 mm), multi-streaming capable
Communications	LAN: Intel® I219LM Gigabit Network Connection LOM WLAN: Intel® 8265 802.11 ac (2x2) wireless with Bluetooth® M.2 combo card vPro™; Intel® 8265 802.11 ac (2x2) wireless with Bluetooth® M.2 combo card non-vPro™; Intel® 7265 802.11 ac (2x2) wireless with Bluetooth® M.2 combo card non-vPro™; Intel® 3168 802.11 ac (2x2) wireless with Bluetooth® M.2 combo card non-vPro™ ⁹
Expansion Slots	1 M.2 2230 for optional wireless NIC; 1 M.2 2280 for storage drives; 2 low-profile PCIe x16 (one wired as a x4)
Ports and Connectors	Front: 1 SD 4 card reader (optional); 1 USB 3.1 Type-C™ (charging); 2 USB 3.1 Gen 1; 1 USB 2.0; 1 USB 2.0 (fast charging); 1 headset connector Back: 1 audio in; 1 serial (optional); 1 RJ-45; 1 audio out; 2 DisplayPort™; 2 USB 2.0; 2 USB 3.1 Gen 1; 1 power connector; 2 USB 2.0 (non-vPro™); 2 USB 3.1 Gen 1 (vPro™) Back (optional): 1 HDMI; 1 VGA; 1 USB 3.1 Type-C™; 1 DisplayPort™
Internal Drive Bays	One 2.5" HDD or One 3.5" HDD
External Drive Bays	One SD 4 card reader; One slim ODD
Available Software	HP business PCs are shipped with a variety of software titles including: HP BIOSphere Gen3, CyberLink Power Media Player, Native Miracast Support, HP ePrint Driver, HP Support Assistant. Please refer to this product's quick spec document for a full list of preinstalled software. ^{14,15,16}
Security Management	Trusted Platform Module TPM 2.0 Embedded Security Chip (SLB9670 - Common Criteria EAL4+ Certified); SATA 0,1 port disablement (via BIOS); Drive lock; Serial, USB enable/disable (via BIOS); Power-on password (via BIOS); Setup password (via BIOS); Solenoid hood lock/intrusion sensor; Support for chassis padlocks and cable lock devices

Management Features	Intel® vPro™ optional (Core i5 and Core i7)
Power	180 W, up to 85% efficient, active PFC
Dimensions	10.6 x 3.7 x 11.7 in 27 x 9.5 x 2.96 cm
Weight	9.98 lb 4.53 kg
Environmental	Low halogen ¹⁸
Energy Efficiency Compliance	ENERGY STAR® certified and EPEAT® registered configurations available ¹⁷

HP ProDesk 600 G3 Small Form Factor PC

Accessories and services (not included)

HP 3D 256GB SATA Solid State Drive

Expand the storage capabilities of your desktop with the HP 3D 256 GB SATA SSD¹, which includes 3D V NAND flash for impressive read/write performance and reliability plus the same solid performance you already get from current from SSD drives.

Product number: N1M49AT

HP USB Business Speakers v2

Quickly and easily add stereo sound to your workspace with HP USB Business Speakers v2, a set of stylish desktop speakers powered by your PC's USB port.

Product number: N3R89AT

HP Business PC Security Lock v2 Kit

Help prevent chassis tampering and secure your PC and display in workspaces and public areas with the HP Business PC Security Lock v2 Kit.

Product number: N3R93AT

Messaging Footnotes

- ¹ Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 10 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.
- ² Multi-Core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of higher performance.
- ³ Some functionality of this technology, such as Intel® Active management technology and Intel Virtualization technology, requires additional 3rd party software in order to run. Availability of future "virtual appliances" applications for Intel vPro technology is dependent on 3rd party software providers.
- ⁴ Sold separately or as an optional feature.
- ⁵ HP BIOSphere Gen3 features may vary depending on the PC platform and configurations.
- ⁶ HP WorkWise smartphone app will soon be available as a free download on the App Store and Google Play.
- ⁷ Based on major competitors as of November 1, 2016 with smartphone managed PC security, performance and print features.
- ⁸ HP Manageability Integration Kit is planned to be available first quarter 2017 and can be downloaded from <http://www8.hp.com/us/en/ads/clientmanagement/overview.html>.
- ⁹ HP Client Security Suite Gen3 requires Windows and Intel® 7th Gen processors.
- ¹⁰ HP Multi Factor Authenticate requires 7th Generation Intel® Core™ processor, Intel® integrated graphics, and Intel® WLAN.
- ¹¹ HP Care Services are optional. Service levels and response times for HP Care Pack Services may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit www.hp.com/go/cpc. HP services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.
- ¹² Financing and service offerings available through Hewlett-Packard Financial Services Company and its subsidiaries and affiliates (collectively HPFSC) in certain countries and is subject to credit approval and execution of standard HPFSC documentation. Subscriptions to use are available for 24 or 36 month terms. Rates and terms are based on customer's credit rating, offering types, services and/or equipment type and options. Not all customers may qualify. Not all services or offers are available in all countries. Other restrictions may apply. HPFSC reserves the right to change or cancel this program at any time without notice.

Technical Specifications Footnotes

- ¹ Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 10 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com/>.
- ² Some devices for academic use will automatically be updated to Windows 10 Pro Education with the Windows 10 Anniversary update. Features vary; see <https://aka.ms/ProEducation> for Windows 10 Pro Education feature information.
- ³ This system is preinstalled with Windows 7 Pro software and also comes with a license and media for Windows 10 Pro software. You may only use one version of the Windows software at a time. Switching between versions will require you to uninstall one version and install the other version. You must back up all data (files, photos, etc.) before uninstalling and installing operating systems to avoid loss of your data.
- ⁴ Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of higher performance.
- ⁵ Your product does not support Windows 8 or Windows 7. In accordance with Microsoft's support policy, HP does not support the Windows 8 or Windows 7 operating system on products configured with Intel and AMD 7th generation and forward processors or provide any Windows 8 or Windows 7 drivers on <http://www.support.hp.com>.
- ⁶ Due to the non-industry standard nature of some third-party memory modules, we recommend HP branded memory to ensure compatibility. If you mix memory speeds, the system will perform at the lower memory speed.
- ⁷ For storage drives, GB = 1 billion bytes. TB = 1 trillion bytes. Actual formatted capacity is less. Up to 30 GB (for Windows 10) is reserved for system recovery software.
- ⁸ TLC SSD in Federa Information Processing Standard
- ⁹ Wireless cards are optional or add-on features and requires separately purchased wireless access point and internet service. Availability of public wireless access points limited. The specifications for the 802.11ac WLAN are draft specifications and are not final. If the final specifications differ from the draft specifications, it may affect the ability of the notebook to communicate with other 802.11ac WLAN devices.
- ¹⁰ Intel® HD Graphics 530: integrated on 6th gen Core™ i7/i5/i3 processors
- ¹¹ Intel® HD Graphics 630: integrated on 7th gen Core™ i7/i5/i3 processors and Pentium® G4620, 4600, 4600T
- ¹² Intel® HD Graphics 610: integrated on Pentium® G4560, G4560T, Celeron™ G3950, G3930, G3930T
- ¹³ Sold separately or as an optional feature.
- ¹⁴ HP BIOSphere Gen 3 requires Intel® 7th generation processors.
- ¹⁵ Miracast is a wireless technology your PC can use to project your screen to TVs, projectors, and streaming media players that also support Miracast. You can use Miracast to share what you're doing on your PC and present a slide show. For more information: <http://windows.microsoft.com/en-us/windows-8/project-wireless-screen-miracast>.
- ¹⁶ HP ePrint Driver requires an Internet connection to HP web-enabled printer and HP ePrint account registration (for a list of eligible printers, supported documents and image types and other HP ePrint details, see www.hp.com/go/eprintcenter). Requires optional broadband module. Broadband use requires separately purchased service contract. Check with service provider for coverage and availability in your area. Separately purchased data plans or usage fees may apply. Print times and connection speeds may vary.
- ¹⁷ EPEAT® registered where applicable. EPEAT registration varies by country. See www.epeat.net for registration status by country.
- ¹⁸ External power supplies, power cords, cables and peripherals are not low halogen. Service parts obtained after purchase may not be low halogen.

Sign up for updates
hp.com/go/getupdated

Learn more at
hp.com

Copyright © 2016 HP Development Company, L.P. The only warranties for HP products are set forth in the express limited warranty statements accompanying such products. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Pentium, Celeron and vPro are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries. Bluetooth is a trademark of its proprietor and used by HP Inc. under license. USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. All Rights Reserved. All other trademarks are the property of their respective owners.

