

T7DEE832R Front loaded TD



INTRODUCING THE SHEER BLOUSE PROTECTOR

Your knitwear, cotton tees, business shirts – the clothes you wear day in, day out – need special care to keep them feeling special. Using low temperatures without extending drying times, AEG SensiDry® Technology ensures that garments are never



SAFE, LOW TEMPERATURES

AEG SensiDry technology draws moisture out of fabrics at half the temperature of conventional tumble dryers, without significantly extending the drying time. This ensures that fabrics are never subject to unnecessary heat. Your clothes will keep the textures

SAVING YOU TIME AND ENERGY EVERY DAY

Our dryers feature ProSense technology, which uses advanced humidity and temperature sensors to adjust the drying time and energy consumption for every size of load - whether it's a day's or a week's worth of washing. This saves time and energy, while gently protecting the clothes that you love and wear every day.

More Benefits :

- FUSS-FREE FILTER FOR EFFICIENCY
- BUILT-IN PROTECTION FOR YOUR CLOTHES

Features :

- Heat pump technology achieves unprecedented energy efficiency
- Panel with text in English
- Sensor dryer: the dryer senses when the clothes are dried to the level specified
- Additional time controlled drying programs
- Cotton programs: Cupboard dry, Extra dry, Iron dry
- Synthetics programs: Cupboard dry, Extra dry, Iron dry
- Special drying programs: Bedlinen, Cottons, Easy iron, Mix, Silk, Sport, Synthetics, Wool, activewear, duvet
- Energy consumption (program cotton cupboard dry): only 2.03 (2.6) kWh after spin speed drying at 1400 (1000) rpm
- Reverse tumble action loosens the clothes and prevents tangling and creasing
- Display type: Medium LCD
- Delay start option
- Drying status indication for: Anti-crease/end, Cool down, Cupboard dry, Drying, Extra dry, Iron dry
- Indications for: Condenser, Filter, Tank
- Condense tank position and capacity: Panel left , 5.28 l
- Feet: 4 adjustable feet
- Full load capacity: 8.0 kg
- Door hinge: Left reversible by user

Technical Specs :

- Product Installation : Free_Standing
- Product Typology : Full_Size_Condense_Heat_Pump
- Product Classification : Statement
- Installation : FS
- Drying technology : Heat pump
- Cabinet type of : Sahara 60
- Design family : P one
- Main colour : White
- Panel colour : White
- Insert panel colour : White
- Front door : P1S+Turbine
- Type of timer min. : EDR14
- Push button functions : Anti-crease, Delay start, Dryness, On/off, Refresh, Start/pause, Time dry
- Push button functions number of : 7
- Knob/Command functionality : Drying program
- Indicator programme : Medium LCD
- Indicators display : Remaining time
- Indicator drying status : Anti-crease/end, Cool down, Cupboard dry, Drying, Extra dry, Iron dry
- Indicators other : Condenser, Filter, Tank
- Display type : Medium LCD
- Other comments technical specifications : Standby II directive compliant from W26/2012
- Height total : 850
- Width mm : 600
- Depth mm : 600
- Drum volume : 118
- Full load capacity kg : 8.0
- Cabinet material : Steel
- Drum material : Stainless steel Protex
- Tank position : Panel left
- Tank capacity : 5.28
- Filter position : Front cabinet
- Humidity control : Conductimetric
- Frequency : 50
- Voltage : 230-240

Product Description :

AEG916 098 118