


T27DS59N0

75 CM, GAS HOB WITH INTEGRATED CONTROLS,

STAINLESS STEEL



The gas cooktop with a stainless-steel surface design and incrementally adjustable FlameSelect.

- ✓ FlameSelect - Thanks to the clever control of gas flow, the flame can be precisely adjusted in 9 gradations. Always the same reliable and precise power levels for outstanding cooking convenience.
- ✓ Powerful cooking at up to 4 kW.
- ✓ Continuous cast-iron pan supports for maximum stability and cooking convenience.

Features

Technical Data

Product name/family : gas hob w integrated controls
Construction type : Built-in
Energy input : Gas
Total number of positions that can be used at the same time : 5
Required niche size for installation (HxWxD) : 45 x 560-562 x 480-492
Width of the product (mm) : 750
Dimensions of the product (mm) : 45 x 750 x 520
Net weight (kg) : 12.0
Gross weight (kg) : 14.0
Residual heat indicator : without
Location of control panel : Hob front
Basic surface material : Stainless steel
Color of surface : Stainless steel
Color of frame : Stainless steel
Approval certificates : CE
Length electrical supply cord (cm) : 100
Knob Material : Plastic
Sealed Burners : No
Type of pan support : Elongated cast iron pan support
Electrical connection rating (W) : 2
Gas connection rating (W) : 11500
Current (A) : 3
Voltage (V) : 220-240
Frequency (Hz) : 60; 50
Main colour of product : Stainless steel
Energy input : Gas
Gas type : Nat gas H/E/(L) 20 (25) mbar
Alternative gas type : Liquid gas G30,31 28-30/37 mbar
Approval certificates : CE
Plug type : no plug
Required cutout/niche size for installation (in) : x x
Appliance Dimensions (h x w x d) (in) : + x x
Dimensions of the packed product (in) : 6.61 x 31.29 x 23.81
Net weight (lbs) : 28
Gross weight (lbs) : 30
Total number of positions that can be used at the same time : 5
Length electrical supply cord (cm) : 100
Required niche size for installation (HxWxD) : 45 x 560-562 x 480-492
Dimensions of the product (mm) : 45 x 750 x 520
Net weight (kg) : 12.0
Gross weight (kg) : 14.0



4 242004 203506

T27DS59N0
75 CM, GAS HOB WITH INTEGRATED CONTROLS,
STAINLESS STEEL

Features

Design

- Stainless steel

Comfort:

- FlameSelect
- Sword control knobs
- 1-hand ignition
- Cast iron continuous pan supports

Power and size:

- 5 Gas burners
- Wok Burner
- 1 rapid, 2 standard, 1 economy, 1 wok burner
- Left rear: Standard burner 1.75 KW
- Right rear: Rapid burner 3 KW
- Center: Wok burner 4 KW
- Left front: Economy burner 1 KW
- Right front: Standard burner 1.75 KW

Environment+safety:

- Flame failure safety device
- Preset of natural gas (20mbar)

Measurements:

- Power cord lenght 1m

Accessories

- Liquid gas nozzles (28-30/37mbar) included

T27DS59N0
75 CM, GAS HOB WITH INTEGRATED CONTROLS,
STAINLESS STEEL

Dimensioned drawings

