

HP ProDesk 400 G2 Desktop Mini PC



The HP ProDesk 400 Desktop Mini incorporates a high level of business class performance and security with a complete portfolio of accessories³ making it a great value for your growing business.



Powerful performance

- Power through your day with speed and performance. Get the latest in processing technology with your choice of 6th Gen Intel® Core™ processors² and Intel® HD Graphics.

Keep it secure, keep it simple

- Help keep your PC safe with optional security accessories³ to deter theft and a full portfolio of HP security solutions including HP BIOSphere,⁴ HP Client Security Suite,⁵ and new Windows 10 Pro¹ features.

- Windows 10 Pro¹
- 6th Gen Intel® Core™ Processors²

Valuable business-class features

- The HP ProDesk 400 Desktop Mini delivers powerful performance, security, manageability, and value for your growing businesses.

Versatile deployment options

- Deploy the HP ProDesk Desktop Mini into different work environments utilizing innovative mounting, expansion, and security options³ that help you create the right solution for your work space.

Featuring

- Help secure the future of your business. PCs from HP make the most of Windows 10 Pro¹ to protect you from today's security threats and maximize management and productivity features for business.
- The HP ProDesk 400 Desktop Mini endured 120,000 hours of rigorous testing during the HP Total Test Process. This combined with HP temperature control technology helps provide peace of mind in your work environment.
- Keep an available ENERGY STAR® certified PC on and updated with low energy consumption.
- Configure, patch, and update devices from a single console with HP Touchpoint Manager⁶. This plus Windows 10 Pro¹ manageability features, and HP Common Core BIOS, provide business-class manageability for your assets.
- HP BIOSphere⁴ is your security toolkit to safeguard and manage critical business data and devices.
- Select Pro and Elite Displays with integrated VESA mount options, easily create a complete solution with your Mini. Directly mount the Mini to the monitor or stand with optional accessories for a clean connection.
- Increase storage and performance with an optional powerful HP Turbo Drive³ that handles your growing and complex workloads.

HP ProDesk 400 G2 Desktop Mini PC Specifications Table



Form Factor	Mini
Available Operating System	Windows 10 Pro 64 ¹ Windows 10 Home 64 ¹ Windows 8.1 Pro 64 ¹ Windows 8.1 64 ¹ Windows 7 Professional 64 (available through downgrade rights from Windows 10 Pro) ² Windows 7 Professional 32 (available through downgrade rights from Windows 10 Pro) ² Windows 7 Professional 64 ¹ Windows 7 Professional 32 ¹ FreeDOS 2.0
Available Processors³	Intel® Core™ i7-6700T with Intel HD Graphics 530 (2.8 GHz, up to 3.6 GHz with Intel Turbo Boost, 8 MB cache, 4 cores); Intel® Core™ i5-6600T with Intel HD Graphics 530 (2.7 GHz, up to 3.5 GHz with Intel Turbo Boost, 6 MB cache, 4 cores); Intel® Core™ i5-6500T with Intel HD Graphics 530 (2.5 GHz, up to 3.1 GHz with Intel Turbo Boost, 6 MB cache, 4 cores); Intel® Core™ i3-6300T with Intel HD Graphics 530 (3.3 GHz, 4 MB cache, 2 cores); Intel® Core™ i3-6100T with Intel HD Graphics 530 (3.2 GHz, 3 MB cache, 2 cores); Intel® Pentium® G4500T with Intel HD Graphics 530 (3 GHz, 3 MB cache, 2 cores); Intel® Pentium® G4400T with Intel HD Graphics 510 (2.9 GHz, 3 MB cache, 2 cores)
Chipset	Intel® H110
Maximum Memory	32 GB DDR4-2133 SDRAM Transfer rates up to 2133 MT/s
Memory Slots	2 SODIMM
Internal Storage	up to 500 GB SATA (7200 rpm) ⁴ 500 GB (8 GB cache) up to 1 TB (8 GB cache) SATA SSHD ⁴ 120 GB up to 256 GB SATA SSD ⁴ 128 GB up to 512 GB SATA 3D SSD ⁴ 128 GB up to 256 GB HP Turbo Drive SSD (M.2 PCIe) 120 GB up to 256 GB SATA SED SSD ⁴
Available Graphics	Integrated: Intel® HD Graphics ⁶ (Integrated graphics will depend on processor)
Audio	DTS Sound+™ audio management technology, HD audio with Realtek ALC221 codec (all ports are stereo), microphone and headphone front ports (3.5 mm), multi-streaming capable, internal speaker.
Expansion Slots	2 M.2 (One internal M.2 PCIe x1 connector for optional wireless NIC. One internal M.2 PCIe x4 connector for optional SSD.)
Ports and Connectors	Front: 2 USB 3.0; 1 headphone; 1 microphone Back: 2 USB 3.0; 2 USB 2.0; 1 RJ-45; 1 DisplayPort; 1 VGA; 1 serial
Input Devices	HP USB Business Slim Keyboard; HP Wireless Business Slim Keyboard and Mouse; HP Wireless Keyboard and Mouse; HP USB Conference Keyboard; HP USB Keyboard; HP USB Antimicrobial Keyboard; HP USB PS/2 Washable Keyboard and Mouse; HP USB Smart Card (CCID) Keyboard ⁷ HP USB 1000 dpi Laser Mouse; HP USB Mouse; HP USB Hardened Mouse; HP USB Optical Mouse; HP Wireless Laser Mouse ⁷
Communications	LAN: Realtek RTL8111HSH-CG GbE WLAN: Broadcom BCM943228Z 802.11n M.2 Bluetooth™; Broadcom BCM943228Z 802.11n M.2; Intel 3165 802.11ac M.2 Bluetooth™; Intel 3165 802.11ac M.2; Intel 7265 802.11ac M.2 Bluetooth™; Intel 7265 802.11n M.2 Bluetooth™ ⁵
Drive Bays	One 2.5"
Available Software	HP business PCs are shipped with a variety of software titles including: HP Drive Encryption, HP Client Security, HP Security Manager, Microsoft Security Essentials, CyberLink Power DVD BD, Native Miracast support, HP ePrint Driver, HP Recovery Manager. Please refer to this product's quick spec document for a full list of preinstalled software. ^{8,9,10,11}
Security Management	Trusted Platform Module SLB9670TT1.2FW4.40 (TPM) 1.2 Common Criteria EAL4+ certified, field upgradeable to 2.0; SATA port disablement (via BIOS); Serial, parallel, USB enable/disable (via BIOS); Optional USB port disable at factory (user configurable via BIOS); Removable media write/boot control; Power-on password (via BIOS); Setup password (via BIOS); HP Chassis (1 bay) Security Kit; Support for chassis padlocks and cable lock devices; Solenoid hood sensor; Support for port cable cover ^{12,13,14}
Management Features	Intel Standard Manageability (select models); Update BIOS via Cloud or Network (BIOS feature)
Power	65 W 89% efficient, active PFC (external)
Dimensions	175 x 177 x 34 mm
Weight	1.3 kg (Configured with 1 HDD only. Weight varies based on configuration.)
Environmental	Low halogen ¹⁴
Energy Efficiency Compliance	ENERGY STAR® certified configurations available ¹³
Warranty	On-site Warranty: One-year (1-1-1) or three-year (3-3-3) limited warranty delivers one year or three years of on-site, next business day service for parts and labor and includes free telephone support 24 x 7. One-year and three-year onsite and labor are not available in all countries. Service offers terms up to 5 years by choosing a Care Pack. To choose the right level of service for your HP product, visit HP Care Pack Central: www.hp.com/go/cpc

HP ProDesk 400 G2 Desktop Mini PC

Recommended Accessories and Services

HP Desktop Mini Security/Dual VESA Sleeve



Wrap your HP Desktop Mini PC in the HP Desktop Mini Security/Dual VESA Sleeve to securely mount your PC behind your display, position your solution on a wall, and lock it down with the optional HP Ultra-Slim Cable Lock.

Product number: G1K22AA

HP Desktop Mini 500GB Hard Drive I/O Module



Add an extra hard drive to your HP Desktop Mini PC and enable compatibility with your existing and legacy peripherals with the HP Desktop Mini 500GB HDD/I/O Module.

Product number: K9Q82AA

HP Desktop Mini DVD Super Multi-Writer ODD Module



Add a DVD Super-Multi Writer to your HP Desktop Mini PC with HP Desktop Mini DVD Super Multi-Writer ODD Module.¹

Product number: K9Q83AA

HP 3-year Next Business Day Onsite Optional Customer Self Repair Desktop/Workstation Only Hardware Service



Care Pack

Receive 3 years of next business day onsite repair from an HP-qualified technician for your computing device, if the issue cannot be solved remotely. For more information on Care Pack services, please visit www.hp.com/go/cpc.

Product number: UE379E

Messaging Footnotes

- ¹ Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 10 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.microsoft.com>.
- ² Multi-Core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. 64-bit computing system required. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of higher performance.
- ³ Sold separately or as an optional feature.
- ⁴ HP BIOSphere features may vary depending on the PC platform & configuration.
- ⁵ Requires Windows.
- ⁶ HP Touchpoint Manager requires purchase of a subscription and supports Android™, iOS and Windows 7 or higher operating systems and PCs, notebooks, tablets and smartphones from various manufacturers. Not available in all countries see www.hp.com/touchpoint for availability information.

Technical Specifications Footnotes

- ¹ Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 10 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.microsoft.com>
- ² This system is preinstalled with Windows 7 Professional software and also comes with a license and media for Windows 10 Pro software. You may only use one version of the Windows software at a time. Switching between versions will require you to uninstall one version and install the other version. You must back up all data (files, photos, etc.) before uninstalling and installing operating systems to avoid loss of your data.
- ³ Multi-Core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. 64-bit computing system required. Performance will vary depending on your hardware and software configurations. Intel's numbering is not a measurement of higher performance.
- ⁴ For storage drives, GB = 1 billion bytes. TB = 1 trillion bytes. Actual formatted capacity is less. Up to 16 GB (for Windows 7) and up to 36 GB (for Windows 8.1 and 10) of system disk is reserved for system recovery software.
- ⁵ Wireless cards are optional or add-on features and require separately purchased wireless access point and internet service. Availability of public wireless access points limited. The specifications for the 802.11ac WLAN are draft specifications and are not final. If the final specifications differ from the draft specifications, it may affect the ability of this desktop PC to communicate with other 802.11ac WLAN devices.
- ⁶ HD content required to view HD images.
- ⁷ Optional or add-on feature
- ⁸ HP ePrint requires an Internet connection to HP web-enabled printer and HP ePrint account registration (for a list of eligible printers, supported documents and image types and other HP ePrint details, see www.hp.com/go/businessmobileprinting). HP PageLift requires Windows 7 or higher.
- ⁹ Microsoft Security Essentials requires Windows 7 and internet access.
- ¹⁰ Miracast is a wireless technology your PC can use to project your screen to TVs, projectors, and streaming media players that also support Miracast. You can use Miracast to share what you're doing on your PC and present a slide show. Miracast is available for Windows 8 and Windows 10. For more information: <http://windows.microsoft.com/en-us/windows-8/project-wireless-screen-miracast>.
- ¹¹ HP Drive Encryption requires Windows. Data is protected prior to Drive Encryption login. Turning the PC off or into hibernate logs out of Drive Encryption and prevents data access.
- ¹² This product ships with TPM 1.2 with option to upgrade to TPM 2.0. Upgrade utility is expected to be available by the end of 2015 via HP Customer Support.
- ¹³ EPEAT® registered where applicable. EPEAT registration varies by country. See www.epeat.net for registration status by country.
- ¹⁴ External power supplies, power cords, cables and peripherals are not low halogen. Service parts obtained after purchase may not be low halogen.

Sign up for updates

hp.com/go/getupdated

© Copyright 2015. HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. Bluetooth is a trademark of its proprietor used by Hewlett-Packard Company under license. Microsoft and Windows are U.S. trademarks of the Microsoft group of companies. Intel and Core are trademarks of Intel Corporation in the U.S. and other countries. Linux® is the registered trademark of Linus Torvalds in the U.S. and other countries. For DTS patents, see <http://patents.dts.com>. Manufactured under license from DTS Licensing Limited. DTS, the Symbol, & DTS and the Symbol together are registered trademarks, and DTS Sound+ is a trademark of DTS, Inc. © DTS, Inc. All Rights Reserved. All other trademarks are the property of their respective owners.

4AA6-0502EEAP, APJ, December 2015

