

- The SRCOOL2KWM is recommended for wall-mount rack enclosures with ventilated doors and/or side panels
- Cooling air delivered to equipment is lessened in an open frame application. Condenser must be ducted.

## AC Unit for Wall Mount Network Racks - 2,000 BTU, 120V

MODEL NUMBER: **SRCOOL2KWM**



Self-contained 2,000 BTU wall-mount server rack cooling system filters, dehumidifies and cools air and directs it toward equipment stored in wall-mount rack enclosures and network closets with no access to facility air conditioning.

### Description

The self-contained SRCOOL2KWM SmartRack® 120V Wall-Mount Rack Air Conditioner mounts to the top of your wall-mount rack enclosure and delivers 2,000 BTU of close-coupled cooling power to the equipment mounted within the cabinet. The space-saving, energy-efficient SRCOOL2KWM filters and dehumidifies air, then cools the air and directs it through the ventilated front door or side panel of the cabinet. This helps prevent shutdowns and other equipment failures caused by overheating. Recommended for server rooms and other IT environments with limited floor space, the SRCOOL2KWM is more efficient than units that cool an entire room, because the magnetic air scoop attached to the front of the unit pushes the cool air directly toward your equipment. A built-in evaporator eliminates condensation, so no water collection tank or floor drain is required. No plumbing or special circuits are needed, so setup is quick and easy.

The 6-ft. (1.83 m) power cord with NEMA 5-15P plug connects to a standard 120V AC outlet. The SRCOOL2KWM restarts automatically after power failures. The user-friendly control panel lets you schedule unattended shutdowns and restarts, adjust the temperature and set other operating conditions. Adding the optional SRCOOLNET2LX module (sold separately) turns the SRCOOL2KWM into a managed network device via web browser, NMS or telnet. It allows you to monitor and adjust temperature and humidity remotely, access activity logs and receive alerts via email, SMS or SNMP.

### Features

**Compact and Efficient Cooling of Rack Equipment** Mounts to most wall-mount rack enclosures with ventilated door or side panels  
 Close-coupled energy-saving cooling directed at equipment instead of whole room  
 Recommended for IT environments with limited floor space  
 2,000 BTU (0.6 kW) of cooling capacity  
 Prevents equipment shutdowns, malfunctions and failures caused by overheating and temperature fluctuations  
 Eco-friendly R134A refrigerant meets environmental standards

**Convenient Operation** Magnetic front scoop directs cool air through rack's ventilated door or side panel to cool overheated rack equipment  
 Magnetic door panel prevents warm air from entering cabinet  
 Restarts

### Highlights

- Mounts to most wall-mount rack enclosures with ventilated door
- Provides 2,000 BTU (0.6 kW) of cooling capacity
- 6-ft. (1.83 m) power cord with NEMA 5-15P plug
- User-friendly control panel with LCD display and diagnostic LEDs
- Temperature control 63-86 degF
- Supports optional remote management via Ethernet

### Package Includes

- SRCOOL2KWM SmartRack Wall-Mount Server Rack Cooling Unit - 2,000 BTU, 120V
- (2) Adjustable exhaust panels
- Exhaust duct adapter
- Directional output vent
- Exhaust duct
- Extra drainage plug
- Magnetic door panel
- (4) M6 x 16 screws
- (8) M4 x 10 screws
- (4) Self-tapping screws
- Magnetic vinyl
- Mounting brackets
- Owner's manual



automatically after power failures  
Intuitive push-button control panel features LCD display and diagnostic LEDs  
Operates at noise levels comparable to an average office setting  
Temperature control 63-86 degF  
**Optional Remote Management** SRCOOLNET2LX accessory (sold separately) allows you to monitor temperature and humidity, receive alerts, review logs and control settings remotely via SNMP, web, SSH or telnet  
**Simple Installation** 6-ft. (1.83 m) power cord with NEMA 5-15P plug attaches to standard AC outlet  
Built-in evaporator eliminates condensation—no floor drain or water collection tank needed  
Magnetic air scoop attaches to rack enclosure's front door to optimize airflow  
Mounting hardware included

## Specifications

OVERVIEW	
UPC Code	037332199928
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Electrical Consumption	276 Watts Max
Input Connection Type	NEMA 5-15P
Input Frequency	60 Hz
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
COOLING	
Cooling Type	Active
Airflow	Evaporator = 78 CFM / Condenser = 130 CFM
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	2-digit LCD displays numerical temperature readout
Front Panel LEDs	Push-button control panel with multiple LEDs for operational configuration
PHYSICAL	
Color	Black
Form Factors Supported	Wall Mount Rack Mount
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	42.93 x 49.78 x 59.94
Shipping Dimensions (hwd / in.)	16.90 x 19.60 x 23.60
Shipping Weight (kg)	24.04
Shipping Weight (lbs.)	53.00
Unit Dimensions (hwd / cm)	28.19 x 34.29 x 34.29
Unit Dimensions (hwd / in.)	11.1 x 13.5 x 13.5



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Unit Weight (kg)	15.88
Unit Weight (lbs.)	35
<b>ENVIRONMENTAL</b>	
Cooling Capacity	2,000 BTU / 0.6 kW
<b>COMMUNICATIONS</b>	
SNMP Compatibility	SRCOOLNET2 (Optional) remote management accessory for remote monitoring and control
<b>SPECIAL FEATURES</b>	
Dehumidifier	0.83 liters/hr
Compressor Type	Rotary
Refrigerant	R134A
Refrigerant Amount	220G
Amp Draw Nominal	2.47A
Sound Level (Noise)	< 55 DB
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to UL484; CSA 22.2 NO. 117-1970, RoHS; NOM
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>