

FUJITSU Document Scanner

# fi-7600



The fi-7600 is full of thoughtful touches to make clear, accurate scanning easy. It has a large ADF with easy alignment guides, paper straightening technology, and a straight feeding path, all to protect your documents and capture the data correctly and consistently.

<p><b>100</b> Pages per minute</p>	<p><b>Duplex</b> Scans both sides</p>	<p><b>TWAIN &amp; ISIS®</b> Supported</p>	<p>Sizes up to <b>Double Letter</b> 12" x 17" max.</p>	<p> 24-bit Color</p>	<p>Scans  Plastic Cards Flat and embossed</p>	<p>Accepts  Sticky Notes  Taped Receipts  Labels</p>	<p><b>600</b> Optical DPI</p>
--	---	---	--	---	---	---	-----------------------------------



## fi-7600 Production-class ADF document scanner

### Incredible speed and flexibility

- Accurately powers through your documents at up to **200 images per minute**
- High-capacity **300-page Automatic Document Feeder** suitable for continuous scanning
- Accepts a **wide variety of documents**: thin paper, plastic cards, long documents, and envelopes
- Special mode to scan **extra-thick documents**
- Two independent control panels**, one on each side, allow the fi-7600 to fit any workspace

### Protect your paper – and the information on it

- Straight paper path** reduces the stress on your stack of documents during scanning
- Forgot to remove a staple? **Intelligent Sonic Paper Protection** "listens" to paper flowing through the machine and stops if a misfeed occurs, reducing damage to your documents
- Intelligent MultiFeed Function** allows easy manual bypass for sticky notes, taped receipts, and labels that can slow down batch scanning
- Ultrasonic Double Feed Detection** identifies sheets stuck together so you don't miss an image
- Skew Reduction** significantly improves feeding performance and ensures that your whole document gets accurately captured from edge to edge

### Clean up and optimize scans without changing settings in advance

PaperStream IP (PSIP) is a TWAIN/ISIS®-compliant driver with smart features including:

- Assisted Scanning** lets you choose the best image cleanup through visual selection
- Advanced Image Cleanup** corrects the toughest documents, including colored and decorated backgrounds, to improve OCR and reduce rescans
- Auto Color Detection** identifies the best color mode for the document
- Blank Page Detection** removes blank pages automatically
- Front and Back Merge** places two sides of a page into one convenient image

### PaperStream Capture makes scanning fast and easy

Eliminate the learning curve. PaperStream Capture's user-friendly interface allows easy operation from start to finish. Changing scan settings is simple. Indexing and sorting features include barcode, patch code, and blank page separation – making batch scanning a breeze for operators.

### Make it even better with PaperStream Capture Pro

Optional PaperStream Capture Pro software offers an improved feature set with superior front-end capture, image processing, and options for enhanced data extraction and indexing for release.

### Centralized fleet management

Includes Scanner Central Admin Agent to remotely manage your entire fi Series fleet. Effectively allocate your resources based on scan volume, consumables wear, and more.

### Options and Consumables for fi-7600

Item	Part number	Description
Post-scan imprinter (fi-760PRB)	PA03740-D101	Prints a string of characters on document after a scan
Print cartridge for fi-760PRB	CA00050-0262	Lifetime: approx 4,000,000 printed characters
Brake roller	PA03740-K010	Lifetime: approx 250,000 sheets or 1 year
Pick roller	PA03740-K011	Lifetime: approx 250,000 sheets or 1 year

Genuine Fujitsu Consumables are available exclusively from the Fujitsu Document Imaging Store at [store.fcpa.fujitsu.com](http://store.fcpa.fujitsu.com) or call toll-free 800.301.9475



**Fujitsu Computer Products of America, Inc.**  
 1250 East Arques Avenue, Sunnyvale, CA 94085  
 888.425.8228 Sales · 800.626.4686 Technical Support  
[us.fujitsu.com/fcpa](http://us.fujitsu.com/fcpa) · [info@fcpa.fujitsu.com](mailto:info@fcpa.fujitsu.com)

### fi-7600 Technical Specifications

Document feeding method	Automatic Document Feeder (ADF)		
Scanning modes	Simplex/Duplex in Color, Grayscale, or Monochrome		
Image sensor type	Color Charge-Coupled Device (CCD) x 2 (Front x 1, Back x 1)		
Light source	White LED Array x 4 (Front x 2, Back x 2)		
Multi-feed protection	Ultrasonic multi-feed detection sensor Paper detection sensor		
Paper protection	Warped document detection iSOP (Intelligent Sonic Paper Protection)		
Document size	Minimum	2.0" x 2.7" (50.8 x 69 mm)	
	Maximum	12" x 17" (304.8 x 431.8 mm)	
	Long page scanning <sup>1</sup>	12" x 220" (304.8 x 5,588 mm) Up to 200m when using auto page truncation	
Paper weight	Paper	5.3 to 110 lb (20 to 413 g/m <sup>2</sup> )	
	Plastic card	Up to 1.4mm <sup>2</sup>	
Scanning speed <sup>3</sup>	200 or 300 dpi, Letter, Color <sup>4</sup> , Grayscale <sup>4</sup> and Monochrome <sup>5</sup>	Simplex	100 pages/minute
		Duplex	200 images/minute
ADF capacity <sup>6</sup>	300 Sheets (A4/Letter: 20 lb. or 80 g/m <sup>2</sup> )		
Background colors	White / Black (switchable)		
Output resolution <sup>7</sup>	Color (24-bit), Grayscale (8-bit), Monochrome (1-bit)	50 to 600 dpi, 600 dpi optical, 1200 dpi software <sup>8</sup>	
Internal video processing	12-bit (4,096 levels)		
Interface	USB 3.1 Gen 1 / USB 3.0 / USB 2.0 / USB 1.1		
Power requirements	100 to 240 VAC, 50/60 Hz		
Power consumption	Operating: 55 W or less Sleep mode: 1.7 W or less Auto-standby (Off) mode: 0.35 W or less		
Operating environment	Temperature	41° F to 95° F (5° C to 35° C)	
	Relative humidity	20% to 80% (non-condensing)	
Dimensions (WxDxH) <sup>9</sup>	25.2" x 18.7" x 8.4" (640 x 473 x 214 mm)		
Weight	24 lb (11 kg)		
Included in the box	Stacker, ADF paper chute, AC cable & adapter, USB cable, Setup DVD-ROM		
Bundled software (DVD format)	PaperStream IP (TWAIN/ISIS) Driver, 2D Barcode for PaperStream <sup>10</sup> , PaperStream Capture, ScanSnap Manager for fi Series <sup>10</sup> , Scan to Microsoft SharePoint <sup>10</sup> , ABBYY FineReader for ScanSnap <sup>10</sup> , Scanner Central Admin Agent, Software Operation Panel, Error Recovery Guide		
Environmental designations <sup>11</sup>	ENERGY STAR® and RoHS		
Supported operating systems	Windows® 10 (32-bit/64-bit), Windows® 8.1 (32-bit/64-bit), Windows® 7 (32-bit/64-bit), Windows Server® 2016 (64-bit), Windows Server® 2012 R2 (64-bit), Windows Server® 2012 (64-bit), Windows Server® 2008 R2 (64-bit), Windows Server® 2008 (32-bit/64-bit)		
Image processing functions	Multi-image output, Auto color detection, Blank page detection, Dynamic threshold (iDTC), Advanced DTC, SDTC, Error diffusion, De-screen, Emphasis, Halftone, Dropout color, sRGB output, Hole punch removal, Index tab cropping, Split image, De-skew, Edge correction, Streak reduction, Cropping, Dither, Static threshold, Divide long page		

<sup>1</sup> Can scan documents longer than A4 sheets. Documents longer than 34" require using lower resolution (200 DPI or less) <sup>2</sup> Can scan up to 3 flat plastic cards or one embossed card at a time <sup>3</sup> Actual scanning speeds are affected by data transmission and software processing times <sup>4</sup> Using JPEG compression <sup>5</sup> Using TIFF CCITT Group 4 compression <sup>6</sup> Maximum capacity varies depending upon paper thickness <sup>7</sup> Selectable maximum density may vary depending on length of document <sup>8</sup> When scanning at high resolutions (600 dpi or higher), some limitations to document size may apply depending on system environment <sup>9</sup> Including the ADF chute and stacker open to minimum positions and one control panel open <sup>10</sup> Can be downloaded following instructions on Setup DVD-ROM <sup>11</sup> PFU Limited, a Fujitsu company, has determined that this product meets the ENERGY STAR® guidelines for energy efficiency and RoHS requirements (2005/95/EC)



Insist on Genuine Fujitsu Service to keep your scanner running at its best

