



LIGHT BURST



Model: LL-2

LIGHT BURST

Indoor/Outdoor Laser Lights

Never struggle with ordinary lighting again! The LL-2 Spinning Laser Lights is perfect for any holiday! With the equipped dual laser modes, the LL-2 beams cover 3000 sq. ft. Don't worry about water ruining this light! It's water resistant design can stand up against those rainy days! The included indoor stand/outdoor stake makes it easy to place on your front lawn all your neighbors can be jealous of your light show!

Weather Resistant IPX-4

Beams cover over 800 sq. ft.

Extra long outdoor stake included

Indoor stand included

Laser Classification: Class 3R

Maximum Power Output: Less than 1mW

Wavelengths: 532nm/650nm

Operation: Indoor/Outdoor

Operating Temp: -17°F to 100° F

Automatic turns on/off light sensor

9 Laser Modes:

RED+GREEN Light Spinning

RED Light Spinning

GREEN Light Spinning

RED+GREEN Light Spinning+flash

RED+GREEN Light Spinning+flash (fast)

RED+GREEN Light Spinning+flash (faster)

RED+GREEN Light Fixed

RED Light Fixed

GREEN Light Fixed

AC CUL Adapter 110V-240V AV (IPX-4 adapter included)



Accessories:

Power Adapter

Outdoor Stake

Indoor Stand

Manual



- Colors: Black
- Master Carton Qty: 2 PDQ's of 10 each, total 20 in master
- Master Carton Weight: 34.1 LBS
- Master Carton Dimensions: 22.8x13.8x18.3
- PDQ Dimensions: 22.5x13.5x8.8
- Gift Box Dimensions: 6.5x8.3x4.7
- Unit Size: 7.5x8.5x5.5
- Unit Weight: 1.5 LBS
- UPC Gift box: 6 06540 03387 6
- UPC PDQ: 10606540033873
- UPC Master Carton: 20606540033870

