

USB-C to DVI Adapter with USB-A Port and PD Charging, White

MODEL NUMBER: **U444-06N-DU-C**



Adds DVI, USB-A and USB-C PD charging ports to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U444-06N-DU-C USB 3.1 Gen 1 USB-C to DVI Adapter expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for transmitting 1080p video to a large display, adding a thumb drive or other USB peripheral, and powering and charging a PD Charging-compliant mobile device—all at the same time.

With a source device that also supports USB DisplayPort Alternate Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

The plug-and-play U444-06N-DU-C requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

To send HD video to a DVI television, projector or monitor, connect the DVI port to the display using a DVI cable (sold separately). The port supports DVI single-link video resolutions up to 1920 x 1080 (1080p) at 60 Hz and DVI digital transfer rates up to 6.75 Gbps (2.25 Gbps per channel).

The USB-A port accepts USB peripherals, such as a flash drive, mouse, keyboard or printer. It supports fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and is backward compatible with previous USB generations. This dedicated BC 1.2-compliant port provides up to 1.5A of fast-charging power to mobile devices.

The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook or Chromebook) the U444-06N-DU-C is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W).

Features

Turn Your Device's USB-C Port into a Multiport Workstation Ideal for transmitting video to a large display, adding a USB peripheral, and powering and charging a PD Charging-compliant mobile device simultaneously. Plug-and-play operation with no software, drivers or external power required. About the size of a credit card for easy carrying in a pocket, purse or laptop bag.

Highlights

- Supports USB DisplayPort Alternate Mode for transmitting video
- Supports DVI video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- PD Charging port supports power input up to 20V 3A
- BC 1.2-compliant USB-A port provides up to 1.5A of fast-charging power
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with DVI input (DVI port)

Package Includes

- U444-06N-DU-C USB 3.1 Gen 1 USB-C to DVI Adapter
- Owner's manual

Transmit Crystal-Clear 1080p Video to DVI Display Compatible with USB-C or Thunderbolt 3 source devices that support USB DisplayPort Alternate Mode
 Supports DVI single-link video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
 Supports DVI digital transfer rates up to 6.75 Gbps (2.25 Gbps per channel)
 Extends video from your primary display to another
 Duplicates the same video on 2 displays
 Converts a secondary display to your primary display

Connect a USB Peripheral USB-A port accepts flash drives, mice, keyboards, printers and other USB peripherals
 Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
 Backward compatible with USB 2.0 and USB 1.1
 BC 1.2-compliant port provides up to 1.5A of fast-charging power to mobile devices
 Note: Host must support USB OTG (On-the-Go)

Charge a Connected Device USB-C PD port connects to wall charger to power and charge the connected PD Charging-compliant USB-C/Thunderbolt 3 device
 Supports power input up to 20V 3A (60W)
 Note: USB-C PD port does not support Quick Charge (QC).

Built-In Cable with Reversible USB-C Connector Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Specifications

| OVERVIEW | |
|--|--|
| UPC Code | 037332193902 |
| Technology | USB; USB 3.1 (Gen 1); DVI; PD Charging |
| VIDEO | |
| Max Supported Video Resolution | DVI: 1920 X 1080 (1080P) @ 60HZ |
| INPUT | |
| Bus Powered | Yes |
| Product Length (in.) | 6 |
| Product Length (cm.) | 15.24 |
| Product Length (ft.) | 0.5 |
| Product Length (m.) | 0.15 |
| BATTERY | |
| Battery Charging (5V/1.5A Port) | Yes |
| POWER | |
| USB Power Delivery (PD) Charging Support | Yes |
| USB Power Delivery (PD) Charging Specification | 2.0 |
| CHARGING | |
| Charging Ports / Amps | 1.5A; 3A |
| Total Charging Watts | 60 |
| PHYSICAL | |

| | |
|---------------------------------------|---|
| Color | White |
| Cable Outer Diameter (OD) | 3.9mm |
| Cable Jacket Rating | VW-1 |
| Wire Gauge (AWG) | 34/28 |
| Material of Construction | Plastic |
| Shipping Dimensions (hwd / cm) | 2.29 x 11.18 x 14.22 |
| Shipping Dimensions (hwd / in.) | 0.90 x 4.40 x 5.60 |
| Shipping Weight (kg) | 0.18 |
| Shipping Weight (lbs.) | 0.40 |
| Unit Dimensions (hwd / in.) | 0.57 x 3.1 x 1.6 |
| Unit Packaging Type | Box |
| Unit Weight (kg) | 0.04 |
| Unit Weight (lbs.) | 0.08 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 to 113 °F (0 to 45 °C) |
| Storage Temperature Range | 14 to 158 °F (-10 to 70 °C) |
| BTUs | 4.1 BTU/Hr |
| Power Consumption (Watts) | 1.2 |
| Operating Humidity Range | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range | 5% to 90% RH, Non-Condensing |
| Power Provided to Connected Device(s) | 5V 0.9A (4.5W) Output (USB-A), Up to 20V 3A (60W) Input (USB-C) |
| CONNECTIONS | |
| Ports | 3 |
| Side A - Connector 1 | USB C (MALE) |
| Side B - Connector 1 | DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK) |
| Side B - Connector 2 | USB 3.0 A (FEMALE) |
| Side B - Connector 3 | USB Type-C (FEMALE) |
| Connector Plating | Nickel |
| FEATURES & SPECIFICATIONS | |
| HDCP Specification | 1.3 |
| USB Specification | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) |
| Driver Required | No |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| STANDARDS & COMPLIANCE | |
|-------------------------------------|-------------------------|
| Certifications | CE, FCC, RoHS, REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>