

# Product data sheet

Specifications



## Rack PDU, Basic, 0U/1U, 100-240V/20A, 220-240V/16A, (7) C13, (2) C19

AP6120A

### Overview

Lead time Usually in Stock

### Main

Product or Component Type PDU  
PDU Type Basic  
Provided Equipment Installation guide  
Safety guide

### Complementary

Input Voltage 100 V  
120 V  
200 V  
208 V  
230 V  
240 V

Height 1.7 in (4.4 cm)

Width 15.3 in (38.8 cm)

Output Voltage 100 V  
120 V  
200 V  
208 V  
230 V  
240 V

Depth 3.7 in (9.3 cm)

Net Weight 3.44 lb(US) (1.56 kg)

mounting location Front  
Rear

Mounting preference No preference

Input Plug Type IEC 60320 C20

Mounting Mode Not rack-mountable

Rack units 1U

USB compatible No

Mounting position Horizontal

Line Rated Current 16 A

Acceptable Input Voltage 100...240 V

Max line current 20 A

Input current limits 20 A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

<b>Load Capacity</b>	2300 VA
<b>Input Frequency</b>	50/60 Hz
<b>Outlet type and quantity</b>	7 IEC 60320 C13 2 IEC 60320 C19

---

## Environment

---

<b>Product Certifications</b>	cUL Listed CE EAC IRAM PSE UL Listed VDE
-------------------------------	--

## Ordering and shipping details

---

<b>GTIN</b>	731304327851
-------------	--------------

## Packing Units

---

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	8.3 in (21 cm)
<b>Package 1 Width</b>	3.0 in (7.6 cm)
<b>Package 1 Length</b>	17.2 in (43.6 cm)
<b>Package 1 Weight</b>	4.45 lb(US) (2.02 kg)
<b>SCC14</b>	50731304327856

## Contractual warranty

---

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

## Resource performance

Energy Efficient Product

---

Take-Back Program Available

---

## Well-being performance

Mercury Free

---

Rohs Exemption Information Yes

---

## Certifications & Standards

Reach Regulation REACH Declaration

---

Eu Rohs Directive Compliant with Exemptions

---

Environmental Disclosure Product Environmental Profile

---

Circularity Profile End of Life Information

---