

Product data sheet

Specifications



APC NetShelter Basic Rack PDU,
0U, 1PH, 3.3kW, 100-240V 20A or
200-240V 16A, 13 C13 outlets,
C20 inlet

AP6020A

Overview

Presentation Reliable rack power distribution designed to increase manageability and efficiency in the data center. The output and input connections are (13) C13. Real-time remote monitoring of connected loads. User-defined alarms warn IT and data center managers of potential circuit overloads to prevent accidental power loss to critical equipment.

Lead time Usually in Stock

Main

Color Black

Product or Component Type PDU

PDU Type Basic

Provided Equipment Installation guide
Safety guide

Complementary

Input Voltage 100 V
120 V
200 V
208 V
230 V
240 V

Height 15.3 in (38.8 cm)

Width 1.7 in (4.4 cm)

Depth 3.7 in (9.3 cm)

Net Weight 3.3 lb(US) (1.5 kg)

mounting location Front
Rear

Mounting preference Lower

Input Plug Type IEC 60320 C20

Mounting Mode Not rack-mountable

Rack units 1U

USB compatible No

Mounting position Horizontal

Line Rated Current 16 A

Acceptable Input Voltage 100...240 V

Max line current 20 A

Input current limits 20 A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Load Capacity	3300 VA
Input Frequency	50/60 Hz
Outlet type and quantity	13 IEC 60320 C13

Environment

Product Certifications	cUL Listed CE EAC IRAM PSE UL Listed VDE
------------------------	--

Ordering and shipping details

GTIN	731304327806
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.2 in (43.6 cm)
Package 1 Width	3.0 in (7.6 cm)
Package 1 Length	8.3 in (21 cm)
Package 1 Weight	4.45 lb(US) (2.02 kg)
SCC14	10731304327803

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)