

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Position a 200A fuse link less than 18 in. from the battery in the positive line to protect against highcurrent draw that may occur during inverter failure.

1250W PowerVerter APS 12VDC 120V Inverter/Charger with Auto Transfer Switching, 2 Outlets

MODEL NUMBER: APS1250



Portable dual-outlet power source for power applications, such as power tools and computers, as a vehicle inverter, standalone AC power source or extended-run UPS. Ideal for RVs, fleet vehicles and emergency vehicles.

Features

Reliable Power for Mobile, Emergency and Remote Sites

- Generates safe, stable, computer-grade 120V AC power from 12V battery bank
- Ideal for powering tools, saws, motors, pumps, portable lighting, appliances and computer equipment in heavy-load conditions
- Designed for easy installation in RVs, over-the-road trucks, fleet vehicles and emergency vehicles
- Functions as a vehicle inverter, standalone AC power source or extended-run UPS
- Features 2 front NEMA 5-15R outlets
- · Unlimited runtime with variety of user-supplied batteries

Meets Normal and Peak Power Demands

- 1250W of continuous power
- 1850W of reserve power up to 1 hr.
- 2500W of peak power up to 10 sec. to accommodate surge power demands during equipment startup and cycling
- Automatic overload detector, built-in cooling fan and resettable AC circuit breaker protect unit from damage

Highlights

- Delivers clean 120V AC power from AC or DC power source
- 1250W continuous output power; 2500W peak power
- Auto-transfer switching option for UPS operation
- Protects against blackouts, surges and EMI/RFI line noise
- Rugged polycarbonate housing resists moisture and impact

Package Includes

- APS1250 1250W PowerVerter
 APS 12V DC 120V AC
 Inverter/Charger
- Owner's manual



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Automatic Transfer Switching

- Transfer relay switches to inverter power during blackout in 16.6 ms
- 3-position switch enables Auto, Charge Only or System Off mode
- DIP switches configure high and low voltage auto-transfer

3-Stage 30A Battery Charger

- Serves as battery charger when external 120V AC power is supplied and powering connected equipment
- Protects battery from overcharging and overdischarging
- · Low-battery protection prevents excessive battery depletion
- DIP switches configure wet/gel charging profiles

Optional Remote Control Capability

 RJ45 communication port allows connection of optional remote control module, such as Tripp Lite's APSRM4

Front-Panel LEDs

• Indicate load level, battery charge level, shutdown status and system fault status

Rugged Polycarbonate Housing

- · Resists moisture, vibration and impact
- Built-in mounting feet for installation on any rigid horizontal surface
- · Grounding lug connects unit to earth ground or vehicle grounding system
- Built-in 6-ft. (1.83 m) AC power cord with NEMA 5-15P plug connects to AC power source

Specifications

OVERVIEW		
UPC Code	037332121653	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	DC INPUT: Requires 12VDC input source capable of delivering 125A for the required duration (when used at full continuous capacity - DC requirements increase during OverPower and DoubleBoost operation). For automotive applications, professional hardwire installation with 225A minimum battery system fusing is recommended. AC INPUT: 120VAC	
Maximum Input Amps / Watts	DC INPUT: Full continuous load - 127A at 12V DC. AC INPUT: 12 amps at 120VAC with full inverter and charger load (6.3A max charger-only)	
Input Connection Type	DC INPUT: Set of 2 DC bolt-down terminals. AC INPUT: NEMA 5-15P input plug	
Voltage Compatibility (VAC)	120	
Voltage Compatibility (VDC)	12	



ουτρυτ		
Frequency Compatibility	60 Hz	
Pure Sine Wave Output	No	
Output (Watts)	1250	
Nominal Output Voltage(s) Supported	120V	
Output Receptacles	(2) 5-15R	
Continuous Output Capacity (Watts)	1250	
Peak Output Capacity (Watts)	2500	
Output Voltage Regulation	LINE POWER (AC): Maintains 120V nominal sine wave output from line power source. INVERTER POWER (AC): Maintains PWM sine wave output voltage of 120 V AC (+/-5%).	
Output Frequency Regulation	60 Hz (+/- 0.3 Hz)	
Overload Protection	Includes 8A input breaker dedicated to the charging system and 12A output breaker for AC output loads	
BATTERY		
Expandable Battery Runtime	Runtime is expandable with any number of user supplied wet, gel or SLA batteries	
Expandable Runtime	Yes	
DC System Voltage (VDC)	12	
Battery Pack Accessory (Optional)	<a class="productLink" href="//www.tripplite.com/12VDC-Sealed-Maintenance-Free-Battery-All-Inverter-
Chargers-12VDC-Battery-Connections~98-121">98-121 sealed lead acid battery (optional)	
Battery Charge	30A max, 3 step, float for long term maintenance	
USER INTERFACE, ALERTS & CONTROLS		
Front Panel LEDs	Set of 6 LEDs offer continuous status information on load percentage (6 levels reported) and battery charge level (7 levels reported). See manual for sequences.	
Switches	3 position on/off/remote switch enables simple on/off power control plus "auto/remote" setting that enables distant on/off control of the inverter system when used in conjunction with optional <a <br="" class="productLink">href="//www.tripplite.com/Remote-Control-Module-Tripp-Lite-PowerVerter-Inverters-Inverter- Chargers-APSRM4">APSRM4 APSRM4 accessory when used in inverter mode. In AC uninterruptible power mode, auto/remote setting enables automatic transfer from line power to battery power - to maintain continuous AC power to connected loads.	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	450	
PHYSICAL		
Cooling Method	Multi-speed fan	
Form Factors Supported	Mounting slots enable permanent placement of inverter on any horizontal surface (see manual for additional mounting information)	
Material of Construction	Polycarbonate	
Receptacle Color	Black	
Shipping Dimensions (hwd / cm)	32.00 x 26.92 x 25.91	



[
Shipping Dimensions (hwd / in.)	12.60 x 10.60 x 10.20
Shipping Weight (kg)	11.02
Shipping Weight (lbs.)	24.30
Unit Dimensions (hwd / cm)	17.78 x 22.23 x 22.86
Unit Dimensions (hwd / in.)	7 x 8.75 x 9
Unit Weight (kg)	10.52
Unit Weight (Ibs.)	23.2
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
LINE / BATTERY TRANSFER	
Transfer Time (Line Power to Battery Mode)	16.6 milliseconds (typical - compatible with many computers, servers and networking equipment - verify transfer time compatibility of loads for UPS applications)
Low Voltage Transfer to Battery Power	In AC "auto" mode, inverter/charger switches to battery mode as line voltage drops to 75V (user adjustable to 85, 95, 105V - see manual)
High Voltage Transfer to Battery Power	In AC "auto" mode, inverter/charger switches to battery mode as line voltage increases to 135V (user adjustable to 145 - see manual)
WARRANTY	
Product Warranty Period (U.S. & Canada)	1-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies