

RDH-370



Remove unwanted moisture from the air by using the Royal Sovereign 70-Pint Dehumidifier.



Highlights

- **Comfort:** Adjustable humidistat with three fan speeds.
- **Convenient Maintenance:** Air filter is removable and washable.
- **Drainage Options:** Choose between manual or continuous drainage.
- **User-Friendly:** Digital controls to manage air quality.
- **Portability:** Includes attachable easy-gliding caster wheels.
- **Eco-Friendly:** Uses R410A refrigerant and is Energy Star certified.

Perfect solution for drier, more comfortable environment!

RDH-370



MULTIPLE FAN
SPEEDS

BUCKET OR
DRAIN HOSE

ENERGY STAR
CERTIFIED



SPECIFICATIONS

Dehumidifying Capacity 70 pints per day

Bucket Size 33L / 8.7 Gal.

Built in Pump No

Direct Drain Option Yes

Refrigerant R410A

Certification Energy Star

Dimensions 16"W x 11.2"D x 24.5"H
406 mm x 284 mm x 622 mm

Weight 46.2 lbs. / 20.96 kgs

Individual Carton Dimensions 17"W x 13.75"D x 26"H
432 mm x 349 mm x 660 mm

Individual Carton Weight 50.7 lbs. / 22.99 kgs

Individual Carton UPC Code 849023090342

Master Carton Dimensions 17"W x 13.75"D x 26"H
432 mm x 349 mm x 660 mm

Master Carton Weight 50.7 lbs. / 22.99 kgs

Master Carton Count 1

Master Carton UPC Code 50849023090347

1 Year Warranty