


## MULTI-VOLTAGE RELAY MODULE

**0E-FRLY12V7**  
**SUITABLE FOR FIRE ALARM AND  
OTHER APPLICATIONS**



0E-FRLY12V7 is an encapsulated multi-voltage relay suited to applications requiring a remote relay for control or status feedback. It includes long flying leads selectable for the input control voltage to be applied. A red LED indicates relay coil is energized. Applications include Fire Alarm Control, security systems, HVAC, temperature control, lighting systems and energy management. 0E-FRLY12V7 is UL 864 listed for Fire Alarm Control Equipment. Includes mnting./wiring hardware.

- VOLTAGE INPUT: 12VDC, 24VDC
- CURRENT DRAW: @12VDC = 28mA;  
@24VDC = 24mA
- POLARIZED COIL INPUT: DC CONTROL INPUT ONLY
- CONTACTS: DRY FORM C SPDT
- CONTACT RATINGS: @5VDC = 250 $\mu$ A/ 0.35 P.F.;  
@24VDC = 7A/ 0.35 P.F.; @120VAC = 7A
- RED LED INDICATES RELAY COIL IS ENERGIZED
- WIRE TYPE: SIX (6) 12" 18AWG FLYING LEADS
- OPER. TEMP: 32°F TO 120°F (0°C TO 49°C), RH 93%

PART #: 0E-FRLY12V7

UPC: 811914027041

LENGTH: 1.5" (CASE ONLY)

WIDTH: 1.0" (CASE ONLY)

HEIGHT: 0.7" (CASE ONLY)

WEIGHT: 2 OUNCES

SIGNALING



UL 864 LISTED  
FIRE ALARM CONTROL EQUIPMENT  
**S35914**

CFSM LISTED  
MEA ACCEPTED