

ThinkVision T22i-10 MONITOR

DISPLAYING THE PERFECT COMBINATION OF VERSATILITY AND PRODUCTIVITY.



Lenovo[™]

DISPLAYS DESIGNED TO PERFORM IN ANY BUSINESS ENVIRONMENT

The Lenovo™ ThinkVision® T22i-10 is a professional collection of next-generation displays perfectly suited for all your corporate endeavors. Delivering an immersive, borderless Full-HD experience, you're guaranteed a bright start to the day, Monday through Friday. Moreover, it's safe to say your office is probably full of cables... well, plugging-in has never been easier with this series' available VGA, DisplayPort™, and HDMI™ ports. Additionally, 4 USB ports matched with an audio port maximize your productivity with complete access to your favorite accessories. So, whether you're crunching numbers in a spreadsheet, putting together a presentation, or simply firing an email, you can expect a brighter and more productive 9 to 5 with one of our these models.

WHY YOU SHOULD BUY THE LENOVO THINKVISION T22i-10 MONITOR




Display of brilliance

With vivid FHD resolution and dynamic contrast, T22i-10 ensure exceptional visual experience across the full screen with no color distortion. You can also enjoy a clean look and seamless views across multi-monitor displays with near-edgeless design.



Stylishly versatile

A modernized design paired with a full functioning stand ensures your display sports an executive look regardless of whether you swivel, tilt, pivot, or lift.



Productivity at its finest

Multi-port connectivity ensures you're always connected whether you're displaying across multiple screens, rapidly charging your mobile, or dialing into a conference call.

THE LENOVO THINKVISION T22i-10 MONITOR IS BEST SUITED FOR

1

Business professionals who require the clarity and versatility of a professional-grade monitor.

2

Organizations that value a monitor with professional performance and versatility to suit any environment.

3

Anyone that requires a high-performance monitor with productivity-enhancing features.



ThinkVision T22i-10 MONITOR



SPECIFICATIONS

Lenovo

DISPLAY		DIMENSIONS (W x D x H)	
Panel Size	21.5" Wide	Size Packed (mm)	577 x 378 x 191
Panel Type	IPS	(inches)	22.7" x 14.9" x 7.5"
Backlight	WLED	Size Unpacked with Stand (mm)	489.7 x 251.9 x 357.6
Resolution (H x V)	1920 x 1080	(inches)	19.28" x 9.92" x 14.08"
Aspect Ratio	16:9	Size Monitor Head Only (mm)	489.7 x 43.5 x 297
Anti-Glare	Yes	(inches)	19.28" x 1.71" x 11.69"
Borderless Screen	Yes	Stand Base Footprint Area (mm)	240 x 240
Screen Dimensions (W x H)		(inches)	9.45" x 9.45"
(mm)	476.064 x 267.786	Weight	Starting at 16.36 lbs (7.42 kg)
(inches)	18.74" x 10.54"	Packed	Starting at 10.85 lbs (4.92 kg)
Maximum Brightness (Typical)	250 cd/m ²	Unpacked	Starting at 6.94 lbs (3.15 kg)
Viewing Angle (H/V at CR 10:1)	178°/178°	Monitor Head Only	
Contrast Ratio (Typical)	1000:1		
Dynamic Contrast Ratio	3M:1		
Pixel Pitch (mm)	0.248 x 0.248		
Color Gamut NTSC (CIE 1931)	72%		
Color Support (Typical)	16.7 Million		
Response Time	4/6/14 ms		
CONNECTIVITY		POWER CONSUMPTION	
Video Input Signals	VGA + HDMI™ 1.4 + DisplayPort™ 1.2	Typical	20 W
Video Cables Supplied (Length)	1.8 m	Maximum	55 W
Audio	Audio-Out	Sleep-Mode	<0.5 W
OSD Languages	English, French, German, Spanish, Italian, Japanese, Simplified Chinese, Russian	Switch Off-Mode	<0.5 W
		Power Supply	Internal
		Power Voltage	100 VAC - 240 VAC
MECHANICAL		COMPLIANCE	
Tilt Angle (Front / Back)	-5° / 30°	Arsenic-Free Glass	Yes
Swivel Angle (Left / Right)	+/45°	PVC-Free	Yes; Without Cable
Lift (mm / inches)	110 / 4.33"	Mercury-Free	Yes
Pivot	-90° / 90°	EPEAT™	Gold
Cable Management	Yes	ENERGY STAR® Rating	7.0
Kensington® Lock	Yes	TCO	7.0
VESA® Mounting	Yes (100 mm)	TCO Edge	2.0
Bezel Color	Raven Black	RoHS (EU 2002/95/EC)	Yes
Bezel Width		China Energy Efficiency Standard	Tier 2
Top (mm / inches)	2 / 0.08"	Windows Certification	Windows 7 / Windows 10
Bottom (mm / inches)	21.4 / 0.84"		
Sides (mm / inches)	2 / 0.08"		



WWW.LENOVO.COM

Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkServer, ThinkVantage and ThinkVision. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Ultrabook, Celeron, Celeron Inside, Core Inside, Intel, Intel Logo, Intel Atom, Intel Atom Inside, Intel Core, Intel Inside, Intel Inside Logo, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, Xeon, Xeon Phi, and Xeon Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product and service names may be trademarks or service marks of others. Battery life (and recharge times) will vary based on many factors including system settings and usage. Visit www.lenovo.com/lenovo/us/en/safecom/ periodically for the latest information on safe and effective computing. ©2017 Lenovo. All rights reserved.