

## USB-C to VGA Adapter Cable, 6 ft. (1.83 m)

MODEL NUMBER: **U444-006-V**



Connects your existing VGA TV, monitor or projector to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, smartphone or PC.

### Features

#### Connects a VGA Display to Your USB-C or Thunderbolt 3 Device

- Compatible with USB-C or Thunderbolt 3 source devices that support USB DisplayPort Alternate Mode
- Ideal for giving video presentations, editing multiple documents or streaming video for digital signage
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps

#### Common Applications

- Extends video from your primary display to another
- Duplicates the same video on 2 displays
- Converts a secondary display to your primary display

#### Crystal-Clear 1080p Video

- Supports HD video resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Supports 36-bit Deep Color (12 bits per channel)

#### Reversible USB-C Connector

- Fumble-free reversible USB-C plug connects in either direction for quick connection every time

#### Premium Construction

- Gold-plated connectors and contacts for maximum conductivity and minimum data loss
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Integral strain relief helps cable and connectors move freely without stress or cracking
- Durable PVC jacket designed to last a long time

### Highlights

- Supports USB DisplayPort Alternate Mode for transmitting video
- Supports HD video resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with VGA input

### Package Includes

- U444-006-V USB 3.1 Gen 1 USB-C to VGA Adapter Cable (M/M), 6 ft.



#### Ready for Instant Use

- Plug-and-play operation with no software, drivers or external power required
- 6 ft. length easy to manage in crowded environments
- Backward compatible with non-1080p displays

## Specifications

OVERVIEW	
UPC Code	037332202512
Technology	USB; USB 3.1 (Gen 1); VGA/SVGA
VIDEO	
Max Supported Video Resolution	VGA: 1920 X 1200 (1080P) @ 60HZ
INPUT	
Bus Powered	Yes
Product Length (in.)	72
Product Length (cm.)	182.88
Product Length (ft.)	6
Product Length (m.)	1.83
BATTERY	
Battery Charging (5V/1.5A Port)	No
PHYSICAL	
Color	Black
Cable Jacket Rating	VW-1
Cable Length (ft.)	6
Cable Length (m)	1.828
Material of Construction	PVC, ABS
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.10
Shipping Weight (lbs.)	0.23
Unit Packaging Type	Polybag
Unit Weight (kg)	0.10



Unit Weight (lbs.)	0.22
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	2.1 BTU/Hr
Power Consumption (Watts)	0.6
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HD15 (MALE)
Connector Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Cable Style	Passive
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>