

## USB-A Male to USB-A Male Cable, SuperSpeed, 3.0/3.1, Industrial, 13 ft. (4 m) - IP67, Shielded, TAA

MODEL NUMBER: U325-013-IND



Connects high-speed USB 3.0 equipment in industrial environments that require protection against dust and moisture.

### Features

#### Shielded USB 3.0 Cable Recommended for Outdoor or Harsh Indoor Environments

This 13-foot (four-meter) industrial-grade USB-A to USB-A cable is ideal for connecting high-speed USB 3.0 equipment—for instance, a computer or server to a patch bay or industrial hub—in outdoor applications and other areas where protection from harsh elements is essential. The shielded cable and USB-A connectors are designed to withstand dust, debris and moisture that could threaten your IT infrastructure. Included dust caps protect the connectors when not in use.

#### IP67 Rating Denotes Resistance to Dust and Water

The IP67 rating means the USB Type-A to USB Type-A cable is not only 100% protected against dust, but also able to endure immersion in one meter of water for up to 30 minutes with no damage or decline in performance, making the cable ideal for basement applications. For applications that require IP67 protection, use the industrial cable with a Tripp Lite N206-SB01-IND surface-mount box and U325-000-IND bulkhead coupler. If only IP44 protection against splashing water from all directions is required, pair the cable with a N206-FP01-IND, N206-FP02-IND or N206-FP04-IND metal wall plate and the U325-000-IND coupler.

#### Heavy Shielding Protects Your Network Data from Destructive Line Noise

The USB-A to USB-A cable's shielded construction helps fight against EMI/RFI line noise that interferes with your signal and can distort or destroy data. Electromagnetic interference and radio frequency interference can be created by electric motors, power cables, welding equipment and other heavy machinery frequently found in industrial applications.

#### Supports USB 3.0 Speeds for a Faster, More Efficient Signal

This USB-A male to USB-A male cable supports USB 3.0 data transfer rates up to 5 Gbps—10 times faster than USB 2.0. Its bi-directional data interface allows data to flow both directions simultaneously, increasing theoretical bandwidth by 10 times for efficient power and little wait-time. The U325-013-IND is also backward compatible with previous USB generations.

#### TAA-Compliant for GSA Schedule Purchases

The U325-013-IND is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

### Highlights

- Built to protect process control and other USB 3.0 applications in harsh environments
- IP67-rated to resist dust and endure immersion in 1 m of water up to 30 min.
- Supports USB 3.0 data transfer rates up to 5 Gbps—10x faster than USB 2.0
- Disperses EMI/RFI line noise that can destroy data and affect equipment performance
- Complies with Federal Trade Agreements Act standards for GSA Schedule purchases

### Applications

- Connect process control, industrial production and diagnostic systems in factories, warehouses and other dusty environments
- Provide USB 3.0 connectivity in outdoor environments susceptible to rain, such as a stadium or outdoor arena
- Set up outdoor digital signage at malls, theaters and bus stops

### Package Includes

- U325-013-IND USB-A Male to USB-A Male Cable, SuperSpeed, 3.0/3.1, Industrial, 13 ft. (4 m)
- Quick Start Guide



#### Lifetime Warranty

The U325-013-IND is backed by a lifetime warranty, ensuring reliability and performance.

## Specifications

OVERVIEW	
UPC Code	037332209566
Technology	USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
INPUT	
Cable Length (ft.)	13
Cable Length (m)	4
Cable Length (in.)	156
Cable Length (cm)	396
PHYSICAL	
Wire Gauge (AWG)	28/24
Shipping Dimensions (hwd / in.)	10.70 x 8.00 x 0.50
Shipping Dimensions (hwd / cm)	27.18 x 20.32 x 1.27
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
Material of Construction	PVC
Color	Black
Cable Outer Diameter (OD)	6.2
ENVIRONMENTAL	
Operating Temperature Range	-4 to 176 F (-20 to 80 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Relative Humidity	20% to 80% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	



USB Specification	USB 3.0 (up to 5 Gbps)
<b>CERTIFICATIONS</b>	
Certifications	ROHS Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>