

Serie | 2 Dishwashers

SMS25AW00G white
ActiveWater Dishwasher 60cm
Freestanding,



A++

- **ExtraDry:** extra drying option for difficult-to-dry loads.
- **Height Adjustable Top Basket:** offers extra space, especially for tall dishes.
- **Glass 40°C:** protective program for gently cleaning and drying glasses.

Technical Data

Cleaning performance :	A
Water consumption (l) :	9.5
Total annual energy consumption (kWh) 220 days :	198
Total annual water consumption (l) 220 days :	2090
Construction type :	Free-standing
Removable work top :	Yes
Door panel options :	Not possible
Height of removable worktop (mm) :	815
Height of the product (mm) :	845
Adjustable feet :	Yes - front only
Maximum adjustability feet (mm) :	20
Adjustable plinth :	No
Net weight (kg) :	49.0
Gross weight (kg) :	50.0
Connection rating (W) :	2400
Current (A) :	13
Voltage (V) :	220-240
Frequency (Hz) :	60; 50
Length of electrical supply cord (cm) :	175
Plug type :	GB plug
Length inlet hose (cm) :	165
Length outlet hose (cm) :	190
Hidden heating element :	Yes
:	Childlock appliance
Water softener (kWh) :	Yes
Top basket type :	low
Adjustable upper basket :	Single
Upper rack cup shelf :	0
Bottom basket type :	low
3rd Rack :	None
Silverware Basket :	Standard
Optional accessories :	
SGZ1010, SMZ2014, SMZ5000, SMZ5001, SMZ5002, SMZ5300	
Included accessories 2 :	baking-sheet spray head grey
Number of place settings :	12
Color / Material body :	White
Color / Material top :	White
Brand :	Bosch
Product name / Commercial code :	SMS25AW00G
Number of place settings :	12
Energy efficiency class - NEW (2010/30/EC) :	A++
Energy consumption annual (kWh/annum) - NEW (2010/30/EC) :	258
Energy consumption (kWh) :	0.90
Power consumption in left-on mode (W) - NEW (2010/30/EC) :	0.10
Power consumption in off-mode (W) - NEW (2010/30/EC) :	0.10
Water consumption annual (l/annum) - NEW (2010/30/EC) :	2660
Drying performance :	A
Reference programme :	Eco
Total cycle time of reference programme (min) :	210
Duration of the left-on mode - NEW (2012/30/EC) (min) :	0
Noise level (dB(A) re 1 pW) :	48
Installation type :	Built-under
Panel ready :	No
Connection rating (W) :	2400
Current (A) :	13
Voltage (V) :	220-240
Frequency (Hz) :	60; 50
Energy Star Qualified :	1/2
NSF certified :	No

Serie | 2 Dishwashers

SMS25AW00G white **ActiveWater Dishwasher 60cm** **Freestanding,**

Performance

- Energy Efficiency Class: A++
- Capacity: 12 place settings
- Energy consumption in Eco 50 programme: 258 kwh per year, based on 280 standard cleaning cycles
- Water consumption in Eco 50 programme: 2660 litres per year, based on 280 standard cleaning cycles
- Programme time in Eco 50 programme: 210 minutes
- A rated performance for washing and A for drying
- Noise level dB (A) re 1pW: 48 dB
- Noise level (silence programme): not available(A) re 1 pW
- Power consumption off-mode / left-on mode: 0.1 W / 0.1 W

Programmes/functions

- 5 programmes: Intensive 70 °C, Eco 50 °C, Glass 40 °C, Quick 45 °C, Pre rinse
- 2 special options: VarioSpeed Plus, Extra Dry

Flexible design elements

- Vario basket system
- Height adjustable top basket when empty
- 2 foldable plate racks in bottom basket
- 2 foldable cup shelves in top basket

Innovations and technology

- Heat exchanger - Hygienic and efficient drying
- DosageAssist detergent dispenser
- EcoSilence BLDC drive
- Automatic detergent detection
- AquaSensor III, Load Sensor

Design features

- Electronic time delay: 1-24 hours with remaining programme time indicator (min), water inlet indicator
- Leak protection system
- LED salt refill indicator, LED rinse aid refill indicator
- Self-cleaning filter system with 3 piece corrugated filter
- Child safety - Childproof door lock
- Dimensions (HxWxD): 84.5 x 60 x 60cm
- Efficiency information relates to the Eco 50 programme. This programme is suitable for cleaning normally soiled tableware and is the most efficient programme in terms of combined energy and water consumption.