

iQ500

WM14T690GB

Front loading automatic washing machine



A+++

iSensoric Washing Machine with intelligent i-Dos automatic dosage and multiTouch LED Display.

- ✓ The precise i-Dos automatic dosing system measures the detergent for you and helps you save water and detergent.
- ✓ With a digital multiTouch Display, this washing machine can be operated intuitively and with highest precision.
- ✓ With the option speedPerfect, get perfect washing results in up to 65% less time.
- ✓ Intelligent, durable and quiet iQdrive motor for highly effective and efficient laundry care.
- ✓ A+++ -30%: washes 30% more efficient than the requirement for energy efficiency class A+++.

Features

Technical Data

Installation type : Freestanding
 Height of removable worktop (mm) : 848
 Dimensions of the product (mm) : 848 x 598 x 590
 Net weight (kg) : 73.0
 Connection rating (W) : 2300
 Current (A) : 10
 Nominal power (kW) : 220-240
 Frequency (Hz) : 50
 Approval certificates : CE, VDE
 Length of electrical supply cord (cm) : 160
 Washing performance class : A
 Door opening : Left
 Wheels : No
 EAN code : 4242003804162
 Capacity (kg) : 9.0
 Energy efficiency : A+++: exceptionally efficient
 Energy consumption annual (kWh/annum) - NEW (2010/30/EC) : 152
 Power consumption in off-mode (W) - NEW (2010/30/EC) : 0.12
 Power consumption in left-on mode - NEW (2010/30/EC) : 0.43
 Water consumption annual (l/annum) - NEW (2010/30/EC) : 11220
 Spin drying performance class : B
 Max. spin speed (rpm) : 1379
 Average washing time cotton 40C (partial load) - NEW (2010/30/EC) : 270
 Average washing time cotton 60C (full load) (min) - NEW (2010/30/EC) : 275
 Average washing time cotton 60C (partial load) - NEW (2010/30/EC) : 270
 Duration of the left-on mode - NEW (2012/30/EC) (min) : 15
 Noise level washing (dB) : 49
 Noise level spinning (dB) : 75
 Installation type : Freestanding



4 242003 804162

Optional accessories

WZ20490 Platform with pull-out
 WZ10130 Extension for cold water inlet /Aquastop
 WX975600 Floor securing component

iQ500

WM14T690GB

Front loading automatic washing machine

Features	
<ul style="list-style-type: none">• iSensoric• Intelligent Dosing System <p>Performance</p> <ul style="list-style-type: none">• Energy efficiency class: A+++• Capacity: 9 kg• Maximum spin speed: 1400 rpm• B spin class• Energy consumption :152 kWh per year, based on 220 standard washing cycles• -30% more economical (152kWh/year) than the standard value (217 kWh/year)• Energy consumption: standard 60 °C cotton programme 0.92 kwh full load and 0.6 kwh partial load and 40 °C cotton programme 0.42 kwh partial load• Water consumption 11220 litres per year, based on 220 standard washing cycles• Cottons 60 Eco and Cottons 40 Eco are the standard washing programmes to which the information in the label relates. These programmes are suitable to clean normally soiled cotton laundry and are the most efficient programmes in terms of combined energy and water consumption.• Programme time:60 °C cotton programme 275 min at full load 270 min at partial load and 40 °C cotton programme 270 min partial load• Duration of the left-on mode: 15 min• Drum volume: 65 litres• Weighted power consumption off-mode / left-on mode: 0.12 W / 0.43 W• Noise level washing : 49dB (A) re 1pW: Noise level spinning:75dB (A) re 1 pW• Noise level spinning:75dB (A) re 1 pW: <p>Programmes/functions</p> <ul style="list-style-type: none">• Special programmes: textile guard re-proofing programme, shirts/blouses, mixed fabrics, automatic, automatic soft, hygiene, rapid 15 minute quick wash, drum clean with reminder, handwash/wool, delicates• Touch control buttons: start/pause with reload function, prewash, less ironing, spin speed selection, temperature selection, speedPerfect, ecoPerfect, i-Dos 1, i-Dos 2, rinse hold, Memory, Child lock and 24 hours time delay	<p>Key features</p> <ul style="list-style-type: none">• i-DOS: intelligent dosing system• varioPerfect: speed or energy efficiency with perfect wash performance every time• waterPerfect Plus: water management system• Consumption indicator: Information about water and energy consumption prior to start of programme• antiVibration Design - for more stability and quietness• Reload function: Pause the already running washing machine to add any forgotten items of laundry to the drum. <p>Additional features</p> <ul style="list-style-type: none">• iQ Drive:innovative motor technology delivering energy efficiency, speed and durability• Large LED-Display for programme status indication, temperature selection, spin speed, remaining time and 24 hours end time delay, load recommendation and consumption indication• Jog dial with integrated on/off control• waveDrum - Gentle washing thanks to a unique drum structure• DrumClean with reminder function• Time delay 24 hours and time remaining indicator• autoLoad Plus• hydroSensor monitors and controls rinse cycles• Multiple water protection• Drum interior light• Electronic child safety package• Self cleaning detergent dispenser• Flow-through sensor for optimum water use• Foam detection system• Out of balance load adjustment• Acoustic signals: Buzzer <p>Technical Information</p> <ul style="list-style-type: none">• Dimensions (H X W X D): 84.8 x 59.8 x 59 cm• Slide-under installation• integrated 32 cm porthole, Alu-Look, white with 171° opening door