

Product data sheet

Specifications



APC Smart-UPS C, Line Interactive, 1000VA, Rackmount 2U, 120V, 6x NEMA 5-15R outlets, SmartConnect port, USB and Serial communication, AVR, Graphic LCD

SMC1000-2UC

Product availability: Non-Stock - Not normally stocked in distribution facility

Overview

Lead time Usually Ships within 2 Weeks

Main

Main Input Voltage	120 V
Other Input Voltage	110 V 125 V
Main Output Voltage	120 V
Other Output Voltage	110 V 125 V
Kw Rating	600 W
Rated power in VA	1000 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-15P
output connection type	6 NEMA 5-15R
number of rack unit	2U
Cable length	8 ft (2.4 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	Documentation CD Installation guide Rack Mounting brackets USB cable
Range of Product	Smart-UPS



Complementary

Communication Port	SmartConnect Ethernet port
Software package	SmartConnect software for remote power monitoring feature availability varies by terms of use

Batteries & Runtime

Run Time [View Runtime Graph](#)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Efficiency	View Efficiency Graph 
Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	4...6 year(s)
Replacement battery	APCRBC124 
Battery Charge Power (Watts)	72 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	Cloud-enabled monitoring
Redundant	No

Physical

color	Black
Height	3.4 in (8.6 cm)
Width	17.008 in (43.2 cm)
Depth	16.0 in (40.6 cm)
Net Weight	45.24 lb(US) (20.52 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	85...136 V adjustable 93...130 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	1000 VA
Max Configurable Power (Watts)	600 W
Transfer Time	6ms typical : 10ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	cULus ENERGY STAR V2.0 (USA)
Equipment protection policy	Lifetime : \$150000

Environmental

Acoustic level	41 dBA
Online Thermal Dissipation	175 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

Control panel	Multi-function LCD status and control console
Free slots	0
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rating	680 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304322733
Returnability	No
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.3 in (23.5 cm)
Package 1 Width	22.4 in (57 cm)
Package 1 Length	21.06 in (53.5 cm)
Package 1 Weight	45.66 lb(US) (20.71 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Energy Efficient Take-back Transparency RoHS/REACH


Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Mercury Free

 RoHS Exemption Information Yes

Environmental Certifications

 Energy Star® ENERGY STAR UPS V2.0 (USA)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu RoHS Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

California Proposition 65 WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov