

## USB-C Docking Station, 4K @ 30 Hz, HDMI, Thunderbolt 3, USB-A Hub, PD Charging, SD/Micro SD, GbE - Silver

MODEL NUMBER: U442-DOCK11-S



### Features

### Highlights

- Transmits audio/video signals from sources supporting USB DisplayPort Alt Mode
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- 2 USB-A ports transfer data from thumb drives or printers at speeds up to 5 Gbps
- Connects you to a wired Ethernet network when no Wi-Fi is available
- Easy installation with plug-and-play operation—no software required

### Applications

- Play video from your laptop or PC on an HDMI display, such as an HDTV or projector
- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Upload data from your notebook or download data from the Ethernet at true 10/100/1000 Mbps Ethernet speeds
- Transfer data to and from a USB flash drive or Micro SD memory card
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Write a report using a USB keyboard with your tablet or Android smartphone

### System Requirements



- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with DVI\* or HDMI input
- Not for use with Thunderbolt monitors

**Package Includes**

- U442-DOCK11-S USB-C Docking Station, 4K, HDMI, Thunderbolt 3, USB-A Hub, PD Charging, SD/MicroSD, Gb – 30 Hz, Silver
- Owner's manual

## Specifications

MODEL TEXT	
What Does This Product Do?	
OVERVIEW	
Over Current Protection	
INPUT	
Cable Length (ft.)	
Cable Length (m)	
Cable Length (in.)	
Built-In Cable Length (ft.)	
Built-In Cable Length (m)	
Built-In Cable Length (in.)	6
Built-In Cable Length (cm)	
External Power Supply Input Specs (V / Hz / A)	
External Power Supply Output Specs (V / A)	



External Power Supply Cord Length (ft.)	
External Power Supply Cord Length (m.)	
Cable Length (cm)	
Product Length (in.)	
Product Length (cm.)	
Product Length (ft.)	
Product Length (m.)	
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	
<b>PHYSICAL</b>	
Unit Packaging Type	
Unit Dimensions (hwd / in.)	
Unit Dimensions (hwd / cm)	
Unit Weight (lbs.)	
Material of Construction	PVC
Color	Silver
Transmitter Unit Dimensions (hwd / in.)	
Transmitter Unit Dimensions (hwd / cm.)	
Receiver Unit Dimensions (hwd / in.)	
Receiver Unit Dimensions (hwd / cm.)	
Transmitter Unit Weight (lbs.)	
Transmitter Unit Weight (kg)	
Receiver Unit Weight (lbs.)	
Receiver Unit Weight (kg)	
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 TO 113F (0 TO 45C)
Storage Temperature Range	14 TO 158F (-10 TO 70C)
Relative Humidity	40 - 50% RH
Operating Elevation (ft.)	
Storage Elevation (ft.)	
BTUs	



Power Consumption (Watts)	
Operating Humidity Range	
Storage Humidity Range	
Power Provided to Connected Device(s)	45W
<b>COMMUNICATIONS</b>	
Signal Range (ft.)	
Network Speed	1Gbps
IEEE Standards Supported	802.3
<b>CONNECTIONS</b>	
Ports	
Side A - Connector 1	(1) USB C (MALE)
Side B - Connector 1	(1) HDMI (FEMALE); (1) MICRO SD (FEMALE); (1) RJ45 (FEMALE); (1) SD (FEMALE); (2) USB A (FEMALE)
Connector Plating	Nickel
<b>PORT EXPANSION</b>	
Max Distance (Between any 2 Units)	
<b>FEATURES &amp; SPECIFICATIONS</b>	
Max Supported Video Resolution	HDMI: 4K @ 30Hz
HDMI Specification	1.4
HDCP Specification	2.2
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
Audio Specification	
Recommended Category Cable	
<b>CERTIFICATIONS</b>	
Certifications	
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>