

1 m (3.3 ft.) USB-C to Mini DisplayPort Cable - 4K 60Hz - Black

**Product ID:** CDP2MDPMM1MB



This USB-C to Mini DisplayPort cable lets you connect your Thunderbolt 3 or USB Type-C enabled device to a Mini DP monitor with just one cable, for a convenient, clutter-free connection.

Harness the video capabilities that are built into your USB-C connection. The USB Type-C to Mini DisplayPort cable delivers the astonishing quality of Ultra HD to your 4K display, at resolutions up to 3840 x 2160. Plus, the adapter is backward compatible with 1080p displays, which makes it a great accessory for home, office or other work environments.

At 1 m (3.3 ft.) in length, this Mini DP cable delivers a compact connection that eliminates excess adapters and cabling, ensuring a tidy, professional installation. For longer installations, we also offer a 6 ft. (1.8 m) USB-C to mDP cable, enabling you to choose the right cable length for your custom installation needs.

For easy operation and installation, this USB 3.1 Type-C to Mini DP adapter cable supports plug-and-play installation on both Windows and Mac computers.

CDP2MDPMM1MB is backed by a 3-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Connect your MacBook or USB-C device to an mDP monitor
- Ideal for home office or hot desk environments

- Experience crisp visuals with support for 4K 60Hz
- Deliver enriched presentations on the go

## Features

- **ADAPTER AND CABLE IN ONE:** This USB-C to Mini DP cable lets you connect your Thunderbolt 3, Thunderbolt 4 or USB-C computer to a Mini DisplayPort (mDP) monitor with just one cable
- **4K 60HZ RESOLUTION:** USB-C to Mini DisplayPort Cable Adapter delivers UHD picture quality with support for video resolutions up to 4K 60Hz; It's also backwards compatible with 1080p monitors or displays
- **HASSLE-FREE SETUP:** This USB Type-C to Mini DP adapter cable supports plug-and-play installation on both Windows and Mac computers; No driver installation required
- **THUNDERBOLT 3 AND USB-C COMPATIBLE:** USB-C to mDP cable works with Thunderbolt 3 / 4 computers and USB Type-C ports supporting video; Please check with your computer manufacturer to confirm video over USB-C (DP Alt mode) support
- **NOTE:** USB-C to mDP video cable; This is not a Thunderbolt (TB) 3 cable, it is not reversible or compatible with TB 1 or 2 peripherals like monitors, audio interfaces, etc; Cable will not work for Apple's Targeted Display Mode for using iMacs as Monitors

---

### Hardware

Warranty	3 Years
AV Input	USB-C
Ports	1
AV Output	Mini DisplayPort - 1.2
Chipset ID	STMicroelectronics - STM32F072CUB6

---

### Performance

Maximum Digital Resolutions	3840x2160 @ 60 Hz
Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200 2560x1440 2560x1600 3840x2160 (Ultra HD 4K)
Wide Screen Supported	Yes
Audio Specifications	DisplayPort - 5.1 Channel Audio

---

### Connector(s)

Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode
-------------	---

Connector B	1 - Mini-DisplayPort (20 pin)
-------------	-------------------------------

---

**Special Notes / Requirements**

Note	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
------	---

---

**Environmental**

Operating Temperature	5C to 35C (41F to 95F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	25%-60%RH

---

**Physical Characteristics**

Color	Black
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1.0 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	0.9 oz [25.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.5 in [1.2 cm]
Shipping (Package) Weight	1.1 oz [30.5 g]

---

**What's in the Box**

Included in Package	1 - USB-C to Mini DisplayPort cable
---------------------	-------------------------------------

---

*\*Product appearance and specifications are subject to change without notice.*