

RPD 9467 JSW UK

12NC: F103048

EAN code: 5054645030484

Hotpoint



MAIN FEATURES

Product group	Washing machine
Construction type	Free-standing
Installation type	Free-standing
Removable work top	No
Loading type	Front
Main colour of product	White
Connection rating (W)	1850
Current (A)	13
Voltage (V)	220-240
Frequency (Hz)	50
Length of Electrical Supply Cord (cm)	120
Plug type	UK
Height of the product	850
Width of the product	595
Depth of the product	605
Net weight (kg)	74

TECHNICAL FEATURES

Automatic programmes	Yes
Spin speed options	Variable
Skip spin	Yes
Weight measurement	Yes
Textile type recognition	Yes
Degree of dirtiness recognition	No
Foam control	Yes
Balance control	Yes
Type of water protection system	-
Cold wash option	Yes
Progress indicator	DISPLAY
Digital countdown indicator	Yes
Start delay options	No delay
Start delay time max. (h)	-
Tub material	Plastic
Drum volume (l)	62
Hot & cold water intake?	No

PERFORMANCES

Energy efficiency class - NEW (2010/30/EC)	A+++
Energy consumption annual (kWh/annum) - NEW (2010/30/EC)	153
Washing performance class - NEW (2010/30/EC)	B
Maximum spin speed (rpm) - NEW (2010/30/EC)	1400
Capacity cotton (kg) - NEW (2010/30/EC)	9
Water consumption annual (l/annum) - NEW (2010/30/EC)	11600
Energy consumption 60 °C full load	0.877
Power consumption in left-on mode - NEW (2010/30/EC)	8
Power consumption in off-mode - NEW (2010/30/EC)	0.50
Moisture content % on dry load after max. spin - NEW (2010/30/EC)	-
Average washing time cotton 60C (full load) (min) - NEW (2010/30/EC)	225
Noise level washing (dB(A) re 1 pW)	53
Noise level spinning (dB(A) re 1 pW)	81