

# QTH167

## 5MP ANALOG HD DVR

### SPECIFICATIONS

DVR Technology	.....	Analog HD
Channels	.....	16
Recording Resolution	.....	5MP / 4MP / 3MP / 1080p / 720p / WD1
Live Viewing Resolution	.....	4K / 2K / 1080p / 1280x1024
Live Display FPS	.....	5MP @ 20FPS
Hard Drive	.....	2 HDD up to 8TB Each
Remote Monitoring	.....	10 Simultaneous Users
Camera Connectivity	.....	QTA, QTH and QCA Analog HD Cameras
PIR Camera Support	.....	Yes



**Supports QTA, QTH and QCA Analog HD, Analog, and Precise Motion (PIR) Cameras**

### RECORDING RESOLUTION & PLAYBACK

5MP	10FPS	160FPS Total
4MP	15FPS	240FPS Total
3MP	15FPS	240FPS Total
1080p (1920 x 1080)	30FPS	480FPS Total
720p (1280 x 720)	30FPS	480FPS Total
WD1	30FPS	480FPS Total

### SYSTEM

Channels	16 Simultaneous Local Playback
Video Compression	H.264
Display Modes	1, 4, 8, 16, Auto Sequence
Recording Modes	Manual, Time Schedule, Motion, Sensor
Backup Methods	PC, USB Flash Drive, USB Hard Drive
Languages	English, Chinese (Simplified & Traditional), Czech, French, Portuguese, Spanish, Turkish, Bulgarian, Greek, Italian, German, Russian, Polish, Japanese, Indonesian, Thai, Hungarian, Lithuanian, Vietnamese, Dutch, Swedish, Norwegian, Persian, Arabic, Romanian

### REMOTE MONITORING

Scan 'N View	Yes
Dual Stream	CIF, D1 (Up to 15FPS)
Simultaneous Users	10 (Bandwidth Permitting)

### COMPATIBILITY

Application Support	QT View
Mobile OS Support	iOS, Android
Computer OS Support	Windows (XP, Vista, 7, 8, 10), Mac OSX (10.7 and Newer)
Camera Support	QTA, QTH and QCA Analog HD, and Analog Cameras

### VIDEO, AUDIO & ALARM PORTS

Video In	BNC (16x)
Video Out	HDMI up to 4K Output (1x), VGA up to 1080p (1x)
Audio In	RCA (x4, 1 Channel Each)
Audio Out	RCA (x4, 1 Channel Each)
Alarm In	Yes (x4)
Alarm Out	Yes (x1)

### COMMUNICATION PORTS

Network	RJ45 10/100 Mbps
USB	USB 2.0 (x1), USB 3.0 (x1)
eSATA	No

### ACCESSORIES

Control	USB Mouse
Connectors/Cables	HDMI Cable
Mounting Hardware	Screws for Hard Drive
Other	Quick Start Guide

# QTH167

## 5MP ANALOG HD DVR

### HARD DRIVES

Maximum Size	8TB
Number Supported	2

### PTZ

PTZ Support	RS485 Cable
Supported Protocols	COC, Null, Pelco P, Pelco D, Lilin, Minking, Neon, Star, VIDO, DSCP, VISCA, Samsung, RM110, HY

### POWER

Power Supply	DC 12V 4A
Power Consumption	≤15w (w/o HDD)

### PHYSICAL

Weight	5 lbs
Dimensions	14.96" W x 10.55" D x 2" H
Operating Temperature	14° - 122° F

