



Philips
4K Ultra HD LCD monitor

E Line
27" (68.6 cm)
4K UHD (3840 x 2160)

27E8VJSB



Magnificent view in an elegant design

Philips 27" 4K UHD monitor gives ultra-clear picture quality. 4K UHD with wide-view delivers same ultimate clarity and life-like visuals from any front angle view. Flicker-free reduces eye fatigue after long use.

Superb Picture Quality

- UltraClear 4K UHD (3840x2160) resolution for precision
- IPS LED wide view technology for image and color accuracy

Elegant Design

- Elegant, slim design complements your home decor
- Narrow border display for a seamless appearance

Features designed for you

- MultiView enables simultaneous dual connect and view
- HDMI-ready for Full HD entertainment
- Less eye fatigue with Flicker-free technology
- LowBlue Mode for easy on-the-eyes productivity

Greener everyday

- Eco-friendly materials meet major international standards
- Low power consumption saves energy bills

PHILIPS


Highlights

UltraClear 4K UHD Resolution




These latest Philips displays utilize high performance panels to deliver UltraClear, 4K UHD (3840 x 2160) resolution images. Whether you are demanding professional requiring extremely detailed images for CAD solutions, using 3D graphics applications or a financial wizard working on huge spreadsheets, Philips displays will make your images and graphics come alive.

IPS technology



IPS displays use an advanced technology which gives you extra wide viewing angles of 178/178 degree, making it possible to view the display from almost any angle. Unlike standard TN panels, IPS displays gives you remarkably crisp images with vivid colors, making it ideal not only for Photos, movies and web browsing, but also for professional applications which demand color accuracy and consistent brightness at all times.

UltraNarrow Border



The new Philips displays feature ultra-narrow borders which allow for minimal distractions and maximum viewing size. Especially suited for multi-display or tiling setup like gaming, graphic design and professional applications, the ultra-narrow border display gives you the feeling of using one large display.

MultiView technology

With the ultra-high resolution Philips MultiView display you can now experience a world of connectivity. MultiView enables active dual connect and view so that you can work with multiple devices like a PC and notebook simultaneously, for complex multi-tasking.

HDMI Ready



An HDMI-ready device has all the required hardware to accept High-Definition Multimedia Interface (HDMI) input. A HDMI cable enables

high-quality digital video and audio all transmitted over a single cable from a PC or any number of AV sources (including set-top boxes, DVD players, A/V receivers and video cameras).

Flicker-free technology



Due to the way brightness is controlled on LED-backlit screens, some users experience flicker on their screen which causes eye fatigue. Philips Flicker-free Technology applies a new solution to regulate brightness and reduce flicker for more comfortable viewing.

LowBlue Mode



Studies have shown that just as ultra-violet rays can cause eye damage, shortwave length blue light rays from LED displays can cause eye damage and affect vision over time. Developed for wellbeing, Philips LowBlue Mode setting uses a smart software technology to reduce harmful shortwave blue light.



Specifications

Picture/Display

- LCD panel type: IPS technology
- Backlight type: W-LED system
- Panel Size: 27 inch / 68.6 cm
- Display Screen Coating: Anti-Glare, 3H, Haze 25%
- Effective viewing area: 596.74 (H) x 335.66 (V)
- Aspect ratio: 16:9
- Optimum resolution: 3840 x 2160 @ 60 Hz
- Pixel Density: 163 PPI
- Response time (typical): 5 ms (Gray to Gray)*
- Brightness: 350 cd/m²
- Contrast ratio (typical): 1000:1
- SmartContrast: 20,000,000:1
- Pixel pitch: 0.155 x 0.155 mm
- Viewing angle: 178° (H) / 178° (V), @ C/R > 10
- Flicker-free
- Picture enhancement: SmartImage game
- Display colors: Color support 1.07 billion colors
- Scanning Frequency: 30 - 83 kHz (H) / 59 - 61 Hz (V)
- LowBlue Mode
- sRGB

Connectivity

- Signal Input: DisplayPort 1.2, HDMI 2.0 x 2
- Sync Input: Separate Sync, Sync on Green
- Audio (In/Out): HDMI audio out

Convenience

- MultiView: PIP/PBP mode, 2x devices
- User convenience: Power On/Off, Menu, Brightness, Input, SmartImage Game
- OSD Languages: Brazil Portuguese, Czech, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Simplified Chinese, Spanish, Swedish, Traditional Chinese, Turkish, Ukrainian
- Other convenience: Kensington lock
- Plug & Play Compatibility: DDC/CI, Mac OS X, sRGB, Windows 10 / 8.1 / 8 / 7

Stand

- Tilt: -5/20 degree

Power

- On mode: 19.9 W (typ.) (EnergyStar 7.0 test method)
- Standby mode: < 0.5 W (typ.)

- Off mode: < 0.3 W (typ.)
- Power LED indicator: Operation - White, Standby mode- White (blinking)
- Power supply: External, 100-240VAC, 50-60Hz

Dimensions

- Product with stand (mm): 613 x 466 x 189 mm
- Product with stand in inch: 24.1 x 18.3 x 7.4 inch
- Product without stand (mm): 613 x 374 x 41 mm
- Product without stand in inch: 24.1 x 14.7 x 1.6 inch
- Packaging in mm (WxHxD): 660 x 523 x 135 mm
- Packaging in inch (WxHxD): 26.0 x 20.6 x 5.3 inch

Weight

- Product with stand (kg): 4.84 kg
- Product with stand (lb): 10.65 lb
- Product without stand (kg): 9.31 kg
- Product without stand (lb): 20.48 lb
- Product with packaging (kg): 6.53 kg
- Product with packaging (lb): 14.37 lb

Operating conditions

- Temperature range (operation): 0 to 40 °C
- Temperature range (storage): -20 to 60 °C
- Relative humidity: 20%-80 %
- Altitude: Operation: +12,000ft (3,658m), Non-operation: +40,000ft (12,192m)
- MTBF: 50,000 hrs (excluding backlight) hour(s)

Sustainability

- Environmental and energy: EnergyStar 7.0, EPEAT Silver, RoHS, Lead-free, Mercury Free, TCO certified, WEEE
- Recyclable packaging material: 100 %

Compliance and standards

- Regulatory Approvals: CE Mark, FCC Class B, TUV/ISO9241-307, EPA, cETLus, CU-EAC

Cabinet

- Color: Black / Gunmetal
- Finish: Glossy

What's in the box?

- Monitor with stand
- Cables: DP cable, HDMI cable, Power cable
- User Documentation



Issue date 2019-01-11

Version: 2.0.1

12 NC: 8670 001 56753
UPC: 6 09585 25238 7

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* "IPS" word mark / trademark and related patents on technologies belong to their respective owners.
* Response time value equal to SmartResponse
* The monitor may look different from feature images.