

## BATTERY BACK UP STANDBY UPS

0E-625V8LCD2

625VA/390W STANDBY UPS

COMMERCIAL AND RESIDENTIAL



The 0E-625V8LCD2 Uninterruptible Power Supply (UPS) is ideal for electronics as well as power protection for individual commercial work spaces. With 625VA and 390 Watts of capacity, the 0E-625V8LCD2 UPS protects equipment from blackouts, brown outs, spikes, and surges.

- STANDBY UPS
- 625VA/390W CAPACITY
- 120V NOMINAL VOLTAGE
- LCD DISPLAY
- 8 OUTLETS
- TRANSFER TIME 4ms
- HID COMPLIANT USB PORT
- FREE MANAGEMENT SOFTWARE DOWNLOAD
- 526 JOULES OF SURGE PROTECTION
- EMI AND RFI FILTRATION
- ENERGY STAR 2.0 CERTIFIED
- CONNECTED EQUIPMENT WARRANTY \$100,000

PART #: 0E-625V8LCD2

UPC: 8 11914 30002 6

LENGTH: 10.6"

WIDTH: 5.9"

HEIGHT: 3.1"

WEIGHT: 6.4 LBS

FULL-LOAD RUNTIME: 2 MIN

HALF-LOAD RUNTIME: 8 MIN

BATTERY SIZE: 12V / 5.5Ah

UL LISTING: E473223

Product Certification:



FOR MORE INFORMATION,  
CONTACT YOUR ADI SALES PERSON.

wboxtech.com