





Capture Bar Codes Anywhere with a Durable Plug-in Scanner



Increase efficiencies in your data collection applications with the CompactFlash Scan Card (CFSC) Series 5

- **Performance** – Advanced technology for scanning 1D and 2D bar codes in a broad range of indoor and outdoor conditions
- **One-Handed Scanning** – After you insert the CFSC into a PDA, you can scan with one hand, leaving your other hand free to handle packages and materials for increased productivity
- **Modular** – Works in the standard CompactFlash or PC Card slot of a wide variety of mobile computers, so you can switch or upgrade computers and keep using the same scanner*

WHICH VERSION IS RIGHT FOR YOU?	
CFSC 5E <i>Entry-Level</i> 	Basic unit for light-duty indoor scanning less than 25 times per day at a distance of 4-7 inches. Requires good lighting conditions and clearly printed, unblemished bar codes on non-reflective, flat surfaces. Features CMOS imaging technology and supports 1D bar codes.
CFSC 5M <i>Mid-Range</i> 	Mid-range unit for most indoor scanning applications. Easy to use and can scan more than 25 times per day, including worn or damaged bar codes, up to 20 inches away. Recommended for ISBN book numbers. Features Class 1 laser and supports 1D and stacked bar codes.
CFSC 5P <i>Performance</i> 	Performance unit for easy-to-use, heavy-duty scanning indoors or outdoors. Can scan more than 25 times per day, including worn or damaged bar codes, even bar codes more than 20 inches away. Ideal for scanning on curved or reflective surfaces, or through thick glass or plastic, including VIN vehicle numbers. Features Class 2 laser and supports 1D and stacked bar codes.
CFSC 5X <i>Xtreme Performance</i> 	Xtreme performance unit for scanning 1D and 2D bar codes indoors in good lighting conditions up to 20 inches away. Features CMOS imaging technology and also supports stacked and postal bar codes.

HARDWARE FEATURES

- Durable card with integrated scanner plugs into a CompactFlash (CF) card slot with a snug, secure fit
- With CF-to-PC Card adapter, also works in a PC Card (PCMCIA) slot*
- Compatible with mobile computers running:
 - Windows Mobile 2003, 2003SE, 5.0 for Pocket PC/Pocket PC Phone Edition, 6 Classic/Professional
 - Windows XP/XP Tablet Edition
- One-handed operation with a handheld device improves efficiency by freeing the other hand to handle packages or materials
- Available in four performance levels to fit your business requirements
- Easy to pack and easy to maintain, with no extra batteries or power adapter required
- Battery Friendly® technology reduces power consumption, maximizing the battery life of your mobile computer
- One year warranty

SOFTWARE FEATURES

- SocketScan™ keyboard emulation software enters scanned data into any Windows application as virtual keystrokes — no custom programming required
- Automatically add prefix and suffix functions, such as carriage return and tab, to further eliminate manual keystrokes
- Assign a beep tone or .WAV audio file to signify a successful scan
- Easily enable/disable bar code symbologies with SocketScan Symbology Selector utility
- View the properties of any bar code, including symbolotly, length, and decoded data, for any of your scanner's supported symbologies
- Compatible with Windows-based development tools for custom applications
- SDK available to application developers for Windows Mobile and Windows XP
- Floating Trigger for Windows Mobile puts an icon on your screen that you can tap to trigger the scanner

*PC Card adapter available separately

CompactFlash Scan Card

Series 5



CFSC in tablet computer

TYPES OF BAR CODES

Linear (1D)	
Stacked Linear Composite	
2D/Matrix	
Postal	



Sales Offices
Corporate Headquarters:
 39700 Eureka Drive
 Newark, CA 94560 USA

Web: socketmobile.com

Phone: +1-510-933-3000

USA & Canada Toll Free: 800-552-3300

Fax: +1-510-933-3030

Online: socketmobile.com/contact

SPECIFICATIONS				
	CFSC 5E Entry Level	CFSC 5M Mid-Range	CFSC 5P Performance	CFSC 5X Xtreme Performance
SKU #	IS5024-608	IS5025-609	IS5026-610	IS5036-750
Scanner Type	CMOS linear imager	Class 1 laser	Class 2 laser	CMOS 2D imager
Types of Bar Codes Decoded	Linear (1D)	Linear (1D), Stacked linear composite (RSS-14)		Linear (1D), Stacked linear, 2D/Matrix, Postal
Symbologies Decoded	Codabar Code 11 Code 128 Code 39 Code 93 D 2 of 5 I 2 of 5 MSI UPC/EAN	Same as CFSC 5E plus: Chinese 2 of 5, RSS-14, RSS-limited/Expanded Stacked		Same as CFSC 5E (except D 2 of 5) plus: Australia Post, Aztec, BPO4 State Code, British Post, Canada Post, Codablock, Composite Code, Data Matrix, Dutch Post, EAN/UCC Composite, ISBN, Japan Post, Matrix 2 of 5, Maxicode, PDF 417/ Macro PDF 417/Micro PDF 417, Planet, Plessey Code, Postnet, QR Code, RSS/RSS-14/Expanded, Standard 2 of 5, Telepen, TLCode 39, 4 State Code
Decode Distance*	1.25 to 24+ inches (3.2 to 61+ cm)	1.00 to 35+ inches (2.5 to 90+ cm)	1.00 to 45+ inches (2.5 to 114+ cm)	1.3 to 32.4 inches (3.4 to 83 cm)
Operating System Support	Windows Mobile 2003/2003SE/5.0 for Pocket PC/Pocket PC Phone Edition/ 6 Classic/Professional Windows XP/XPTablet Edition			
Interface Standard	CompactFlash Type II PC Card (PCMCIA), requires Type II PC Card adapter**			CompactFlash Type I PC Card (PCMCIA), requires Type I or II PC Card adapter**
Included Software	SocketScan for Windows Mobile SocketScan for Windows XP/XP Tablet Edition			
Certification/Compliance	FCC: Part 15, Class B CE: EN55024:2003 C-TICK: s.182 RoHS	FCC: Part 15, Class B ICES-003 Class B AS 3548 C-TICK: s.182 21CFR1040.10 RoHS	CE: EN55024:2003 CISPR 22 Japan VCCI Class B VCCI 21CFR1040.11***	FCC: Part 15, Class B CE: EN55024:2003 C-TICK: s.182 VCCI Class B RoHS
Warranty	One year			

*Depends on symbol size, symbology, label media, W-N Ratio, scan angle

**PC Card adapters available separately

***Except for deviations pursuant to Laser Notice No. 50, dated July 26, 2001



© 2008, Socket Mobile, Inc. Socket, the Socket logo, Business Mobility Now!, Increasing Mobile Productivity, CompactFlash Scan Card, SocketScan, and Battery Friendly are registered trademarks or trademarks of Socket Mobile, Inc. Microsoft is a registered trademark of Microsoft Corporation in the United States and other countries. All other brand and product names are trademarks of their respective holders. Information is subject to change. 6450-00160H 5/2008

Business Mobility Now!™