TRIPP-LITE

USB-C to Gigabit Network Adapter with Right Angle USB-C, Thunderbolt 3 Compatibility -White

MODEL NUMBER: U436-06N-GBW-RA







Connects the USB-C or Thunderbolt 3 port on your computer, laptop, MacBook, Chromebook or tablet to a wired Gigabit Ethernet network.

Features

USB-C to Gigabit Ethernet Adapter Connects to Your Laptop's USB-C or Thunderbolt 3 PortThis USB Type-C to Gigabit Ethernet NIC Network Adapter (M/F) allows your computer, tablet, laptop, notebook, MacBook, Chromebook, Ultrabook or smartphone to connect to a wired Ethernet network. Connect the right-angle USB-C connector to your device's USB-C or Thunderbolt 3 port, and connect the RJ45 port to a UTP cable (such as Tripp Lite's N201-Series, sold separately). Ideal for settings in which no Wi-Fi is available or when a wired connection offers faster speeds, this USB 3.1 Gen 1 adapter lets you enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers and audio/video streaming.

Built-In USB-C Cable Attaches in Either DirectionUnlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Right-Angle USB-C Plug Makes Connecting in Tight Spaces EasierThe space-saving right-angle USB-C plug is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

Ready to Use Right Out of the PackageThe plug-and-play network adapter requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go. Plug it into your laptop for instant network connection.

Specifications

OVERVIEW

UPC Code

037332214157

Highlights

- Connect to a wired 10/100/1000 Mbps network where Wi-Fi is weak or unavailable
- More convenient, less expensive than installing or upgrading an internal Ethernet card
- Widely compatible with Windows, Mac and Chromium operating systems
- Right-angle USB-C plug allows easier connection in confined or hard-to-reach spaces
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Upload data from your MacBook or download data from the Ethernet at true 10/100/1000 Mbps speeds

System Requirements

- Laptop or computer with an available USB-C port
- Ethernet network and a Cat6 cable to connect to it.

Package Includes

- U436-06N-GBW-RA Right-Angle USB-C to Gigabit Ethernet Network Adapter (M/F), White
- Quick Start Guide

TRIPP-LITE

Built-In Cable Length (m)0.1Built-In Cable Length (in.)3.9Bus PoweredYeProduct Length (in.)6	94 es 5.24 5 .15 0	
Built-In Cable Length (m)0.1Built-In Cable Length (in.)3.9Bus PoweredYeProduct Length (in.)6Product Length (cm.)15Product Length (ft.)0.5Product Length (m.)0.1BATTERY0.1	1	
Built-In Cable Length (in.)3.9Bus PoweredYeProduct Length (in.)6Product Length (cm.)15Product Length (ft.)0.5Product Length (m.)0.1BATTERY9	94 es 5.24 5 .15	
Bus Powered Ye Product Length (in.) 6 Product Length (cm.) 15 Product Length (ft.) 0.5 Product Length (m.) 0.1	es 5.24 5 .15 0	
Product Length (in.) 6 Product Length (cm.) 15 Product Length (ft.) 0.5 Product Length (m.) 0.1 BATTERY 0.1	5.24 5 15 0	
Product Length (cm.) 15 Product Length (ft.) 0.5 Product Length (m.) 0.1 BATTERY 0.1	5.24 .5 .15 0	
Product Length (ft.) 0.5 Product Length (m.) 0.1 BATTERY	5 .15 0	
Product Length (m.) 0.1 BATTERY	.15 o	
BATTERY	0	
Battery Charging (5V/1.5A Port) No		
	OLS	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators Ne	etwork cable connected = Green; Data transmitting = Green	
PHYSICAL		
Color Wh	/hite	
Material of Construction AB	BS, PVC	
Cable Jacket Rating VV	W-1	
Unit Dimensions (hwd / in.) 0.6	630 x 6.000 x 1.060	
Unit Dimensions (hwd / mm) 16	6 x 150 x 27	
Unit Packaging Type Bo	ox	
ENVIRONMENTAL		
Operating Temperature Range 32	2° to 113°F (0° to 45°C)	
Storage Temperature Range 14	4° to 176°F (-10° to 80°C)	
Operating Humidity Range 10	0% to 85% RH, Non-Condensing	
Storage Humidity Range 5%	% to 90% RH, Non-Condensing	
COMMUNICATIONS		
Network Compatibility 1 C	Gbps (Gigabit)	
CONNECTIONS		
Number of Ports 1		
Side A - Connector 1 US	SB C (MALE) - RIGHT ANGLE	
Side B - Connector 1 RJ	J45 (FEMALE)	



Connector Plating	Nickel	
Contact Plating	Gold	
FEATURES & SPECIFICATIONS		
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)	
Driver Required	No	
Recommended Category Cable	Cat6 Cables	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	3-year limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.