



**Hewlett Packard**  
Enterprise

# HPE G2 R6000/60309 3- WIRE 32A/230V OUTLETS (4) C13 (4) C19 (1) IEC 32A/3U RACKMOUNT INTL UPS (Q7G11A)

## Uninterruptable Power System



### WHAT'S NEW

- Brings Online Double-Conversion technology to the Hewlett Packard Enterprise single-phase UPS portfolio.
- Supports the HPE 1GbE Network Management Module as a standard feature.
- Provides virtualization-ready support for

### OVERVIEW

Does your IT workload require high availability power protection? HPE Online Double Conversion Rackmount Uninterruptible Power System enables high system availability by eliminating transfer time to battery power for all connected IT equipment. HPE Enhanced Battery Management technology improves battery service life by up to 50% [1] while monitoring

---

HPE SimpliVity when using the Eaton Intelligent Power Manager software (free download).

- Adds a UPS model for North America and Japan (NA/JPN) specifically targeting backup power for larger network switches.
- Adds an R6000 international (INTL) model that provides 20% [2] more power than current R5000 INTL model.
- Supports greater flexibility by adding hardwired power input for 30A/32A models (R8000).

battery health and providing advanced notice when replacement is required. Scale system runtime from minutes to hours by adding up to four Extended Runtime Modules. HPE Online Double Conversion UPS includes a 1GbE Network Management Module that provides access to the UPS and its embedded web-based user interface, allowing you to monitor and manage individual UPS systems. With Eaton® Intelligent Power Manager software, users can centralize remote monitoring and management of multiple HPE UPS systems and seamlessly integrate them into virtualization platforms, such as HPE SimpliVity, to manage virtual machines and extend battery runtime.

## FEATURES

### Improve the Availability of Your IT Systems

The HPE Online Double Conversion Rackmount Uninterruptible Power System utilizes a power topology that offers one of the highest levels of power protection by helping eliminate transfer time to battery power for all connected server, storage, and networking equipment.

HPE Enhanced Battery Management technology increases battery service life by up to 50% [1] through an advanced, three-stage charging technique that closely monitors battery health and provides advanced notice when batteries need replacement.

Scale UPS runtime from minutes to hours by adding up to four Extended Runtime Modules to your UPS.

### Monitor and Manage your HPE UPS from Across the Network

The HPE Online Double Conversion Rackmount Uninterruptible Power System includes the new 1GbE Network Management Module that supports easy integration into most IT networks and access to the embedded web-based user interface for managing individual UPS systems.

Eaton Intelligent Power Manager (IPM) software, available via free download, enables remote monitoring and management of multiple Hewlett Packard Enterprise UPS systems across the network from a single interface.

Eaton IPM also supports seamless integration of Hewlett Packard Enterprise UPS systems into industry-leading virtualization platforms, such as HPE SimpliVity, allowing you to manage critical and non-critical virtual machines to extend battery runtime.



**Technical specifications****HPE G2 R6000/60309 3-wire 32A/230V Outlets (4)  
C13 (4) C19 (1) IEC 32A/3U Rackmount INTL UPS**

<b>Product Number (SKU)</b>	Q7G11A
<b>Form factor</b>	3U rackmount
<b>Power output</b>	6kVA (5.4kW)
<b>Power distribution</b>	Single-phase
<b>UPS Battery type</b>	Maintenance-free, sealed, valve-regulated lead acid (VRLA)
<b>Minimum dimensions (H x W x D)</b>	129.5 x 439.4 x 721.4 mm
<b>Weight</b>	48.9 kg
<b>Warranty</b>	HPE Online Double Conversion Rackmount UPS are covered by a 3-year warranty which covers depot repair of the UPS, or direct replacement of the UPS, including parts and labor.



For additional technical information, available models and options, please reference the [QuickSpecs](#)

## HPE POINTNEXT

Access expertise at every step of your IT journey with [HPE Pointnext Services](#). [Advisory Services](#) focuses on your business outcomes and goals, to design your transformation and build a roadmap tuned to your unique challenges. Our [Professional](#) and [Operational Services](#) help speed up time-to-production and keep your IT stable and reliable.

### Operational Services from HPE Pointnext Services

- [HPE Datacenter Care](#) helps modernize and simplify IT operations. Partner with an assigned account team, access technical expertise, an enhanced call experience gives you priority access, choose hardware and software support, implement proactive monitoring to help stay ahead of issues, and access HPE IT best practices and IP.
- [HPE Proactive Care](#) offers an enhanced call experience and helps reduce problems with personalized proactive reports and advice. This also includes collaborative software support for Independent Software Vendors (ISVs), (Red Hat, VMWare, Microsoft, etc.). [Read more](#)
- [HPE Foundation Care](#) helps when there is a problem and has a choice of response levels. Collaborative software support is included and provides troubleshooting help for ISVs running on your server. [Read more.](#)

### Other related services

[Defective Media Retention](#) is optional and applies only to Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

[HPE Service Credits](#) offers a menu of technical services, access additional resources, and specialist skills.

[HPE Education Services](#) delivers a comprehensive range of services to support your people as they expand their skills required for a digital transformation.

Consult your HPE Sales Representative or Authorized Channel Partner of choice for any additional questions and support options.




## HPE GREENLAKE

[HPE Greenlake](#) is HPE's market-leading IT as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model. HPE GreenLake delivers public cloud services and infrastructure for workloads on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please [explore them here](#).

**Make the right purchase decision.  
Contact our presales specialists.**

[Find a partner](#)



[1] Based on testing performed by HPE's designated supplier.

[2] Power input from G1 UPS to G2 UPS models increases by 900 VA, an increase of 20% over G1 power.



© Copyright 2020 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Image may differ from the actual product [PSN1011483963DKEN](#), November, 2020.