



Hewlett Packard
Enterprise

HPE T1000 GEN5 NA/JP UPS WITH MANAGEMENT CARD SLOT (Q1F49A)

Uninterruptible Power System



WHAT'S NEW

- LCD offers an industry leading graphical interface that provides critical UPS information in a single screen view.
- Remote access through an optional 1GbE network management adapter.
- Slim tower design help to conserve valuable space.

OVERVIEW

Do you need more reliable power with advance battery management in a space saving design? HPE Line Interactive Tower Uninterruptible Power Systems deliver clean power with an advanced battery management capability. Computing environments are expected to deal with the frequencies and severities of power outages, increased power demands from the public and private cloud, software as a service (SaaS), and mobile computing plus online services and applications while maintaining tight cost controls. HPE Line Interactive Tower Uninterruptible Power Systems was designed to meet these

needs and exceed expectations as the industry requires a reliable, efficient and easy-to-use UPS within your computing environment.

FEATURES

Delivers Power Protection and Management for IT Environments

The HPE Line Interactive Tower Uninterruptible Power Systems models lower your power protection cost by providing up to eight (8) power outlets per UPS, allowing you to safeguard your IT and office equipment.

Standard features include an intuitive front panel display, enhanced battery management (EBM), network transient protection, and serial and USB ports for data exchange with the host computer.

Includes (at no additional cost) HPE Power Protector Software that provides the flexibility to monitor power conditions and control the HPE Line Interactive Tower Uninterruptible Power Systems both locally or remotely.

Backed by a 3-year limited warranty and an exclusive 30-day battery pre-failure warning, which provides notification from the HPE Power Protector software of an impending battery failure.

Increased Efficiency and Capacity to Maintain Uptime and Business Continuity

The HPE Line Interactive Tower Uninterruptible Power Systems models provide from 1.5kVA (R1500 G4) up to 7.2kVA (R7000) of output power in as little as 4U of rack space.

HPE Power Protector Software and an optional UPS Network Module enables you to monitor and manage power through HPE Systems Insight Manager and other SNMP management programs or via a standard Web browser (UPS Network Module optional on R1500 G4).

Includes a front panel LCD display for ease of management.

Enhanced system flexibility with two independently controlled load segments.

Simple and Fast Integration

HPE Line Interactive Tower Uninterruptible Power Systems batteries can be hot-swapped safely without ever shutting down equipment.

LCD offers an industry-leading graphical interface that provides complete critical UPS information in a single screen view.



Technical specifications**HPE T1000 Gen5 NA/JP UPS with Management Card Slot**

Product Number (SKU)	Q1F49A
Form factor	Tower
Power output	Operating Voltage Settings Power Out (VA/Watts) 100V (Japan) to 110V 1000VA/770W 120V 1000VA/700W
Power distribution	Single Phase
UPS Battery type	Maintenance-free, sealed, valve-regulated lead acid (VRLA)
Minimum dimensions (H x W x D)	(WxDxH) 150 x 340 x 210 mm
Weight	11.5 kg
Warranty	3 year limited warranty



[For additional technical information, available models and options, please reference the QuickSpecs](#)

HPE POINTNEXT

Access expertise at every step of your IT journey with [HPE Pointnext Services](#). [Advisory Services](#) focuses on your business outcomes and goals, to design your transformation and build a roadmap tuned to your unique challenges. Our [Professional](#) and [Operational Services](#) help speed up time-to-production and keep your IT stable and reliable.

Operational Services from HPE Pointnext Services

- [HPE Datacenter Care](#) helps modernize and simplify IT operations. Partner with an assigned account team, access technical expertise, an enhanced call experience gives you priority access, choose hardware and software support, implement proactive monitoring to help stay ahead of issues, and access HPE IT best practices and IP.
- [HPE Proactive Care](#) offers an enhanced call experience and helps reduce problems with personalized proactive reports and advice. This also includes collaborative software support for Independent Software Vendors (ISVs), (Red Hat, VMWare, Microsoft, etc.). [Read more](#)
- [HPE Foundation Care](#) helps when there is a problem and has a choice of response levels. Collaborative software support is included and provides troubleshooting help for ISVs running on your server. [Read more.](#)

Other related services

[Defective Media Retention](#) is optional and applies only to Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

[HPE Service Credits](#) offers a menu of technical services, access additional resources, and specialist skills.

[HPE Education Services](#) delivers a comprehensive range of services to support your people as they expand their skills required for a digital transformation.

Consult your HPE Sales Representative or Authorized Channel Partner of choice for any additional questions and support options.




HPE GREENLAKE

[HPE Greenlake](#) is HPE's market-leading IT as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model. HPE GreenLake delivers public cloud services and infrastructure for workloads on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please [explore them here](#).

**Make the right purchase decision.
Contact our presales specialists.**

[Find a partner](#)



© Copyright 2020 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Image may differ from the actual product
[PSN1010748732CZEN](#), November, 2020.