iMouse S80 Wireless Fabric Optical Mini Mouse

www.adesso.com



2.4 GHz Wireless Technology

The 2.4GHz Wireless Technology has 65536 IDs with 12 channels and works up to 30 feet. This provides the reliability to ensure your other wireless devices will not interfere with your keyboard.

Fabric Surface

Contoured body with soft canvas fabric cover comfortable grip-feeling without any fatigue for long time use.

Mini, Compact and Portable

The compact and durable design will make this mouse become your ideal choice when you travel. The mini compact size makes it easy to store your mouse in your laptop bag or briefcase while on the go.

Optical Sensor

Optical sensor technology improves precision and even lets you work on most surfaces like marble, wood and leather surfaces without the need of a mouse pad. With an optical resolution of 800/1200/1600 DPI, you can browse comfortably basically on any surface.

Battery Saving

With the built-in Auto-Sleep features, you can automatically maximize your battery life when your device is not in use.

DPI Switch - 3 Levels

With three selectable DPI options from 800 to 1600, users can change their desired DPI settings for different





Specifications:

• Wire

• Tracking Method: Optical Wireless RF 2.4GHz Connectivity: Up to 30 ft. (10m) Interface: USB Battery: (2) AAA batteries • Hand Orientation: **Right & Left** Buttons: 6 (Left & Right Mouse Button, Scroll Wheel/Middle Button, DPI Button, Forward/Back Button) Resolution: 800/1200/1600 DPI Dimensions: 3.8 x 2.2 x 1.5" (98 x 56 x 38mm) Weight 0.12 lbs (53g)

Windows® 10/8/7/XP

An Available USB Port

Requirements:

Operating System Connectivity Interface

Includes:

Adesso[®] iMouse S80 **USB** Wireless Receiver (2) AAA Batteries Quickstart Guide

Shipping Information:

ltem	UPC Code	Package Dimensions	Package Weight	Qty/ Carton
iMouse S80R	783750009669	6.0" x 3.0" x 8.25"	0.38 lbs	10/40
iMouse S80L	783750009652	6.0" x 3.0" x 8.25"	0.38 lbs	10/40
iMouse S80B	783750009638	6.0" x 3.0" x 8.25"	0.38 lbs	10/40





FC CE 🗭